







Ferrite Specifications

Test Frequency	Edge Hole	Inner Hole
30 Mhz	17-27 Ohms	22-30 Ohms
50 Mhz	22-30 Ohms	29-37 Ohms
100 Mhz	29-34 Ohms	35-40 Ohms



Recommended PCB Layout (Bottom View)



Part Number	t _{gold}
KF22-A15S-NJ	Flash
KF22-A15S-NJ15	15u"
KF22-A15S-NJ30	30u"

Material and Finish

Shell: Steel, zinc plated or tin plated

Insulator: PBT with glass-fiber reinforcement
UL 94V-0
color-black

Contact Material:
Phosphor Bronze

Duplex plated as follows:

- 30 .000030" [0.00076mm] gold on mating end, tin-lead on termination end, with entire contact nickel
- 15 .000015" [0.00038mm] gold on mating end, tin-lead on termination end, with entire contact nickel

(Standard) Gold flash on mating end, Gold flash or tin-lead on termination end, with nickel underplate on entire contact

Electrical Specifications

Rated Current:

5A

Rated Voltage:

300V DC

Withstanding Voltage:

500V (rms) AC for 1 min

Insulation Resistance:

more than 1000 Mohm at 500v DC

Contact Resistance:

13 mohm Max

Dielectric Strength:

1000V for 1 min

Temperature Rating:

-55°C to +105°C

CSA NRTL/C Certified File No. LR78160
UL Recognized File No. E169636

REVISION	DATE	DESCRIPTION	DRAWN BY	DESIGNED BY	UNITS
A1	10/7/99	New Drawing	K. Wallace		mm
A2	10/26/00	Ref ECD 00-122	CHECKED BY	APPROVED BY	DATE
					10/7/99

KF22-A15S-NJ

Rt. Ang Ferrite D-Sub

15 Pos. Female, 0.318" Footprint



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[KF22-A15S-NJ](#)