


© COPYRIGHT —

BY —

REVISIONS

LTR	DESCRIPTION	DATE	DWN	APR
V1	REVISED PER ECO-11-005294	5APR11	RK	HMR




.078/.081 DIA.



VIEW A-A



NICKEL ON ENTIRE TERMINAL
WITH .000030 GOLD OVER
INSIDE OF MATING AREA
AND WIRE BARREL.




.110
.085

.105
.080



SECT IB-IB

.145
.120



SECT C-C



NICKEL ON ENTIRE TERMINAL
WITH .000030 GOLD OVER
INSIDE OF MATING AREA.

GOLD	3	.012 PH. BRZ	60617-6
GOLD	1	BRASS	-5
TIN		PH. BRZ	-4
TIN		.012 BRASS	60617-1
FINISH		MATERIAL	PART NO

UNLESS OTHERWISE
SPECIFIED DIMENSIONS
ARE IN INCHES.
TOLERANCES ON:
DECIMALS $\pm .015$
ANGLES $\pm$

MATERIAL

SEE TABLE

FINISH

SEE TABLE

CONTRACT NO

DR *M. FEHER* 11-16-79CHK *D.S. Heide* 1/4/80APPRO *D. Heide* 1-7-80

APPRO

WIRE RANGE

24-18 AWG

INSULATION DIA

.100 MAX

TE

TE Connectivity

NAME

SOCKET, LOOSE PIECE,
COMMERCIAL MATE-N-LOK

SIZE

A

CODE IDENT NO

00779

DRAWING NO

60617

SCALE

SHEET

CUSTOMER DRAWING