

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19 .

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

G

14

P

LTR

DESCRIPTION

DATE

DWN

APVD


A

REV / 0720-0828-95

07DEC95

ME

SB



1. WIRE INSUL DIA, 2.03-3.18 [.080-.125]
2. TONGUE MATL THK, 0.79±0.05 [.031±.002]

5000	ON TAPE, REEL	184206-2
1000	LOOSE PIECE	184206-1
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMMAX RECOMMENDED OPERATING
TEMPERATURE:
170°C [338°F]THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.DWN
L OLMEDA 23JAN95CHK
M ELLIS 23JAN95APVD
S BORTNER 23JAN95

PRODUCT SPEC

UL486A

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

AMP Incorporated
Harrisburg, PA 17105-3608NAME
TERMINAL, RING,
DIAMOND GRIP™,
WIRE SIZE, 22-16 AWGSIZE
A3CAGE CODE
00779DRAWING NO
C-184206SCALE
8:1SHEET
1 OF 1REV
AFOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS
PRODUCT INFORMATION CENTER
1-800-522-6752FOR APPLICATION
TOOLING INFORMATION
TOOLING ASSISTANCE CENTER
1-800-722-1111FOR ORDER ENTRY
1-800-526-5142VOLTAGE RATING:
-CIRCULAR MIL AREA:
0.26mm²-1.65mm² [509-3260]DIMENSIONS:
mm [in]MATERIAL
BODY, CU, SLV, CU PER
ASTM B152TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ±-
1 PLC ±-
2 PLC ±0.20 [.008]
3 PLC ±-
4 PLC ±-
ANGLES ±-FINISH
TIN PLATE
PER MIL-T-10727