


CX2041NL

- RF TRANSFORMER, 1:1
- 0.05–450 MHz
- IMPEDANCE = 75 OHMS
- SURFACE MOUNT

NOTES: UNLESS OTHERWISE SPECIFIED

1. OPERATING TEMPERATURE: -40°C TO $+85^{\circ}\text{C}$
2. STORAGE TEMPERATURE: -50°C TO $+125^{\circ}\text{C}$
3. JEDEC MOISTURE: LEVEL 1.
4. DIMENSIONS ARE IN INCHES WITH THE FOLLOWING TOLERANCE:
.XX= ± 0.01
.XXX= ± 0.005
5. OPTIONAL TAPE & REEL PACKAGING CAN BE ORDERED
BY ADDING A "T" SUFFIX TO THE PART NUMBER(EX: CX2041NLT)
6. ROHS COMPLIANT



ELECTRICAL SPECIFICATIONS: $\odot 25^{\circ}\text{C}$


INSERTION LOSS:

FREQUENCY	ATTENUATION(S21)
50 KHz	-3.0 dB MAX
100 KHz	-1.5 dB MAX
1 MHz	-0.8 dB MAX
5 MHz	-0.8 dB MAX
120 MHz	-0.8 dB MAX
160 MHz	-1.3 dB MAX
200 MHz	-2.0 dB MAX
300 MHz	-2.5 dB MAX
450 MHz	-3.4 dB MAX

RETURN LOSS:

FREQUENCY	ATTENUATION(S11)
100 KHz	-8.0 dB MIN
400 KHz	-18.0 dB MIN
1 MHz	-24.0 dB MIN
5 MHz	-28.0 dB MIN
10 MHz	-25.0 dB MIN
30 MHz	-22.0 dB MIN
80 MHz	-14.5 dB MIN
120 MHz	-11.5 dB MIN
180 MHz	-8.5 dB MIN
200 MHz	-8.0 dB MIN

ELECTRICAL SPECIFICATIONS: $\odot 25^{\circ}\text{C}$



© Copyright, 2013. Pulse Electronics Corp. All rights reserved. Drawing specifications subject to change without notice. (12/16/13)

PULSE CONFIDENTIAL
&
PROPRIETARY

PRODUCT SPECIFICATION:
XFMR, RF, SGL, RAC, 1:1CT, .05–450MH

DWG. NO./ PART NO.
CX2041NL

SHEET:
1 OF 1

REV.
M14