


20 | 19 | 18 | 17 | 16 | 15 | 14 | 13 | 12 | 11 | 10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1

M

VIEW ON MATING SIDE



A = 8 STANDARD CONTACTS L = 3

C = 8 STANDARD CONTACTS L = 3

S = 16 TOTAL NUMBER OF CONTACTS

MARKING	STANDARD
PERFORMANCE LEVEL	G2/0 = CONTACT AREA LEVEL2 / TERMINATION TIN
FLUX PROOF	NO
FLICING CLIP	NO
DIMENSIONS	SD-85003-0002 SHT 1

C	G2/0	c2,4,6,8,10,12,14,16
A	G2/0	a2,4,6,8,10,12,14,16
CONTACT SYMBOL	PERFORMANCE LEVEL	CONTACT POSITION NUMBER

EC NO. 12004-XXXX		DRAWN N.S. 09/09/02		CHECKED G.L. 09/09/02		APPROV. C.G. 09/09/02		REV. B		GENERAL TOLERANCES (UNLESS SPECIFIED)		SCALE <input checked="" type="checkbox"/> MM <input type="checkbox"/> INCH	DESIGN UNITS <input checked="" type="checkbox"/> MM <input type="checkbox"/> INCH	DIMENSIONS		SHT REV		
														<input checked="" type="checkbox"/> THIRD ANGLE PROJECTION	<input type="checkbox"/> INCH	<input type="checkbox"/> INCH	<input type="checkbox"/> MM	REVISE ON CAD ONLY
														TITLE: 48 POS MALE CONNECTOR ACCORDING DIN 41612 STYLE C/2 CONTACTS ARRANGEMENT				
														MOLEX INCORPORATED				
														CAD FILENAME SD-85003-0531.S0 MATERIAL NO. 85003-0531 DRAWING NO. SD-85003-0531				SHEET NO. 1 OF 1
														DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				SIZE D