



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AJ	16		A	REVISED PER EC OS14-0150-05	30AUG05	BM	JL
			A1	REVISED PER ECO-10-000444	31OCT09	KK	AEG



- 1 ZINC PER QQ-Z-363.
- 2 POLYMETHYLPENTENE, GENERAL PURPOSE.
- 3 PHOSPHOR BRONZE PER QQ-B-750.
- 4 BRASS PER ASTM-B-453.
- 5 NICKEL PLATE PER QQ-N-290, 3.81µm [.000150] MINIMUM THICK.
- 6 TIN PLATE PER ASTM-B-545, 3.81µm [.000150] MINIMUM THICK.
- 7 GOLD PLATE PER ASTM-B-488, 0.76µm [.000030] MINIMUM THICK.
- 8 SEE INSTRUCTION SHEET 408-2769.
- 9 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED PANEL CUTOUT

PCB CONFIGURATION

9 OBSOLETE	2.79 ±0.25 [.110 ±.010]	5227676-2
	4.11 ±0.43 [.162 ±.017]	5227676-1
A		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. VARELA - 20APR2005	Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
		CHK J. HAVENER - 20APR2005		
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J. LIPPERT - 20APR2005	NAME	
	0 PLC ± -	PRODUCT SPEC	JACK, RIGHT ANGLE, PCB 50 OHM, SERIES BNC	
	1 PLC ± -	108-12078		
	2 PLC ± 0.05 [.002]	APPLICATION SPEC		
	3 PLC ± -	—	SIZE	CAGE CODE
	4 PLC ± -	—	DRAWING NO	RESTRICTED TO
MATERIAL	FINISH	WEIGHT	A1 00779 5227676	
1 2 3 4	5 6 7	CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 1 REV A1