


ADSL LINE TRANSFORMERS

For GlobespanVirata CO Chipsets



- Approved by GlobespanVirata for use in Annex A and Annex C, Central Office applications
- Small footprint minimizes board space
- Excellent THD performance
- Designed to meet UL1950 and EN60950 supplementary insulation requirements for working voltages up to 250 Vrms

Electrical Specifications @ 25°C — Operating Temperature -40°C to +85°C

Part Number ¹	Surface Mount Leads	Chipset(s)	ADSL CO Termination	Turns Ratio Line : Chip (±2%)	Inductance @ 10 kHz, 100 mV (1-4) with (2-3) shorted	Leakage Inductance @ 100 kHz, 0.1 Vrms Line Side	DC Resistance	
							Line Side (1-4) with (2-3) shorted	Chip Side ²
BX2373JB	J-Lead	Titanium™ Fourte, Titanium™ Fourte RT, and Titanium™ G16	Active	1.15CS:1CS	474 µH ±10%	10 µH MAX	2.5 Ω MAX	2.2 Ω MAX
BX2373WA	Gull-Wing							
BX2369JB	J-Lead		Passive	1.41CS:1CS	474 µH ±6%	10 µH MAX	2.2 Ω MAX	1.7 Ω MAX
BX2369WA	Gull-Wing							
B2414JB	J-Lead	Jupiter™	Active	0.95CS:1CS	750 µH ±7%	5 µH MAX	1.5 Ω MAX	1.5 Ω MAX
B2414WA	Gull-Wing							

Additional Electrical Specifications


Part Number ¹	Longitudinal Balance (from 20 kHz to 1.0 MHz)	THD @ 150 kHz (100 Ω)	Insertion Loss at 100 Ω (dB)	Interwinding Capacitance (@ 100 kHz, 0.1 Vrms)	Isolation Voltage (60 sec)
BX2373JB	≤ -45 dB	≤ -85 dB (@ 12 Vpp)	≤ 0.50 (150 kHz to 300 kHz) ≤ 1.00 (1.0 MHz)	≤ 50 pF	1500 Vrms
BX2373WA					
BX2369JB	≤ -45 dB	≤ -85 dB (@ 15 Vpp)	≤ 1.00 (150 kHz to 1.0 MHz)	≤ 50 pF	1500 Vrms
BX2369WA					
B2414JB	≤ -45 dB (to 1.1 MHz)	≤ -85 dB (@ 12 Vpp)	≤ 0.40 (150 kHz to 300 kHz) ≤ 0.75 (1.0 MHz)	≤ 50 pF	1500 Vrms
B2414WA					

NOTES:

- Transformers are shipped in trays unless Tape & Reel packaging is specified by adding the suffix "T" to the part number (i.e. BX2373JBT).
- Chip Side DCR Measurements: **Schematic A** = (8-5) with (6-7) shorted; **Schematic B** = (8-6) with (5-7) shorted.


Schematics

BX2373WA/BX2369WA/B2414WA



Schematic A

BX2373JB/BX2369JB/B2414JB



Schematic B


ADSL LINE TRANSFORMERS

For GlobespanVirata CO Chipsets




Mechanicals

BX2373JB/BX2369JB/B2414JB



BX2373WA/BX2369WA/B2414WA



For More Information :

UNITED STATES (Worldwide)

12220 World Trade Drive
 San Diego, CA 92128
 U.S.A.
<http://www.pulseeng.com>
 TEL: 858 674 8100
 FAX: 858 674 8262

UNITED KINGDOM (Northern Europe)

1 & 2 Huxley Road
 The Surrey Research Park
 Guildford, Surrey GU2 5RE
 United Kingdom
 TEL: 44 1483 401700
 FAX: 44 1483 401701

FRANCE (Southern Europe)

Zone Industrielle
 F-39270
 Orgelet
 France
 TEL: 33 3 84 35 04 04
 FAX: 33 3 84 25 46 41

SINGAPORE (Southern Asia)

150 Kampong Ampat
 #07-01/02
 KA Centre
 Singapore 368324
 TEL: 65 287 8998
 FAX: 65 280 0080

TAIWAN, R.O.C. (Northern Asia)

3F-4, No. 81, Sec. 1
 HsinTai Wu Road
 Hsi-Chih, Taipei Hsien
 Taiwan, R.O.C.
 Tel: 886 2 2698 0228
 FAX: 886 2 2698 0948

HONG KONG (China/Hong Kong)

19/F, China United Plaza
 1008 Tai Nan West Street
 Cheung Sha Wan, Kowloon
 Hong Kong, China
 TEL: 852 2788 6588
 FAX: 852 2776 1055

DISTRIBUTOR

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners.