



SERIES 62T**Thumbwheel with Pushbutton****FEATURES**

- Scroll and select functions
- Sealed against dust and particles
- Custom bezels that will blend with HMI grips and control panels
- Optional integrated pushbutton with over three million actuations
- MIL-STD-202 and MIL-STD-810F Compliant
- Standard panel seal
- Choice of cable length and termination


APPLICATIONS

- Scroll & select equipment in industrial and non-automotive transportation applications
- Display selectors
- Hand-grip joysticks

**DIMENSIONS** in inches (and millimeters)

WAVEFORM AND TRUTH TABLE

R* - TWO 2.2KΩ RESISTORS REQUIRED FOR OPERATION.



POSITION	OUTPUT A	OUTPUT B
#1		
#2	●	
#3	●	●
#4		●

● Indicates logic high; blank indicates logic low.
Code repeats every 4 positions.

SPECIFICATIONS**Environmental Specifications**

MIL-STD-810F Qualified

Operating Temperature Range: -40° C to 85° C**Storage Temperature Range:** -55° C to 100° C**Humidity:** 240 hours at 95% humidity at 30° C**Mechanical Vibration:** Harmonic motion with amplitude of 15g, within a varied frequency of 10 to 2000 Hz**Mechanical Shock:**

Test 1: 100g for 6 ms half-sine wave with a velocity change of 12.3 ft/sec

Test 2: 100g for 6 ms sawtooth wave with a velocity change of 9.7 ft/sec

Pushbutton Electrical and Mechanical Specifications**Rating:** 10mA @ 5 Vdc**Contact Resistance:** <10ohms**Life:** 3 million actuations minimum**Contact Bounce:** <4 ms make, <10ms break**Actuation Force:** N – None, 7–700g, 10 – 1000g.**Thumbwheel Travel:** .060 ± .015 in**Rotary Electrical and Mechanical Specifications****Operating Voltage:** 5.00±0.25 Vdc**Supply Current:** 25mA Max.**Output:** Open collector phototransistor, external pull up resistors are required**Output Code:** Two-bit quadrature, channel A leads channel B by 90° electrically during clockwise rotation of the thumbwheel
Logic high shall be no less than 3.8 Vdc
Logic low shall be no greater than 0.8 Vdc**Power Consumption:** 125 mW Max.**Mechanical Life:** 1,000,000 cycles of operation for Low and Non-Rotational Torque. 500,000 cycles of operation for Medium Rotational Torque. 1 cycle is a rotation through all positions and a full return.**Average Rotational Torque:**

M: 2.2±.75 in-oz, L: 1.2±0.5 in-oz, N: <0.50 in-oz. Initially torque shall be within 75% of initial value throughout life.

Materials and Finishes**Face Plate:** Plastic**Housing:** ABS Plastic**Side Plate:** Reinforced thermoplastic**Wiper:** Silicone rubber with adhesive**Gasket:** Silicone rubber with adhesive**Wheel:** Plastic**Shaft:** Aluminum**Slide Springs:** Music wire**Detent Spring:** Music wire**Detent Balls:** Nickel plated stainless steel**PC Boards:** NEMA grade FR4. Double clad with copper

Plated with gold over nickel

Pushbutton board is tin plating over copper

LED: Gallium Aluminum Arsenide**Phototransistor:** Gold and Aluminum Alloys**Code Section Housing:** Reinforced plastic**Detent Housing:** Thermoplastic**Code Rotor:** Delrin 100 plastic**Dome:** Stainless steel**Dome retainer:** Delrin 100 plastic**Slide Rods:** Stainless steel**Splining Key:** Stainless steel**Actuator:** Reinforced thermoplastic**Screws:** Aluminum or Stainless**Wiper Plate:** Copper**Solder:** Lead free (96.5% tin, 3% silver, 0.5% copper, no clean)

Series

Angle of Throw: 22 = 22.5° for code change and 16 detent positions

Rotational Torque: N = Non-Detent, L=Low Torque, M=Medium Torque

Pushbutton Option: 0=No Pushbutton, 7=700 grams, 10=1000 grams

Termination: C = .050 Center ribbon Cable with connector

Cable Termination: 040=4.0 inches. Cable is terminated with [Amp Connector P/N 7-215083-6](#).See [Amp Mateability Guide](#) for Mating Connector details.

Available from your local Grayhill Component Distributor. For pricing and discounts, contact a local Sales Office, an authorized local Distributor, or Grayhill.