







REVISIONS				
REV.	ECO. NO.	DESCRIPTION	DATE	BY
A	2145	INITIAL RELEASE	07/16/2010	LH
B	2456	CORRECTED OPEN TOP VIEW TO MATCH PART, UPDATED DWG FORMAT	9/27/2011	JH



NOTES:

1. INSULATOR MATERIAL: PBT.
2. CONTACT MATERIAL: PHOSPHOR BRONZE.
3. PLATING: GOLD FLASH OVERALL.
4. UL FLAMMABILITY RATING: 94V-0.
5. DIELECTRIC WITHSTANDING VOLTAGE: 650V AC.
6. CURRENT RATING: 1 AMP PER CONTACT.
7. CONTACT RESISTANCE: 30 MILLI OHMS MAX.
8. INSULATION RESISTANCE: 1000 MEGA OHMS.
9. OPERATING TEMPERATURE: -40 °C TO +85 °C.
10. DOUBLE TUNING FORK TYPE CONTACT, ACCOMMODATES .020" [0.50mm] SQ PINS, .079" [2.00mm] PITCH LOW-PROFILE MINI TYPE.



RoHS COMPLIANT

DRAWN 7/16/2010 LH	DATE 7/16/2010 LH	NAME SULLINS CONNECTOR SOLUTIONS
UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES [MM]		
TOLERANCES: ANGULAR: $\pm 30'$		
.XX=± .012 [.30] .XXX=± .008 [.20] .XXXX=± .004 [.10]		
INTERPRET DIMENSIONS AND TOLERANCING PFR: ASME Y14.5M-2009		
SIZE C	CAGE CODE 54453	DWG. NO. 11504
SCALE: 16:1		SHEET 1 OF 1