

K9506Z

Drive: 1"
Finish: forged, phosphated
Material: CHROMO-EXTRA
Torque according to DIN and ASME
T=depth of female hexagon
With Dynamic-Drive-Profile



					L mm	D1 mm	D2 mm	T mm		
K9506Z-1		7314150131686	1	1	108	42.5	54	30	K560F-7	1060
K9506Z-1.1/16		7314150131693	1	1 1/16	108	44.5	54	30	K560F-7	1120
K9506Z-1.3/16		7314150131716	1	1 3/16	108	49	54	30	K560F-7	1200
K9506Z-1.1/4		7314150131723	1	1 1/4	108	51.5	54	30	K560F-7	1220
K9506Z-1.7/16		7314150131754	1	1 7/16	108	56.5	54	35	K560F-7	1280
K9506Z-1.1/2		7314150131761	1	1 1/2	108	59	54	35	K560F-7	1330
K9506Z-1.5/8		7314150131785	1	1 5/8	108	62.5	54	38	K560F-7	1470
K9506Z-1.13/16		7314150131808	1	1 13/16	108	69	60.3	42	K560F-7	1640
K9506Z-1.7/8		7314150131815	1	1 7/8	108	70	60.3	42	K560F-7	1680

Special pry bar

3681

With a long tapered end for alignments and a rolling head for prying.
Finish: black phosphated with polished head
Material: hardened special alloyed steel



					
3681-11		7314150132980	1	304	230
3681-16		7314150132997	1	406	450
3681-20		7314150133000	1	508	835

