

- 1

CONTACT MATING AREA MEETS THE PERFORMANCE REQUIREMENTS OF
TE CONNECTIVITY PRODUCT SPECIFICATION 108-1957; BASED ON
TELCORDIA GR-1217-CORE, APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.
- 2

PHOSPHOR BRONZE
- 3

GLASS FILLED POLYESTER
- 4

DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
- 5





CONNECTOR MARKED WITH PART NUMBER AND DATE CODE
- 6

DRILLED HOLE DIAMETER 0.7±0.025
FINISHED HOLE DIA 0.60±0.05 REF
COPPER THICKNESS 0.025-0.050
TIN LEAD THICKNESS 0.004-0.010
- 7

CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT
TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995
- 8

APPLICATION SEATING HEIGHT TO PRINTED CIRCUIT BOARD

LOC		DIST		REVISIONS					
AD		47		P	LTR	DESCRIPTION	DATE	DWN	APVD
					C	REVISED PER ECO-11-013132	13JUL2011	HMR	MH



RECOMMENDED
PRINTED CIRCUIT BOARD
LAYOUT
COMPONENT SIDE OF PRINTED CIRCUIT BOARD

120683-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	H. MOLL	5-25-99	STE TE Connectivity			
		CHK	H. ANDREWS	5-25-99				
		APVD	H. ANDREWS	5-25-99	NAME			
					SHROUD ASSEMBLY, 30 POSITION, 6 ROW, RIGHT HAND, Z-PACK HS3			
					SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
					A1	00779	C=120683	-
					CUSTOMER DRAWING			
					SCALE	6:1	SHEET 1 OF 1	REV C