

HDSP-C2x1/C2x3

2.3" Single Digit PCB Based LED Display



Data Sheet

Description

This is a 2.3" height single digit display. It utilizes GaAsP/ GaP Red, Orange, Yellow, Green and AlGaAs/GaAs Red chips. This device is halogenated.


Features

- High reliability
- Excellent characters appearance
- Available in CA and CC
- RoHS Compliant
- Gray top surface with white diffused segments.

Ordering Information

Red	Green	Yellow	Orange	AlGaAs Red	Description
HDSP-C2E1	HDSP-C2G1	HDSP-C2Y1	HDSP-C2L1	HDSP-C2A1	Common Anode, Right Hand Decimal
HDSP-C2E3	HDSP-C2G3	HDSP-C2Y3	HDSP-C2L3	HDSP-C2A3	Common Cathode, Right Hand Decimal


Package Dimensions



Notes:

1. All dimensions are in millimeter.
2. Unless otherwise stated, the tolerance is $\pm 0.25\text{mm}$.

Circuit Diagram



Absolute Maximum Ratings at $T_A = 25^\circ\text{C}$

Parameter	Symbol	Red/Yellow/ Orange	Green	AlGaAs Red	Units
Power Dissipation per segment/Dot Point (DP)	P_D	230/115	250/125	200/100	mW
Continuous Forward Current per segment or DP	I_F	25	25	25	mA
Derating Linearly from 25°C per segment		0.33	0.33	0.33	mA/ $^\circ\text{C}$
Reverse Voltage per segment/DP	V_R		20/10		V
Operating Temperature	T_O		-40 to 85		$^\circ\text{C}$
Storage Temperature	T_S		-40 to 85		$^\circ\text{C}$
Wave solder Condition 1.6mm below body			250 $^\circ\text{C}$ peak for 3 secs max		

Electrical / Optical Characteristic at $T_A = 25^\circ\text{C}$ **Red**

Parameter	Symbol	Min	Typ	Max	Units	Test Conditions
Average Luminous Intensity (Digit Average)	I_V	–	20	–	mcd	$I_F = 10\text{mA}$
Peak Wavelength	λ_P	–	640	–	nm	$I_F = 20\text{mA}$
Dominant Wavelength	λ_d	–	626	–	nm	$I_F = 20\text{mA}$
Forward Voltage per segment/DP	V_F	–	8.0/4.0	9.2/4.6	V	$I_F = 20\text{mA}$
Reverse Current per segment/DP	I_R	–	–	100	μA	$V_R = 20\text{V}/10\text{V (DP)}$
Luminous Intensity Matching Ratio (Segment to Segment)	I_{V-M}		2:1			$I_F = 10\text{mA}$

Green

Parameter	Symbol	Min	Typ	Max	Units	Test Conditions
Average Luminous Intensity (Digit Average)	I_V	–	28	–	mcd	$I_F = 10\text{mA}$
Peak Wavelength	λ_P	–	565	–	nm	$I_F = 20\text{mA}$
Dominant Wavelength	λ_d	–	569	–	nm	$I_F = 20\text{mA}$
Forward Voltage per segment/DP	V_F	–	9.0/4.5	10/5	V	$I_F = 20\text{mA}$
Reverse Current per segment/DP	I_R	–	–	100	μA	$V_R = 20\text{V}/10\text{V (DP)}$
Luminous Intensity Matching Ratio (Segment to Segment)	I_{V-M}		2:1			$I_F = 10\text{mA}$

Yellow

Parameter	Symbol	Min	Typ	Max	Units	Test Conditions
Average Luminous Intensity (Digit Average)	I_V	–	12	–	mcd	$I_F = 10\text{mA}$
Peak Wavelength	λ_P	–	587	–	nm	$I_F = 20\text{mA}$
Dominant Wavelength	λ_d	–	589	–	nm	$I_F = 20\text{mA}$
Forward Voltage per segment/DP	V_F	–	8.6/4.3	9.2/4.6	V	$I_F = 20\text{mA}$
Reverse Current per segment/DP	I_R	–	–	100	μA	$V_R = 20\text{V}/10\text{V (DP)}$
Luminous Intensity Matching Ratio (Segment to Segment)	I_{V-M}		2:1			$I_F = 10\text{mA}$

Orange

Parameter	Symbol	Min	Typ	Max	Units	Test Conditions
Average Luminous Intensity (Digit Average)	I_V	–	20	–	mcd	$I_F = 10\text{mA}$
Peak Wavelength	λ_p	–	610	–	nm	$I_F = 20\text{mA}$
Dominant Wavelength	λ_d	–	605	–	nm	$I_F = 20\text{mA}$
Forward Voltage per segment/DP	V_F	–	8.6/4.3	9.2/4.6	V	$I_F = 20\text{mA}$
Reverse Current per segment/DP	I_R	–	–	100	μA	$V_R = 20\text{V}/10\text{V (DP)}$
Luminous Intensity Matching Ratio (Segment to Segment)	I_{V-M}		2:1			$I_F = 10\text{mA}$

AlGaAs Red

Parameter	Symbol	Min	Typ	Max	Units	Test Conditions
Average Luminous Intensity (Digit Average)	I_V	–	78	–	mcd	$I_F = 10\text{mA}$
Peak Wavelength	λ_p	–	660	–	nm	$I_F = 20\text{mA}$
Dominant Wavelength	λ_d	–	643	–	nm	$I_F = 20\text{mA}$
Forward Voltage for segment/DP	V_F	–	7.4/3.7	8.0/4.0	V	$I_F = 20\text{mA}$
Reverse Current per segment/DP	I_R	–	–	100	μA	$V_R = 20\text{V}/10\text{V (DP)}$
Luminous Intensity Matching Ratio (Segment to Segment)	I_{V-M}		2:1			$I_F = 10\text{mA}$

Red




Figure 1. Relative Luminous Intensity Vs Forward Current




Figure 2. Forward Voltage Vs Current (Segment)




Figure 3. Forward Voltage Vs Current (DP)




Figure 4. Relative Luminous Intensity Vs Wavelength

Green




Figure 5. Relative Luminous Intensity Vs Forward Current




Figure 6. Forward Voltage Vs Current (Segment)




Figure 7. Forward Voltage Vs Current (DP)




Figure 8. Relative Luminous Intensity Vs Wavelength

Yellow




Figure 9. Relative Luminous Intensity Vs Forward Current




Figure 10. Forward Voltage Vs Current (Segment)




Figure 11. Forward Voltage Vs Current (DP)




Figure 12. Relative Luminous Intensity Vs Wavelength

Orange




Figure 13. Relative Luminous Intensity Vs Forward Current




Figure 14. Forward Voltage Vs Current (Segment)




Figure 15. Forward Voltage Vs Current (DP)




Figure 16. Relative Luminous Intensity Vs Wavelength

AlGaAs Red




Figure 17. Relative Luminous Intensity Vs Forward Current




Figure 18. Forward Voltage Vs Current (Segment)




Figure 19. Forward Voltage Vs Current (DP)







Figure 20. Relative Luminous Intensity Vs Wavelength

Packing Tube Specifications:

10 PCS PRODUCTS PER IC TUBE



Tube Front View



Tube Top View

For product information and a complete list of distributors, please go to our web site: www.avagotech.com

Avago, Avago Technologies, and the A logo are trademarks of Avago Technologies in the United States and other countries.
Data subject to change. Copyright © 2005-2010 Avago Technologies. All rights reserved.
AV02-2496EN - May 14, 2010

Avago
TECHNOLOGIES