

Plug-in Screw Connector Systems for Printed Circuit Boards

TYPE 971-SLT-SMD

5 mm spacing - 2 to 12 poles


 [Distributor Stock Check](#)



Series	Download PDF	3D Model	Can plug with	How to order	Color specifications	Print
--------	--------------	----------	---------------	--------------	----------------------	-------



RoHS WEEE Pb free
compliant



Dimensions: mm (in.)

Length of Connector (L)

L = No. of Poles x Center to Center Spacing

(A) Odd numbers of poles

(B) Even numbers of poles

(C) PCB Pad layout

Recommended Stencil Thickness: 0.15 mm (0.006 in.)

When locating connector, allow 0.5 mm clearance around it for process-induced variations.

Description

U.S. Pat. 6,224,399B1

- Pinstrip
- low profile
- Plug-In Direction Perpendicular to PCB and Wire Entrance Parallel to PCB when plugged with **950-NAF-DS**, **950-NLFL-DS**, **958-NLFL-DS**, **950-FL-DS**, **950-T-FL-DS**, **115-F-111**, **115-F-118** and **115-F-211**
- Exceptional pin retention force on SMT
- Typical resistance to horizontal peel off force per 2 poles: 15 kgf (33 lbf), per 6 poles: 28 kgf (61 lbs) (depending on soldering process).

Technical Data

Center to Center Spacing: 5 mm (0.197 in.)

Approval Information

Rating	Current(A)	Voltage(V)	Application group	AWG
UL	10	300	B	
CSA	10	300	B	

Material

Molding: Polyamide 4.6, 30% GF (glass fiber reinforced), self extinguishing UL 94, V-0, color Black

Temperature limits:

Short Time: 260°C (500°F)

Continuous: RTI 105°C (221°F)

Low Limit: -40°C (-40°F)

Comparative Tracking Index: CTI > 250

Oxygen Index Rating: 37 %

Average weight: 0.1 gram,

Solder Pin: Ø 1.1 mm (0.04 in.), Tin plated copper alloy

Top of page

How to order

Item 971-SLT-SMD

- Options
- G05: Gold Plating (5 micro inches)
 - G30: Gold Plating (30 micro inches)
 - S30: Silver Plating (30 micro inches)
 - TR: Tape and Reel Assembly
 - PCP: Removable Pick Cap

Note: Plated component: solder pin

Ordering Note: This product is currently available in Tape and Reel in 6 poles only. For other configuration, please contact factory.

971-SLT-SMD /

POLES:
02 to 12

Request sample
Request quote

Quantity

Accessories

Add to shopping cart