




	1	2	3	4	5	6	7																																																																											
A	  RECOMMENDED PCB. LAYOUT  Material Terminal body (Contact pin): Brass Wire guard: Stainless steel Surface of solder tail: Tin plated Insulator (housing): Thermoplastic (UL94V-0) Electrical Voltage rating: 300VAC Current rating: 15A Wire range: Solid wire(AWG): 12-28 Stranded wire(AWG): 12-28 Pull force: Screw: Wire strip length: 6-7mm Withstanding Voltage: 1.6KV Operating temperature: -40°C to +115°C Soldering temperature: 250°C±10°C/5 Sec Safety approval :  N=Number of contacts							A																																																																										
B								B																																																																										
C								C																																																																										
D								D																																																																										
E								E																																																																										
F								F																																																																										
G	RoHS compliant <table><tr><td>Scale</td><td>1:1</td></tr><tr><td>TOLERANCE</td><td></td></tr><tr><td>X.</td><td>±0.50</td></tr><tr><td>X.X</td><td>±0.30</td></tr><tr><td>X.XX</td><td>±0.10</td></tr><tr><td>DIM</td><td>TOL</td></tr><tr><td>X.°</td><td>±1°</td></tr><tr><td>X.X°</td><td>±X°</td></tr><tr><td>Angle</td><td>TOL</td></tr></table> <table><tr><td></td><td></td><td></td><td></td><td></td><td>Date</td><td>Name</td><td>Customer-No.</td></tr><tr><td></td><td></td><td></td><td></td><td>Drawn</td><td>29.07.2009</td><td>Dean</td><td rowspan="3">ASSMANN WSW-No. A-TB508-HGxx</td></tr><tr><td></td><td></td><td></td><td></td><td>Approved</td><td>29.07.2009</td><td>Hellwig</td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td>Drawing-No.</td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td>ASS 3605 CO</td><td>rev01</td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td>Replace</td><td>Sheet</td></tr></table> 							Scale	1:1	TOLERANCE		X.	±0.50	X.X	±0.30	X.XX	±0.10	DIM	TOL	X.°	±1°	X.X°	±X°	Angle	TOL						Date	Name	Customer-No.					Drawn	29.07.2009	Dean	ASSMANN WSW-No. A-TB508-HGxx					Approved	29.07.2009	Hellwig															Drawing-No.								ASS 3605 CO	rev01								Replace	Sheet	G
Scale	1:1																																																																																	
TOLERANCE																																																																																		
X.	±0.50																																																																																	
X.X	±0.30																																																																																	
X.XX	±0.10																																																																																	
DIM	TOL																																																																																	
X.°	±1°																																																																																	
X.X°	±X°																																																																																	
Angle	TOL																																																																																	
					Date	Name	Customer-No.																																																																											
				Drawn	29.07.2009	Dean	ASSMANN WSW-No. A-TB508-HGxx																																																																											
				Approved	29.07.2009	Hellwig																																																																												
							Drawing-No.																																																																											
							ASS 3605 CO	rev01																																																																										
							Replace	Sheet																																																																										
H	<table><tr><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr></table>																							H																																																										
	1	2	3	4	5	6	7	SVxxx																																																																										