


LOC	DIST	REVISIONS					
CM	52	P	LTR	DESCRIPTION	DATE	DWN	APVD
			F	REVISED PER EC 0G1B-0065-99	17-JUN-99	KW	JE

D




C

B


A



- 1. WIRE RANGE: 0.08 - 0.15 MM² (28 - 26 AWG)
- 2. INSULATION RANGE: 0.81 - 1.45



1.45	.057	1.96	.077	2.79	.110	-	-
0.81	.032	1.93	.076	2.54	.100	-	-
0.51	.020	1.78	.070	2.36	.093	13.84	.545
0.32	.013	1.57	.062	2.31	.091	6.48	.255
0.13	.005	1.55	.061	2.24	.088	3.18	.125
MM	IN	MM	IN	MM	IN	MM	IN
CONVERSION TABLE							



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
0.32 PH BRZ

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±0.13
3 PLC ±-
4 PLC ±-
ANGLES ±-
FINISH
PRE TIN

DWN
T. BECK
6-16-97

CHK
R. SWING
6-16-97

APVD
A. BEDDICK
8-22-97

PRODUCT SPEC
108-1025

APPLICATION SPEC
114-1008

WEIGHT
-

CUSTOMER DRAWING

MINI
APPLICATOR

350221-1
PART NUMBER

AMP
AMP Incorporated
Harrisburg, PA 17105-3608

NAME
RECEPTACLE, .093 DIAMETER,
28-26 AWG, .032-.057
INSULATION, P.C. CONTACT

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-350221

RESTRICTED TO
-

SCALE
10:1

SHEET
1

OF
1

REV
F

D

C

B

A

350221

AMP 1471-9 REV 27JUN96
17-JUN-99 09:12:35 amp19538 /home/amp19538/ednmod