



+ CONNECTORS

BOARD-TO-BOARD HEADERS & RECEPTACLES



✓ Active

TE CONNECTIVITY (TE)
Mezalok, Socket, 114 p, 12 mm, 50 Au, LF
[Mezalok](#) | [Mezalok](#)

2102061-4
TE Internal Number: 2102061-4

[EU RoHS Compliant](#)
[EU ELV Compliant](#)
Connector Style Receptacle

Number of Positions 114
Centerline (Pitch) 1.27 mm [.05 in]
Stack Height 12 mm [.472 in]
Packaging Method Tape & Reel

[↓](#) **PRODUCT DRAWING**
English

[↓](#) **3D PDF**

DOCUMENTATION

Product Drawings

ASSEMBLY, SOCKET, 114 POSITION, MEZALOK STACKING CONNECTOR
PDF
English

CAD Files

3D PDF
PDF
3D

Customer View Model
2D_DXF.ZIP
English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Specifications

Product Specification

Product Specification For The Mezalok Stacking Connector System

PDF

English

Qualification Test Report

MEZALOK* Stacking Connector System

PDF

English

Design For Environment Standard

Mezalok Stacking Connectors

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

- Connector Style Receptacle
- Sealable No
- Connector & Contact Terminates To Printed Circuit Board
- Gasket Without
- Stabilizers Without
- Row-to-Row Spacing 1.27 mm [.0499 in]
- Series Mezalok
- PCB Mounting Orientation Vertical
- Connector Type Connector Assembly
- Boss Without
- Hybrid No
- Strain Relief Without
- Product Type Connector

Configuration Features

- Stackable Yes
- Number of Positions 114
- Number of Rows 6

Electrical Characteristics

Dielectric Withstanding Voltage (VAC) 750
Voltage (VAC) 250
Insulation Resistance (MΩ) 1000

Body Features

Color Natural

Contact Features

Contact Protection Without
Contact Mating Area Plating Material Gold
Contact Mating Area Plating Thickness 1.27 μm [49.9999 μin]
Contact Layout Matrix
Contact Base Material Beryllium Copper
Contact Type Socket

Termination Features

Termination Method to PC Board Surface Mount - Solder Ball

Mechanical Attachment

PCB Mount Retention Without

Housing Features

Centerline (Pitch) 1.27 mm [.05 in]
Housing Material LCP (Liquid Crystal Polymer)
Housing Color Natural

Dimensions

Stack Height 12 mm [.472 in]
Height 8 mm [.3144 in]

Usage Conditions

Operating Temperature Range -55 – 125 °C [-67 – 257 °F]

Operation/Application

Assembly Process Feature None
Pick and Place Cover With
For Use With Pin Housing

Industry Standards

Industry Standard Configuration VITA 61
Industry Standard VITA 61

Packaging Features

Packaging Method Tape & Reel
Packaging Quantity 350

Other

Comment Conforms to requirement of VITA 61 (VITA 42 Alternate)., VITA 42 and VITA 61 are not intermateable but are footprint and XMC architecture compatible.

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF