


- Designed for Complementary Use with BDX54, BDX54A, BDX54B and BDX54C
- 60 W at 25°C Case Temperature
- 8 A Continuous Collector Current
- Minimum  $h_{FE}$  of 750 at 3V, 3 A



Pin 2 is in electrical contact with the mounting base.

MDTRACA

#### absolute maximum ratings at 25°C case temperature (unless otherwise noted)

RATING		SYMBOL	VALUE	UNIT
Collector-base voltage ( $I_E = 0$ )	BDX53	$V_{CBO}$	45	V
	BDX53A		60	
	BDX53B		80	
	BDX53C		100	
Collector-emitter voltage ( $I_B = 0$ )	BDX53	$V_{CEO}$	45	V
	BDX53A		60	
	BDX53B		80	
	BDX53C		100	
Emitter-base voltage	$V_{EBO}$		5	V
Continuous collector current	$I_C$		8	A
Continuous base current	$I_B$		0.2	A
Continuous device dissipation at (or below) 25°C case temperature (see Note 1)	$P_{tot}$		60	W
Continuous device dissipation at (or below) 25°C free air temperature (see Note 2)	$P_{tot}$		2	W
Operating junction temperature range	$T_j$		-65 to +150	°C
Operating temperature range	$T_{stg}$		-65 to +150	°C
Operating free-air temperature range	$T_A$		-65 to +150	°C

NOTES: 1. Derate linearly to 150°C case temperature at the rate of 0.48 W/°C.  
2. Derate linearly to 150°C free air temperature at the rate of 16 mW/°C.

#### PRODUCT INFORMATION

**electrical characteristics at 25°C case temperature (unless otherwise noted)**

PARAMETER	TEST CONDITIONS			MIN	TYP	MAX	UNIT	
$V_{(BR)CEO}$ Collector-emitter breakdown voltage	$I_C = 100 \text{ mA}$	$I_B = 0$	(see Note 3)	BDX53 BDX53A BDX53B BDX53C	45 60 80 100			V
$I_{CEO}$ Collector-emitter cut-off current	$V_{CE} = 30 \text{ V}$	$I_B = 0$		BDX53		0.5		
	$V_{CE} = 30 \text{ V}$	$I_B = 0$		BDX53A		0.5	mA	
	$V_{CE} = 40 \text{ V}$	$I_B = 0$		BDX53B		0.5		
	$V_{CE} = 50 \text{ V}$	$I_B = 0$		BDX53C		0.5		
$I_{CBO}$ Collector cut-off current	$V_{CB} = 45 \text{ V}$	$I_E = 0$		BDX53		0.2		
	$V_{CB} = 60 \text{ V}$	$I_E = 0$		BDX53A		0.2	mA	
	$V_{CB} = 80 \text{ V}$	$I_E = 0$		BDX53B		0.2		
	$V_{CB} = 100 \text{ V}$	$I_E = 0$		BDX53C		0.2		
$I_{EBO}$ Emitter cut-off current	$V_{EB} = 5 \text{ V}$	$I_C = 0$				2	mA	
$h_{FE}$ Forward current transfer ratio	$V_{CE} = 3 \text{ V}$	$I_C = 3 \text{ A}$	(see Notes 3 and 4)	750				
$V_{BE(sat)}$ Base-emitter saturation voltage	$I_B = 12 \text{ mA}$	$I_C = 3 \text{ A}$	(see Notes 3 and 4)			2.5	V	
$V_{CE(sat)}$ Collector-emitter saturation voltage	$I_B = 12 \text{ mA}$	$I_C = 3 \text{ A}$	(see Notes 3 and 4)			2	V	
$V_{EC}$ Parallel diode forward voltage	$I_E = 3 \text{ A}$	$I_B = 0$				2.5	V	

NOTES: 3. These parameters must be measured using pulse techniques,  $t_p = 300 \mu\text{s}$ , duty cycle  $\leq 2\%$ .

4. These parameters must be measured using voltage-sensing contacts, separate from the current carrying contacts.

**thermal characteristics**

PARAMETER	MIN	TYP	MAX	UNIT
$R_{\theta,JC}$ Junction to case thermal resistance			2.08	°C/W
$R_{\theta,JA}$ Junction to free air thermal resistance			62.5	°C/W

**resistive-load-switching characteristics at 25°C case temperature**

PARAMETER	TEST CONDITIONS <sup>†</sup>			MIN	TYP	MAX	UNIT
$t_{on}$ Turn-on time	$I_C = 3 \text{ A}$	$I_{B(on)} = 12 \text{ mA}$	$I_{B(off)} = -12 \text{ mA}$		1		μs
$t_{off}$ Turn-off time	$V_{BE(off)} = -4.5 \text{ V}$	$R_L = 10 \Omega$	$t_p = 20 \mu\text{s}$ , dc $\leq 2\%$		5		μs

<sup>†</sup> Voltage and current values shown are nominal; exact values vary slightly with transistor parameters.

**PRODUCT INFORMATION**

## TYPICAL CHARACTERISTICS




Figure 1.




Figure 2.




Figure 3.

## PRODUCT INFORMATION

MAXIMUM SAFE OPERATING REGIONS




Figure 4.

THERMAL INFORMATION




Figure 5.

PRODUCT INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bourns](#):

[BDX53](#) [BDX53C](#) [BDX53A](#) [BDX53B](#) [BDX53A-S](#) [BDX53B-S](#) [BDX53C-S](#) [BDX53-S](#)