




## Long Life Cermet Potentiometer 2 Million Cycles






### FEATURES

- 2 million cycles
- Cermet element
- 12.5 mm square single turn panel control
- 4, 6 and 6.35 shaft diameters and 29 terminal styles
- Multiple assemblies - up to four modules
- Test according to CECC 41000 or IEC 60393-1
- Low temperature coefficient
- Custom designs on request
- Linearity  $\pm 3\%$  ( $\pm 2\%$  available)
- Material categorization: For definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)


**RoHS  
COMPLIANT**

VERSATILE	MODULAR	COMPACT	ROBUST
<b>CONFIGURATION EXAMPLE</b> - Dimensions in millimeters (inches) $\pm 0.5\text{ mm}$ ( $\pm 0.02\text{ in}$ )			
Single module, single shaft, vertical mounting, PC pins with support plate, metric bushing and shaft			
			
Dual modules, single shaft, PC pins with front support plates, imperial bushing and shaft			

**GENERAL SPECIFICATIONS**

<b>ELECTRICAL (initial)</b>							
Resistive Element	Cermet						
Electrical Travel	$270^\circ \pm 10^\circ$						
Standard Resistance Values	1 k $\Omega$ , 5 k $\Omega$ , 10 k $\Omega$ , 50 k $\Omega$						
Tolerance	<table> <tr> <td>Standard</td><td><math>\pm 20\%</math></td></tr> <tr> <td>On Request</td><td><math>\pm 5\%</math> or <math>\pm 10\%</math></td></tr> </table>	Standard	$\pm 20\%$	On Request	$\pm 5\%$ or $\pm 10\%$		
Standard	$\pm 20\%$						
On Request	$\pm 5\%$ or $\pm 10\%$						
Taper							
Circuit Diagram							
Power Rating at 70 °C	<table> <tr> <td>Linear Taper</td><td>0.1 W at + 70 °C</td></tr> <tr> <td>Non-Linear Taper</td><td>0.05 W at + 70 °C</td></tr> <tr> <td>Multiple Assemblies</td><td>0.1 W at + 70 °C per module</td></tr> </table> 	Linear Taper	0.1 W at + 70 °C	Non-Linear Taper	0.05 W at + 70 °C	Multiple Assemblies	0.1 W at + 70 °C per module
Linear Taper	0.1 W at + 70 °C						
Non-Linear Taper	0.05 W at + 70 °C						
Multiple Assemblies	0.1 W at + 70 °C per module						
Temperature Coefficient (Typical)	$\pm 150$ ppm						
Limiting Element Voltage	350 V						
End Resistance (Typical)	2 $\Omega$						
Independent Linearity	$\pm 3\%$ ( $\pm 2\%$ available)						
Insulation Resistance	$10^6$ M $\Omega$ min.						
Dielectric Strength	1500 V <sub>RMS</sub> min.						
Attenuation	-						
Mechanical Endurance	2 000 000 cycles						

<b>MECHANICAL</b> (initial)	
<b>Mechanical Travel</b>	300° ± 5°
<b>Operating Torque (Typical)</b>	
<b>Single and Dual Assemblies</b>	0.4 Ncm to 1.7 Ncm max. (0.57 oz.-inch to 2.55 oz.-inch max.)
<b>Three to Four Modules (Per Module)</b>	0.2 Ncm to 0.3 Ncm max. (0.28 oz.-inch to 0.42 oz.-inch max.)
<b>End Stop Torque</b>	
<b>4 mm Dia. Shafts</b>	35 Ncm max. (2.9 lb-inch max.)
<b>6 mm and 1/4" Dia. Shafts</b>	80 Ncm max. (6.8 lb-inch max.)
<b>Tightening Torque</b>	
<b>7 mm Dia. Bushings</b>	150 Ncm max. (13 lb-inch max.)
<b>10 mm and 3/8" Dia. Bushings</b>	250 Ncm max. (21 lb-inch max.)
<b>Weight</b>	7 g to 9 g per module (0.25 oz. to 0.32 oz.)

<b>ENVIRONMENTAL</b>	
<b>Operating Temperature Range</b>	- 55 °C to + 125 °C
<b>Climatic Category</b>	55/125/56
<b>Sealing</b>	IP64


<b>MARKING</b>	<b>PACKAGING</b>
<ul style="list-style-type: none"> <li><b>Potentiometer Module</b> Vishay logo, nominal ohmic value, and tolerance (code), identify P11L version, variation law, manufacturing date (four digits), "3" for the lead 3</li> <li><b>Switch Module</b> Version, manufacturing date (four digits), "c" for common lead</li> </ul>	<ul style="list-style-type: none"> <li>Box</li> </ul>

<b>PERFORMANCES</b>				
<b>TESTS</b>	<b>CONDITIONS</b>	<b>TYPICAL VALUES AND DRIFTS</b>		
		$\Delta R_T/R_T$ (%)	$\Delta R_{1-2}/R_{1-2}$ (%)	<b>OTHER</b>
<b>Electrical Endurance</b>	1000 h at rated power 90'/30' - ambient temp. 70 °C	± 2 %	-	-
<b>Climatic Sequence</b>	Dry heat at + 125 °C/damp heat cold - 55 °C/damp heat, 5 cycles	± 1 %	-	-
<b>Damp Heat, Steady State</b>	+ 40 °C, 93 % relative humidity 56 days	± 2 %	-	Insulation resistance: > 1000 MΩ
<b>Change of Temperature</b>	- 55 °C to + 125 °C, 5 cycles	± 0.2 %	-	-
<b>Mechanical Endurance</b>	2 million cycles turn angle: ± 60° temperature: 20 °C	± 20 %	-	Independent linearity: ± 10 %
<b>Shock</b>	50 g's, 11 ms 3 shocks - 3 directions	± 0.2 %	± 0.5 %	-
<b>Vibration</b>	10 Hz to 55 Hz 0.75 mm or 10 g's, 6 h	± 0.2 %	-	$\Delta V_{1-2}/V_{1-3} = \pm 0.5 \%$

ORDERING INFORMATION (part number)																	
P	1	1	L	2	F	A	G	O	S	Y	0	0	5	0	2	K	A
<b>MODEL</b>	<b>NUMBER OF MODULES</b>		<b>BUSHING</b>	<b>LOCATING PEG</b>		<b>SHAFT</b>	<b>SHAFT STYLE</b>		<b>LEADS</b>		<b>RESISTANCE CODE/TOLERANCE/TAPER OR SPECIAL</b>						
P11L	1 2 3 4																

STANDARD RESISTANCE ELEMENT DATA				
STANDARD RESISTANCE VALUES	LINEAR TAPER		NON-LINEAR TAPER	
	MAX. POWER AT 70 °C	MAX. WORKING VOLTAGE	MAX. POWER AT 70 °C	MAX. WORKING VOLTAGE
Ω	W	V	W	V
1K	0.1	10.0	0.05	7.1
5K	0.1	22.4	0.05	15.8
10K	0.1	31.6	0.05	22.4
50K	0.1	70.7	0.05	50.0

ORDERING INFORMATION (part number)																											
P	1	1	L	2	F	A	G	O	S	Y	0	0	5	0	2	K	A										
MODEL	NUMBER OF MODULES	BUSHING		LOCATING PEG		SHAFT	SHAFT STYLE		LEADS		RESISTANCE CODE/TOLERANCE/TAPER OR SPECIAL																
		<table border="1"> <thead> <tr> <th></th><th><math>\emptyset</math></th><th>L</th></tr> </thead> <tbody> <tr> <td>F</td><td>3/8"</td><td>3/8"</td></tr> <tr> <td>Q</td><td>7</td><td>8</td></tr> <tr> <td>V</td><td>10</td><td>9.5</td></tr> </tbody> </table>			$\emptyset$	L	F	3/8"	3/8"	Q	7	8	V	10	9.5												
	$\emptyset$	L																									
F	3/8"	3/8"																									
Q	7	8																									
V	10	9.5																									



BUSHINGS		mm ( $\pm 0.5$ )	mm ( $\pm 0.5$ )	INCHES ( $\pm 0.02$ )
		V	Q	F
A	Shafts	$\emptyset$	6	4
B	Bushing	$\emptyset$	10	7
C		L	9.5	3/8
J	Lead versions X.. Y..		7	0.278
	K		11.1	0.436
G	Panel		8.2	0.323
H	Cutout	$\emptyset$	10.5	7.5
	Thread		0.75	32 thread/inch
	Wrench nut		12	0.500

**Note**

- Hardware supplied in separate bags

**ORDERING INFORMATION** (part number)

P	1	1	L	2	F	A	G	O	S	Y	0	0	5	0	2	K	A
MODEL	NUMBER OF MODULES		BUSHING		LOCATING PEG				SHAFT		SHAFT STYLE		LEADS		RESISTANCE CODE/TOLERANCE/TAPER OR SPECIAL		
					A = B = C = 0 =	See table below											

**LOCATING PEGS** (anti-rotation lug)


The locating peg is provided by a plate mounted on the bushing and positioned by the module sides. Four set positions are available, clock face orientation: 12, 3, 6, 9.

All P11 bushings have a double flat. When panel mounting holes have been punched accordingly, an anti-rotation lug is not necessary.

Locating peg code C not available for bushing Q.

CODE	$\varnothing d$ (mm)	L (mm)	e (mm)
A	2	6.2	0.7
B	2	7.75	0.7
C	3.5	13.5	1.1

Locating pegs are supplied in separate bags with nuts and washers




ORDERING INFORMATION (part number)																																																						
P	1	1	L	2	F	A	G	O	S	Y	0	0	5	0	2	K	A																																					
MODEL	NUMBER OF MODULES		BUSHING		LOCATING PEG																																																	
<b>SHAFT</b>																																																						
<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="width: 10%;"></th><th style="width: 10%; text-align: center;">Ø</th><th style="width: 10%; text-align: center;">L</th></tr> </thead> <tbody> <tr><td>AP</td><td style="text-align: center;">Custom shaft</td><td></td></tr> <tr><td>EA</td><td style="text-align: center;">4</td><td style="text-align: center;">9.5</td></tr> <tr><td>EB</td><td style="text-align: center;">4</td><td style="text-align: center;">12.5</td></tr> <tr><td>EJ</td><td style="text-align: center;">4</td><td style="text-align: center;">22</td></tr> <tr><td>FG</td><td style="text-align: center;">6</td><td style="text-align: center;">16</td></tr> <tr><td>FL</td><td style="text-align: center;">6</td><td style="text-align: center;">25</td></tr> <tr><td>FR</td><td style="text-align: center;">6</td><td style="text-align: center;">50</td></tr> <tr><td>GG</td><td style="text-align: center;">1/4"</td><td style="text-align: center;">5/8"</td></tr> <tr><td>GH</td><td style="text-align: center;">1/4"</td><td style="text-align: center;">3/4"</td></tr> <tr><td>GJ</td><td style="text-align: center;">1/4"</td><td style="text-align: center;">7/8"</td></tr> <tr><td>GL</td><td style="text-align: center;">1/4"</td><td style="text-align: center;">1"</td></tr> <tr><td>GO</td><td style="text-align: center;">1/4"</td><td style="text-align: center;">1.5"</td></tr> </tbody> </table>																	Ø	L	AP	Custom shaft		EA	4	9.5	EB	4	12.5	EJ	4	22	FG	6	16	FL	6	25	FR	6	50	GG	1/4"	5/8"	GH	1/4"	3/4"	GJ	1/4"	7/8"	GL	1/4"	1"	GO	1/4"	1.5"
	Ø	L																																																				
AP	Custom shaft																																																					
EA	4	9.5																																																				
EB	4	12.5																																																				
EJ	4	22																																																				
FG	6	16																																																				
FL	6	25																																																				
FR	6	50																																																				
GG	1/4"	5/8"																																																				
GH	1/4"	3/4"																																																				
GJ	1/4"	7/8"																																																				
GL	1/4"	1"																																																				
GO	1/4"	1.5"																																																				
<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="width: 10%;"></th><th style="width: 10%; text-align: center;">SHAFT STYLE</th><th style="width: 10%; text-align: center;">LEADS</th><th style="width: 10%; text-align: center;">RESISTANCE CODE/ TOLERANCE/ TAPER OR SPECIAL</th></tr> </thead> <tbody> <tr><td>S</td><td style="text-align: center;">Slotted</td><td></td><td></td></tr> <tr><td>R</td><td style="text-align: center;">Round</td><td></td><td></td></tr> <tr><td>F</td><td style="text-align: center;">Flattened</td><td></td><td></td></tr> <tr><td>D</td><td style="text-align: center;">Custom</td><td></td><td></td></tr> </tbody> </table>																		SHAFT STYLE	LEADS	RESISTANCE CODE/ TOLERANCE/ TAPER OR SPECIAL	S	Slotted			R	Round			F	Flattened			D	Custom																				
	SHAFT STYLE	LEADS	RESISTANCE CODE/ TOLERANCE/ TAPER OR SPECIAL																																																			
S	Slotted																																																					
R	Round																																																					
F	Flattened																																																					
D	Custom																																																					

### SHAFTS - Dimensions in millimeters (inches)


The shaft length is always measured from the mounting face.  
Standard shafts are designed by a 3 letters code (3 digits).  
Shafts slots are aligned to  $\pm 10^\circ$  of the wiper position.  
All standard shafts are slotted except flattened and splined, see exceptions for bushing.

#### FLATTED SHAFT

Bushing: F  
Shaft: GHF



#### SPLINED SHAFT



#### CUSTOM SHAFTS

When special shafts are required - flat, threaded ends, special shaft lengths, etc. a drawing is required.

### STANDARD COMBINATION OF SHAFT STYLES AND BUSHINGS

SHAFT DIA.	BUSHING CODE	SHAFT LENGTH AND STYLE AVAILABLE IN STANDARD (others on request)					
6	V	FGS	FLS	FRS			
6.35	F	GGS	GHS	GJS	GLS	GOS	GHF
4	Q	EAS	EBS	EJS	FHK		

**ORDERING INFORMATION** (part number)







P	1	1	L	2	F	A	G	O	S	Y	0	0	5	0	2	K	A		
MODEL	NUMBER OF MODULES		BUSHING		LOCATING PEG		SHAFT		SHAFT STYLE	<b>LEADS</b>									
										Available leads									
										A00	W00	X00	Y00	Z00			RESISTANCE CODE/ TOLERANCE/ TAPER OR SPECIAL		
										A10	W10	X03	Y03	Z03					
										A13	W20	X04	Y04	Z04					
										A14		X10		Z10					
										A20		X13		Z13					
										A23		X14		Z14					
										A24		X20		Z20					
												X23		Z23					
												X24		Z24					

FIRST DIGIT	
<b>Y</b>	Soldering lugs
<b>X</b>	PCB pins
<b>Z</b>	PCB pins with front support plate
<b>A</b>	PCB pins with front and back support plates
<b>W</b>	PCB pins - vertical mounting with 2 extra pins - 1 module only

SECOND DIGIT	
<b>0</b>	Y = 4.65 (0.183") A, X, Z, W = 5.08 (0.200") pin spacing pins section 0.9 x 0.3 (0.035" x 0.012")
<b>1</b>	2.54 (0.100") pin spacing pin section 0.6 x 0.3 (0.024" x 0.012")
<b>2</b>	5.08 (0.200") pin spacing pins section 0.6 x 0.3 (0.024" x 0.012")

THIRD DIGIT	
<b>0</b>	5.08 (0.200") space between modules
<b>3</b>	7.62 (0.300") space between modules
<b>4</b>	10.16 (0.400") space between modules

**DIMENSIONS** in millimeters (inches)  $\pm 0.5$  mm ( $\pm 0.02$ )


SOLDER LUGS Y		PCB PIN OUT	
			
HORIZONTAL MOUNTING			
FRONT AND REAR SUPPORT PLATES			
 Rear support plate E F A/A2 A1 1 3.81 (0.150) 2 3.81 (0.150) 3 3.81 (0.150)			
FRONT SUPPORT PLATE			
 Z Z1 Z2 1 5.08 (0.200) 2 2.54 (0.100) 3 5.08 (0.200) 4 3.81 (0.150) 5 3.81 (0.150)			
VERTICAL MOUNTING			
 A B C D E F W-W2 W1 1 12.7 (0.500) 2 4 (0.157) 3 12.7 (0.500) 4 12.7 (0.500) 5 5.08 (0.200) 6 2.54 (0.100)			


**THE POSITION OF EACH MODULE IS FREE**

BUSHINGS	MILLIMETERS ( $\pm 0.5$ )		INCHES ( $\pm 0.02$ )
	V	Q	
E Leads Z00	3.85	1.85	0.150
E Leads Z1. Z2. A..	3.6	1.6	0.140
F	Leads Z0: 5.08 (0.200")		Leads A..Z1, Z2: 3.81 (0.150")
J Leads X..Y..	7	5	0.278

ORDERING INFORMATION (part number)																	
P	1	1	L	2	F	A	G	O	S	Y	0	0	5	0	2	K	A
MODEL	NUMBER OF MODULES	BUSHING	LOCATING PEG	SHAFT	SHAFT STYLE	LEADS	RESISTANCE CODE/ TOLERANCE/ TAPER OR SPECIAL										
Resistance code: 1K = 102 5K = 502 10K = 103 50K = 503  Tolerance code: Standard: M = $\pm 20\%$ On request: K = $\pm 10\%$ , J = $\pm 5\%$  Taper: A, L, F or special code given by Vishay																	

SPECIAL CODES GIVEN BY VISHAY
Option available:
<ul style="list-style-type: none"> <li>Custom shaft</li> <li>Specific design on request</li> <li>Specific linearity</li> <li>Multiple assemblies with various modules</li> </ul>

APPLICATION NOTE
<p>The potentiometer shall be used in voltage divider with an impedance load at least 100 times higher than the total potentiometer nominal resistance value.</p> <p>Advised load impedance:            1 M<math>\Omega</math> min. for resistance range of 1 k<math>\Omega</math> to 50 k<math>\Omega</math></p> 

**P11L OPTION: ROTARY SWITCH MODULES**


- Rotary switches
- Current up to 2 A
- Actuation CW or CCW position
- Sealing IP60

**MODULES: RS ON/OFF SWITCH  
RSI CHANGEOVER SWITCH**

The position of each module is free.

RS and RSI rotary switches are housed in a standard P11L module size 12.7 mm x 12.7 mm x 5.08 mm (0.5" x 0.5" x 0.2"). They have the same terminal styles as the assembled electrical modules.

An assembly can comprise 1 or more switch modules.

Switch actuation is described as seen from the shaft end.

D: Means actuation in maximum CCW position

F: Means actuation in maximum CW position

The switch actuation travel is 25° with a total mechanical travel of 300° ± 5° and electrical travel of electrical modules is 238° ± 10°.

Leads finish: Gold plated

**RDS SINGLE POLE SWITCH, NORMALLY OPEN**

In full CCW position, the contact between 1 and 3 is open. It is made at the beginning of the travel in CW direction.

**RSF SINGLE POLE SWITCH, NORMALLY OPEN**

In full CW position, the contact between 1 and 3 is open. It is made at the beginning of the travel in CCW direction.

**RSID SINGLE POLE CHANGEOVER**

In full CCW position, the contact is made between 3 and 2 and open between 3 and 1. Switch actuation (CW direction) reverses these positions.

**RSIF SINGLE POLE CHANGEOVER**

In full CW position, the contact is made between 1 and 2 and open between 1 and 3. Switch actuation (CCW direction) reverses these positions.

**ORDERING INFORMATION (First order only)**
**RSID**
**RSD**

SPST: Single pole, open switch in CCW position - 2 pins

**RSF**

SPST: Single pole, open switch in CW position - 2 pins

**RSID**


SPDT: Single pole, changeover switch in CCW position - 3 pins

**RSIF**

SPDT: Single pole, changeover switch in CW position - 3 pins

**SWITCH SPECIFICATIONS**

Switching Power Maximum	0.5 VA =	
Switching Current Maximum	0.1 A, 5 V =	
Maximum Current Through Element	2 A	
Contact Resistance	100 mΩ	
Dielectric Strength	Terminal to Terminal	1000 V <sub>RMS</sub>
	Terminal to Bushing	2000 V <sub>RMS</sub>
Maximum Voltage Operation	5 V =	
Insulation Resistance Between Contacts	10 <sup>6</sup> MΩ	
Life at P <sub>max.</sub>	100 000 actuations	
Minimal Travel	25°	
Operating Temperature	- 40 °C to + 85 °C	

**ELECTRICAL DIAGRAM**

**Note**

(1) Common


### P11L OPTION: DETENT MODULES

The detents mechanism is housed in a standard P11L module.  
Up to 21 detent positions available.

Count detents as follows: 1 for CCW position, 1 for full CW position, plus the other positions forming equal resistance increments (linear taper) - not equal angles.

Available: CVID - CVIF - CVIM  
CV3 - CV11 - CV21

Mechanical endurance: 50 000 cycles



#### ORDERING INFORMATION (First order only for special code creation)

**CV1M**

<b>CV1M</b>	1 detent at half travel
<b>CV1D</b>	1 detent at CCW position
<b>CV1F</b>	1 detent at CW position
<b>CV3</b>	3 detents
<b>CV11</b>	11 detents
<b>CV21</b>	21 detents

### P11L OPTION: NEUTRAL MODULES "EN"

Neutral or screen module is housed in a standard P11L module.  
It is used as a screen between two electrical modules.


The leads can be connected to ground.

#### ORDERING INFORMATION (First order only for special code creation)

**EN**

<b>EN</b>	Neutral module
-----------	----------------

### P11L OPTION: SPECIAL LINEARITY - CONFORMITY



The independent linearity (conformity for the non-linear laws) is the maximum gap  $\Delta V$  between the actual variation curve and the theoretical variation curve the nearest to it. The linearity and the conformity are expressed in percentage of the total applied voltage E

$$\text{linearity conformity} = \frac{\pm \Delta V_{\max.}}{E}$$

They are measured over 90 % of actual electrical travel (centered).


On request linearity can be guaranteed in linear taper.

#### ORDERING INFORMATION (First order only)

**J123**

<b>J123</b>	Independent linearity $\pm 3\%$ (linear law)
<b>J145</b>	Independent linearity $\pm 2\%$ (linear law)

For other request, contact us.

**EXAMPLES OF FIRST ORDER INFORMATION**
**FIRST EXAMPLE: Triple module (switch is counted as a module)**

**ORDERING INFORMATION:**

PART NUMBER	P11L3VAFGSY00.....	
SHAFT AND BUSHING	See drawing of special shaft attached	
MODULE NO. 1	503 M A	
MODULE NO. 2	103 M A	J123
MODULE NO. 3	503 M A	

**PART NUMBER DESCRIPTION** (used on some Vishay document or label, for information only)

P11L	3	V	A	FG	S	Y00			T1927		e3
MODEL	MODULES	BUSHING	LOCATING PEG	SHAFT	SHAFT STYLE	LEADS	VALUE	TOL.	TAPER	SPECIAL	LEAD (Pb)-FREE

## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## Material Category Policy

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.**

**Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.**

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.**