

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION

BELDEN
SENDING ALL THE RIGHT SIGNALS

1310A Multi-Conductor - Speaker Cable



For more Information
please call

1-800-Belden1



General Description:

14 AWG stranded (105x34) oxygen-free high-conductivity bare copper OFC conductors, PO insulation, conductors cabled, PVC jacket. Sequential footage marking every two feet.

Usage (Overall)

Suitable Applications: Speaker Cable, Direct Burial, Indoor/Outdoor Home Theater, In-Wall Speaker, Outdoor Speaker

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material	Dia. (in.)
4	14	105x34	High Conductivity BC - Bare Copper	.074

Total Number of Conductors: 4

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
PO - Polyolefin	.105

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	Red
3	White
4	Green

Overall Nominal Diameter: 0.319 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +75°C

UL Temperature Rating: 75°C

Bulk Cable Weight: 79 lbs/1000 ft.

Max. Recommended Pulling Tension: 208 lbs.

Min. Bend Radius/Minor Axis: 3.250 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CL3, CM

CEC/C(UL) Specification: CM

EU Directive 2011/65/EU (ROHS II): Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 07/01/2005

EU Directive 2002/96/EC (WEEE): Yes

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

1310A Multi-Conductor - Speaker Cable

EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1581 Vertical Flame and FT-1 Flame Test
CSA Flame Test:	FT1

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	6102UE

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (μH/ft)
.16

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
20.5

Nominal Velocity of Propagation:

VP (%)
66

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
2.5

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
13 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1310A 006U500	500 FT	41.500 LB	BLUE, LIGHT		4 #14 PE FRPVC
1310A 008U500	500 FT	41.500 LB	GRAY		4 #14 PE FRPVC
1310A 0081000	1,000 FT	84.000 LB	GRAY	C	4 #14 PE FRPVC
1310A 010U500	500 FT	41.500 LB	BLACK		4 #14 PE FRPVC
1310A 0101000	1,000 FT	84.000 LB	BLACK	C	4 #14 PE FRPVC
1310A 1SLU500	500 FT	41.500 LB	WHITE 1SL		4 #14 PE FRPVC
1310A 1SL1000	1,000 FT	84.000 LB	WHITE 1SL	C	4 #14 PE FRPVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 11-06-2013

© 2014 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Belden Wire & Cable:

[1189A 009U500](#) [1310A 006U500](#) [1310A 008U500](#) [1310A 0081000](#) [1310A 010U500](#) [1310A 0101000](#) [1310A 1SLU500](#) [1310A 1SL1000](#)