





**MARKETING SALES DRAWING**  
**DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING**  
**DIMENSIONS IN METRIC - [ ]**


## Electrical Testing per Tucsonix standard test plans and Mil-Std-202 Test Methods.



## MOUNTING HARDWARE



## LOCK WASHER



## HEX NUT

## NOTES:

1. TUSONIX STANDARD PART NUMBER: 4601-050.  
TUSONIX RoHS COMPLIANT PART NUMBER: 4601-050 LF.  
CUSTOMER MUST SPECIFY STANDARD OR RoHS  
PART NUMBER WHEN ORDERING.
2. MATERIALS: BUSHING - TIN PLATED STEEL.  
TOP SEAL FINISH: STANDARD PART #: 60/40 SOLDER PLATED.  
RoHS PART #: MATTE TIN PLATED.  
LEAD STANDARD PART: SILVER PLATED COPPER.  
NUT - TIN PLATED BRASS.  
L"WASHER - TIN PLATED PHOSPHOR BRONZE.
3. PART MARKING: TRADEMARK AND VARIATION NUMBER.  
STANDARD PART: BLACK INK. RoHS PART: GREEN INK.
4. MOUNTING TORQUE: 8 lb - ins. max.
5. SEAL TESTED PER MIL-STD-202 METHOD 112 CONDITION A.
6. DCR - .01 max.
7. MAX. SOLDER TEMPERATURE 500°F.

MIN. CAP. ( F)	WORKING VOLTAGE DC		CURRENT D.C.	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD-220					
	85°C	125°C		30 KHz	100 KHz	300 KHz	1 MHz	10 MHz	1 GHz
1.4	100	70	15 A	15	25	34	44	60	70

**--TOLERANCES--**  
Unless Otherwise  
Specified

DECIMAL ±

IGLES ±

Title **COAXIAL  
BROADBAND - "L"  
HERMETICALLY SEALED**

Drawn **S.M. 12-22-97** Scale **X 3**

Approved J.Mc 12-22-97

# **TUSONIX**

TUCSON, ARIZONA

A

4601-050

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Tusonix:

[4601-050LF](#)