

Features


Mono-function and multi-function timer range
22.5 mm wide

87.01 - 1 Pole - Multi-function and multi-voltage
87.02 - 2 Pole - Multi-function and multi-voltage, (timed + instantaneous options)

External time setting potentiometer option

- Wide supply voltage range:
(24...240)V AC / (24...48)V DC
- LED indicator
- Time setting from 0.05 seconds to 60 hours
- 35 mm rail (EN 60715) mount

87.01 / 87.02
Screw terminal



87.01




- Multi-function
- 1 pole
- 35 mm rail (EN 60715) mount

87.02




- Multi-function
- Timing can be regulated using ext. Potentiometer
- 2 timed contacts or 1 timed + 1 instantaneous contact
- 35 mm rail (EN 60715) mount

AI: ON delay
BE: Signal OFF delay
CE: Signal ON and OFF Delay
DE: Signal ON pulse
DI: ON pulse
EE a: Signal OFF pulse
GI: Fixed pulse delayed
SW: Symmetrical recycling: ON start




Wiring diagram
(without signal START)




Wiring diagram
(with signal START)

AI: ON delay
BE: Signal OFF delay
CE: Signal ON and OFF Delay
DE: Signal ON pulse
DI: ON pulse
EE a: Signal OFF pulse
GI: Fixed pulse delayed
SW: Symmetrical recycling: ON start



Wiring diagram
(without signal START)



Wiring diagram
(with signal START)

Contact specification

Contact configuration

1 CO (SPDT)

2 CO (DPDT)

Rated current/Maximum peak current A

8/30

8/30

Rated voltage/Maximum switching voltage V AC

250/400

250/400

Rated load AC1 VA

2,000

2,000

Rated load AC15 (230 V AC) VA

400

400

Single phase motor rating (230 V AC) kW

0.185

0.185

Breaking capacity DC1: 30/110/220 V A

8/0.5/0.2

8/0.5/0.2

Minimum switching load mW (V/mA)

300 (10/5)

300 (10/5)

Standard contact material

AgCdO

AgCdO

Supply specification

Nominal voltage (U_N) V AC (50/60 Hz)

24...240

24...240

V DC

24...48

24...48

Rated power AC/DC VA (50 Hz)/W

5/0.5

5/0.5

Operating range AC

(0.85...1.1) U_N

(0.85...1.1) U_N

DC

(0.85...1.2) U_N

(0.85...1.2) U_N

Technical data

Specified time range

See page 6

See page 6

Repeatability %

± 2

± 2

Recovery time ms

50

50

Minimum control impulse ms

50

50

Setting accuracy-full range %

± 5

± 5

Electrical life at rated load in AC1 cycles

100·10³

100·10³

Ambient temperature range (Contact current) °C

-20...+70

-20...+60 / -20...+70 (< 5 A)

Protection category

IP 20

IP 20

Approvals (according to type)



Features

Mono-function and multi-function timer range
22.5 mm wide


87.11 - ON delay, multi-voltage

87.21 - ON pulse, multi-voltage

87.31 - Symmetrical recycling, multi-voltage

- 1 Pole output contact
- Wide supply voltage range:
(24...240)V AC / (24...48)V DC
- LED indicator
- Time setting:
Types 87.11/21 - 0.05 seconds to 60 hours
Type 87.31 - 0.5 seconds to 10 seconds
- 35 mm rail (EN 60715) mount

87.11 / 87.21 / 87.31
Screw terminal



87.11



87.21



87.31




- Mono-function
- 35 mm rail (EN 60715) mount

- Mono-function
- 35 mm rail (EN 60715) mount


- Mono-function
- 35 mm rail (EN 60715) mount

AI: ON delay




Wiring diagram
(without signal START)

DI: ON pulse



Wiring diagram
(without signal START)

SW: Symmetrical recycling: ON start



Wiring diagram
(without signal START)

Contact specification

Contact configuration

1 CO (SPDT)

1 CO (SPDT)

1 CO (SPDT)

Rated current/Maximum peak current A

8/30

8/30

8/30

Rated voltage/Maximum switching voltage V AC

250/400

250/400

250/400

Rated load AC1

2,000

2,000

2,000

Rated load AC15 (230 V AC)

400

400

400

Single phase motor rating (230 V AC) kW

0.185

0.185

0.185

Breaking capacity DC1: 30/110/220 V A

8/0.5/0.2

8/0.5/0.2

8/0.5/0.2

Minimum switching load mW (V/mA)

300 (10/5)

300 (10/5)

300 (10/5)

Standard contact material

AgCdO

AgCdO

AgCdO

Supply specification

Nominal voltage (U_N) V AC (50/60 Hz)

24...240

24...240

24...240

V DC

24...48

24...48

24...48

Rated power AC/DC VA (50 Hz)/W

5/0.5

5/0.5

5/0.5

Operating range AC

(0.85...1.1) U_N

(0.85...1.1) U_N

(0.85...1.1) U_N

DC

(0.85...1.2) U_N

(0.85...1.2) U_N

(0.85...1.2) U_N

Technical data

Specified time range

See page 6

See page 6

See page 6

Repeatability %

± 0.2

± 0.2

± 0.2

Recovery time ms

50

50

50

Minimum control impulse ms

—

—

—

Setting accuracy-full range %

± 5

± 5

± 5

Electrical life at rated load in AC1 cycles

100 · 10³

100 · 10³

100 · 10³

Ambient temperature range °C

-20...+70

-20...+70

-20...+70

Protection category

IP 20

IP 20

IP 20

Approvals (according to type)




Features

Mono-function and multi-function timer range
22.5 mm wide

87.41 - Signal OFF delay, multi-voltage, 1 Pole
87.61 - True OFF delay, multi-voltage, 1 Pole
87.62 - True OFF delay, multi-voltage, 2 Pole

- Wide supply voltage range:
Type 87.41, (24...240)V AC/(24...48)V DC
Types 87.61/62, (24...240)V AC/DC
- LED indicator
- Time setting range:
Type 87.41 - 0.05 seconds to 60 hours
Types 87.61/62 - 0.15 seconds to 10 minutes
- 35 mm rail (EN 60715) mount

87.41 / 87.61 / 87.62
Screw terminal



87.41



- Mono-function
- 1 pole
- 35 mm rail (EN 60715) mount

87.61




- Mono-function
- 1 pole
- 35 mm rail (EN 60715) mount

87.62




- Mono-function
- 2 pole
- 35 mm rail (EN 60715) mount

BE: Signal OFF delay




Wiring diagram
(with signal START)

BI: True OFF delay



Wiring diagram
(without signal START)

BI: True OFF delay



Wiring diagram
(without signal START)

Contact specification

Contact configuration	1 CO (SPDT)	1 CO (SPDT)	2 CO (DPDT)
Rated current/Maximum peak current A	8/30	5/10	5/10
Rated voltage/Maximum switching voltage V AC	250/400	250/400	250/400
Rated load AC1 VA	2,000	1,250	1,250
Rated load AC15 (230 V AC) VA	400	250	250
Single phase motor rating (230 V AC) kW	0.185	0.125	0.125
Breaking capacity DC1: 30/110/220 V A	8/0.5/0.2	5/0.5/0.2	5/0.5/0.2
Minimum switching load mW (V/mA)	300 (10/5)	300 (10/5)	300 (10/5)
Standard contact material	AgCdO	AgCdO	AgCdO

Supply specification

Nominal voltage (U _N)	V AC (50/60 Hz)	24...240	24...240	24...240
	V DC	24...48	24...240	24...240
Rated power AC/DC	VA (50 Hz)/W	5/0.5	1.5/1.5	1.5/1.5
Operating range	AC	(0.85...1.1)U _N	(0.85...1.1)U _N	(0.85...1.1)U _N
	DC	(0.85...1.2)U _N	(0.85...1.2)U _N	(0.85...1.2)U _N

Technical data

Specified time range	See page 6	See page 6	See page 6
Repeatability %	± 0.2	± 1	± 1
Recovery time ms	50	200	200
Minimum control impulse ms	50	800 ms (A1 - A2)	800 ms (A1 - A2)
Setting accuracy-full range %	± 5	± 5	± 5
Electrical life at rated load in AC1 cycles	100 · 10 ³	100 · 10 ³	100 · 10 ³
Ambient temperature range °C	-20...+70	-20...+70	-20...+70
Protection category	IP 20	IP 20	IP 20
Approvals (according to type)	   	  	

Features


Mono-function and multi-function timer range
22.5 mm wide

87.82 - Star-Delta timer, multi-voltage, star and delta output contacts

87.91 - Multi-function Recycling timer, 1 Pole

- Wide supply range: (24...240)V AC / (24...48)V DC
- LED indicator
- Time setting voltage range: Type 87.82 - 0.05 minute to 1 minute
 Type 87.91 - 0.05 seconds to 60 hours
- 35 mm rail (EN 60715) mount

87.82 / 87.91
 Screw terminal



87.82




- Mono-function: Star - delta
- 2 pole
- 35 mm rail (EN 60715) mount

87.91




- Multi-function recycling
- 1 pole
- 35 mm rail (EN 60715) mount

SD: Star - delta




Wiring diagram
 (without signal START)

LI: Asymmetrical recycling (ON starting)
LE: Signal asymmetrical recycling (ON starting)
PI: Asymmetrical recycling (OFF starting)
PE: Signal asymmetrical recycling (OFF starting)



Wiring diagram
 (without signal START)



Wiring diagram
 (with signal START)

Contact specification

Contact configuration

	2 NO (DPST-NO)	1 CO (SPDT)
Rated current/Maximum peak current A	8/30	8/30
Rated voltage/Maximum switching voltage V AC	250/400	250/400
Rated load AC1 VA	2,000	2,000
Rated load AC15 (230 V AC) VA	400	400
Single phase motor rating (230 V AC) kW	0.185	0.185
Breaking capacity DC1: 30/110/220 V A	8/0.5/0.2	8/0.5/0.2
Minimum switching load mW (V/mA)	300 (10/5)	300 (10/5)
Standard contact material	AgCdO	AgCdO

Supply specification

Nominal voltage (U_N) V AC (50/60 Hz)	24...240	24...240
	24...48	24...48
Rated power AC/DC VA (50 Hz)/W	5/0.5	5/0.5
Operating range AC	$(0.85...1.1)U_N$	$(0.85...1.1)U_N$
	$(0.85...1.2)U_N$	$(0.85...1.2)U_N$

Technical data

Specified time range	See page 6	See page 6
Repeatability %	± 0.2	± 0.2
Recovery time ms	50	50
Minimum control impulse ms	—	50
Setting accuracy-full range %	± 5	± 5
Electrical life at rated load in AC1 cycles	$100 \cdot 10^3$	$100 \cdot 10^3$
Ambient temperature range °C	-20...+70	-20...+70
Protection category	IP 20	IP 20
Approvals (according to type)	   	

Ordering information

Example: 87 series multi-function timer 8 A, 1 CO (SPDT) contact, (24...240)V AC (50/60 Hz) and (24...48)V DC supply.

8 7 . 0 1 . 0 . 2 4 0 . 0 0 0 0

Series _____

Type _____

- 0 = Multi-function
(AI, BE, CE, DI, DE, EE a, GI, SW, ON, OFF)
- 1 = ON delay (AI)
- 2 = ON pulse (DI)
- 3 = Symmetrical recycling: ON start (SW)
- 4 = Signal OFF delay (BE)
- 6 = True OFF delay (power OFF) (BI)
- 8 = Star - delta (SD)
- 9 = Asymmetrical recycling (LI, LE, PI, PE)

Supply voltage

- 240 = { (24...48)V DC
(24...240)V AC}
- 240 = (24...240)V AC/DC for 87.61 and 87.62

Supply version

- 0 = AC (50/60 Hz)/DC

No. of poles

- 1 = 1 pole
- 2 = 2 pole for 87.02/62
- 2 = 2 NO (DPST-NO) for 87.82

Technical data

Insulation

Dielectric strength	between input and output circuit	V AC	4,000
	insulation (1.2/50 µs) between input and output	kV	6
	between open contacts	V AC	1,000
	between adjacent contacts	V AC	2,000 (Type 87.02, 87.62)

EMC specifications

Type of test	Reference standard		
Electrostatic discharge	contact discharge	EN 61000-4-2	8 kV
	air discharge	EN 61000-4-2	8 kV
Radio-frequency electromagnetic field (80 ÷ 1000 MHz)		EN 61000-4-3	10 V/m
Fast transients (burst) (5-50 ns, 5 kHz) on Supply terminals		EN 61000-4-4	6 kV
Surges (1.2/50 µs) on Supply terminals	common mode	EN 61000-4-5	4 kV
	differential mode	EN 61000-4-5	4 kV
Radio-frequency common mode (0.15 ÷ 80 MHz) on Supply terminals		EN 61000-4-6	10 V
Radiated and conducted emission		EN 55022	class B

Other data

Signal control (B1)			
- current absorption	1 mA		
- max cable length (capacity of ≤ 10 nF / 100 m)	250 m		
- when applying a control signal to B1, which is different from the supply voltage at A1/A2	B1 is isolated from A1 and A2 by an opto-coupler, and can therefore be operated at a voltage other than the supply voltage		

Note: when applying a control signal to B1 it is recommended to attach a bypass resistance 56 kOhm/2 W across B1 - A2

If using a control signal of between (24... 48)V DC and a supply voltage of (24...240)V AC; ensure that the signal – is connected to A2 and the + is applied to B1, and that L is applied to B1 and N to A2

External potentiometer for 87.02	Use a 10 kΩ/≥ 0,25 W linear potentiometer. Maximum cable length 10 m. When using an external potentiometer, remove the bridge between Z1 and Z2, and set the timer'spotentiometer to its minimum setting. Consider the voltage potential at the potentiometer to be the same as the timer supply voltage.		
----------------------------------	---	--	--

Power lost to the environment	87.01/02/11/21/31/41/91	87.61/62	87.82
without contact current	W 5	1.5	8
with rated current	W 15	7	18

Screw torque	Nm	1.2	
Max. wire size		solid cable	stranded cable
	mm²	1x4 / 2x2.5	1x4 / 2x1.5
	AWG	1x12 / 2x14	1x12 / 2x16

Time scales

Type	Function Code	Function	Time ranges - minimum to maximum span									
			s	s	s	min	min	min	h	h	h	h
			0.05	0.15	0.5	0.05	0.15	0.5	0.05	0.15	0.5	3
			1	3	10	1	3	10	1	3	10	60
87.01	AI	ON delay	•	•	•	•	•	•	•	•	•	•
	BE	Signal OFF delay	•	•	•	•	•	•	•	•	•	•
	CE	Signal ON and OFF delay	•	•	•	•	•	•	•	•	•	•
	DI	ON pulse	•	•	•	•	•	•	•	•	•	•
	DE	Signal ON pulse	•	•	•	•	•	•	•	•	•	•
	EE a	Signal OFF pulse	•	•	•	•	•	•	•	•	•	•
	GI	Fixed pulse (0.5s) delayed	•	•	•	•	•	•	•	•	•	•
	SW	Symmetrical recycling: ON start	•	•	•	•	•	•	•	•	•	•
87.11	AI	ON delay	•	•	•	•	•	•	•	•	•	•
87.21	DI	ON pulse	•	•	•	•	•	•	•	•	•	•
87.31	SW	Symmetrical recycling: ON start			•							
87.41	BE	Signal OFF delay	•	•	•	•	•	•	•	•	•	•
87.61	BI	True OFF delay (power OFF)		0.15	•	0.07			•			
87.62				2.5		1.3						
87.82	SD	Star - delta ($T_U = \sim 60$ ms)				•						
87.91	LI	Asymmetrical recycling (ON start)	•	•	•	•	•	•	•	•	•	•
	LE	Signal asymmetrical recycling (ON start)	•	•	•	•	•	•	•	•	•	•
	PI	Asymmetrical recycling (OFF start)	•	•	•	•	•	•	•	•	•	•
	PE	Signal asymmetrical recycling (OFF start)	•	•	•	•	•	•	•	•	•	•

Functions

U = Supply Voltage

S = Signal switch

C = Output Contact


LED** Green	Timing	NO output contact	Contacts Timed		DIP switch	Contacts Instantaneous*	
			Open	Closed		Open	Closed
	None	Open	15 - 18 25 - 28*	15 - 16 25 - 26*	Up	21 - 24*	21 - 22*
	In progress	Open	15 - 18 25 - 28*	15 - 16 25 - 26*		21 - 22*	21 - 24*
	In progress	Closed	15 - 16 25 - 26*	15 - 18 25 - 28*		21 - 22*	21 - 24*
	None	Closed	15 - 16 25 - 26*	15 - 18 25 - 28*	Down	21 - 22*	21 - 24*

* 25-26-28 only for type 87.02 with 2 timed contacts. 21-22-24 only for type 87.02 with 1 instantaneous contact + 1 timed positioning the front DIP switch.

** The LED on types 87.61 and 87.62 is illuminated when supply voltage is supplied to timer.

Wiring diagram


Multi-function
without signal START




Type
87.01
87.02

87.01
87.02

with signal START



87.01
87.02



87.01
87.02

* A voltage other than the supply voltage can be applied to the command START (B1). Example:

A1 - A2 = 230 V AC
B1 - A2 = 24 V AC

** Type 87.02: regulated using an external potentiometer (10 kΩ - 0.25 W).

NB.: remove link between Z1-Z2 and position the Timer potentiometer on "zero".

(AI) ON delay.

Apply power to timer. Output contacts transfer after preset time has elapsed. Reset occurs when power is removed.

(DI) ON pulse.

Apply power to timer. Output contacts transfer immediately. After the preset time has elapsed, contacts reset.

(GI) Fixed pulse (0.5s) delayed.

Apply power to timer. Output contacts transfer after preset time has elapsed. Reset occurs after a fixed time of 0.5s.

(SW) Symmetrical recycling: ON start.

Apply power to timer. Output contacts transfer immediately and cycle between ON and OFF for as long as power is applied. The ratio is 1:1 (time on = time off).

(BE) Signal OFF delay.

Power is permanently applied to the timer. The output contacts transfer immediately on closure of the Signal Switch (S). Opening the Signal Switch initiates the preset delay, after which time the output contacts reset.

(CE) Signal ON and OFF delay.

Power is permanently applied to the timer. Closing the Signal Switch (S) initiates the preset delay, after which time the output contacts transfer. Opening the Signal switch initiates the same preset delay, after which time the output contacts reset.

(DE) Signal ON pulse.

Power is permanently applied to the timer. On momentary or maintained closure of Signal Switch (S), the output contacts transfer, and remain so for the duration of the preset delay, after which they reset.

(EE a) Signal OFF pulse.

Power is permanently applied to the timer. On opening of the Signal Switch (S) the output contacts transfer, and remain so for the duration of the preset delay, after which they reset.

Permanently ON.

Selecting the function ON when power is applied to the relay the first contact transfers immediately and remains in that position.




Permanently OFF.

The contact returns to the original position when the OFF function is selected.


Functions

Wiring diagram


Mono-function
without signal START




with signal START (S)




Asymmetrical recycler
without signal START




with signal START (S)




Type
87.11



87.21




87.31




87.61




87.82




87.41



87.91




switch position



switch position



switch position



(AI) ON delay.

Apply power to timer. Output contacts transfer after preset time has elapsed. Reset occurs when power is removed.

(DI) ON pulse.

Apply power to timer. Output contacts transfer immediately. After the preset time has elapsed, contacts reset.

(SW) Symmetrical recycling: ON start.

Apply power to timer. Output contacts transfer immediately and cycle between ON and OFF for as long as power is applied. The ratio is 1:1 (time on = time off).

(BI) True OFF delay (power OFF).

Apply power to timer (minimum 300 ms). Output contacts transfer immediately. Removal of power initiates the preset delay, after which time the output contacts reset.

(SD) Star - delta.

Apply power to timer. The star contact (λ) closes immediately. After preset delay has elapsed the star contact (λ) resets. After a further fixed time of ~60 ms the delta contact (Δ) closes and remains in that position, until reset on power off.

(BE) Signal OFF delay.

Power is permanently applied to the timer. The output contacts transfer immediately on closure of the Signal Switch (S). Opening the Signal Switch initiates the preset delay, after which time the output contacts reset.

(LI) Asymmetrical recycling (ON start).

Apply power to timer. Output contacts transfer immediately and cycle between ON and OFF for as long as power is applied. The ON and OFF times are independently adjustable.

(PI) Asymmetrical recycling (OFF start).

Apply power to timer. Output contacts transfer after time T1 has elapsed and cycle between OFF and ON for as long as power is applied. The ON and OFF times are independently adjustable.

(IE) Signal asymmetrical recycling (ON start)

Power is permanently applied to the timer. Closing Signal Switch (S) causes the output contacts to transfer immediately and cycle between ON and OFF, until opened.

(PE) Signal asymmetrical recycling (OFF start).

Power is permanently applied to the timer. Closing the Signal Switch (S) initiates delay T1 after which the output contacts transfer and continue to cycle between OFF and ON, until the Signal Switch is opened.