


## 213437-3 Product Details

[Share](#) [Print](#) [Email](#)


213437-3

TE Internal Number: 213437-3

 **Active**

 [View 3D PDF](#)

### ARINC 404 Connectors

[Not EU RoHS or ELV Compliant](#)

#### Product Highlights:

- Sealed
- Seal Type = Interface seal on pin insert
- Shell Size = 2 Inserts
- Shell Configuration = Plug
- Contact Arrangement (Module A) = 33C4

[View all Features](#)

#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [PLUG CONNECTOR KIT, ARINC 404, DUAL INSERT, RM2P SERIES](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version E)
- [3D Model](#) (IGES, Version E)
- [3D Model](#) (STEP, Version E)

[List all Documents](#)

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Sealed](#) = Yes
- [Shell Size](#) = 2 Inserts
- Shell Finish = Cadmium plated per QQ-P-416 with yellow chromate conversion.

#### Mechanical Attachment:

- [Keying](#) = 01

#### Electrical Characteristics:

- Shell Configuration = Plug
- Signal Contacts = Without
- [Shell Mounting Modification](#) = 00
- [Custom Order Code](#) = 201

#### Termination Features:

- Seal Type = Interface seal on pin insert

#### Contact Features:

- Contact Type (Module A) = Socket
- Contact Type (Module B) = Socket

#### Configuration Features:

- [Contact Arrangement \(Module A\)](#) = 33C4
- [Contact Arrangement \(Module B\)](#) = C8

#### Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C

#### Other:

- Brand = AMP
- Comment = Contacts sold separately.

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

