





PART NO.  
20021111



- NOTES:
- 1.MATERIAL:  
HOUSING: HIGH TEMPERATURE THERMOPLASTIC, UL94-V0 BLACK.  
TERMINAL: COPPER ALLOY
  - 2.THE HOUSING WILL WITHSTAND EXPOSURE TO 260~C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER OR VAPOR PHASE REFLOW OVEN.
  - 3.THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
  - 4.PRODUCT SPEC: GS-12-629
  - 5.PACKAGE SPEC: GS-14-1420

|             |                |      |          |                                       |                               |                  |                               |
|-------------|----------------|------|----------|---------------------------------------|-------------------------------|------------------|-------------------------------|
| mat'l. code |                |      |          | surface<br>ISO 1302 ✓                 | tolerance<br>ISO 406 ISO 1101 | projection<br>mm | product family<br>MINITEK127® |
| ltr         | ecn no         | dr   | date     | tolerances unless otherwise specified |                               | mm               | title                         |
| E           | ELX-N-23548    | TIM  | 03/21/16 | angles                                | .0±.30                        |                  | UNSHROUDED HDR VT TH          |
| F           | ELX-N-25883    | TONY | 01/11/17 | linear                                | .00±.20                       |                  |                               |
| G           | ELX-N-27768    | TONY | 08/18/17 | 0°±2'                                 | .000±.10                      | scale 1:1        |                               |
|             |                |      |          | dr                                    | ZK HU                         | 09/28/12         | dwg no                        |
|             |                |      |          | enr                                   | ZK HU                         | 09/28/12         | sheet 1 of 2                  |
|             |                |      |          | chr                                   | BIAN RICK                     | 09/28/12         | size                          |
|             |                |      |          | appd                                  | BIAN RICK                     | 09/28/12         | A3                            |
| sheet index | revision sheet | G    | G        |                                       |                               |                  | type Product Customer Drawing |
|             |                | 1    | 2        |                                       |                               |                  |                               |

| PART NO.           | POS.   | DIM"X" | DIM"Y" |
|--------------------|--------|--------|--------|
| 20021111-XXX92XXLF | 2 X 46 | 58.42  | 57.15  |
| 20021111-XXX94XXLF | 2 X 47 | 59.69  | 58.42  |
| 20021111-XXX96XXLF | 2 X 48 | 60.96  | 59.69  |
| 20021111-XXX98XXLF | 2 X 49 | 62.23  | 60.96  |
| 20021111-XXXA0XXLF | 2 X 50 | 63.50  | 62.23  |

```

-LEAD FREE
-PLATING OPTIONAL
1: GOLD FLASH AT CONTACT, 127um MIN. MATTE TIN AT TAIL
2: GOLD FLASH AT CONTACT, GOLD FLASH AT TAIL
4: 0.25um Au MIN. AT CONTACT, 127um MIN.MATTE TIN AT TAIL
5: 0.25um Au MIN. AT CONTACT, GOLD FLASH AT TAIL
6: 0.38um GXT MIN. AT CONTACT, 127um MIN.MATTE TIN AT TAIL
7: 0.38um GXT MIN. AT CONTACT, GOLD FLASH AT TAIL
8: 0.76um GXT MIN. AT CONTACT, 127um MIN.MATTE TIN AT TAIL
9: 0.76um GXT MIN. AT CONTACT, GOLD FLASH AT TAIL

```

- PACKING STYLE
  - T: TUBE
  - Q: TAPE & REEL WITHOUT CAP
- PIN NO. SEE TABLE
- MATING LENGTH(DIM\*A\*)
  - 0: 3.05MM
- TAIL LENGTH(DIM\*B\*)
  - 0: 2.30MM (FOR 1.6MM PCB)
  - 1: 1.60MM (FOR 1.0MM PCB)
  - 2: 2.70MM (FOR 2.0MM PCB)
- RESERVE CODE
  - 0: STANDARD

[illegible]