







LOC	DIST	REVISIONS				
		REV	LTR	DESCRIPTION	DATE	APP'D
CM	53	AG2	REVISED	PER ECO-11-004587	11 MAR 11	RK HMR

D




1. MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK™ PLUG.
2. RECOMMENDED PANEL THICKNESS 0.76 - 2.29.
3. PANEL MUST BE PUNCHED SO THAT THE HOUSING ENTERS THE PANEL IN THE SAME DIRECTION AS THE PUNCH.
4. OPTIONAL FOR KEYING HOUSING IN PANEL.
5. CIRCUIT NUMBER 1 LOCATION.
6. DIMENSION INDICATED IS AS MOLDED. ADDITIONAL GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR.
7. FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION. NO RIBS OR SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, OPTIONAL.
8. UNDERWRITERS RECOGNIZED COMPONENT LOGO AND CSA CERTIFICATION LOGO TO BE LOCATED ONCE EACH ON SIDE OF HOUSING.
9. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

C



RECOMMENDED PANEL CUTOUT

B



3-DIMENSIONAL MODEL
NTS

4.45	.175	27.43	1.080
2.79	.110	14.35	.565
2.54	.100	13.97	.550
2.41	.095	13.46	.530
2.29	.090	13.21	.520
0.76	.030	8.64	.340
0.38	.015	8.13	.320
0.25	.010	7.62	.300
0.13	.005	6.35	.250
MM	IN	MM	IN

CONVERSION TABLE

9 SUPERSEDED BY 1-480699-0
9 OBSOLETE

BLACK	1-480699-9
GREY	1-480699-8
BLUE	1-480699-6
GREEN	1-480699-5
YELLOW	1-480699-4
ORANGE	1-480699-3
RED	1-480699-2
BROWN	1-480699-1
NATURAL	1-480699-0
COLOR	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 24JUL92	TE Connectivity	
DIMENSIONS: mm		CHK R. SWING 24JUL92	NAME CAP.2 CIRCUIT, UNIVERSAL MATE-N-LOK (TM)	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APP'D D. SELF 27JUL92	RESTRICTED TO	
0. PLC ± - 1. PLC ± - 2. PLC ± 0.13 3. PLC ± - 4. PLC ± - ANGLES ± 1° 0'		PRODUCT SPEC APPLICATION SPEC WEIGHT -	SIZE A1 00779	
MATERIAL NYLON,UL 94V-2		FINISH -	CUSTOMER DRAWING	
SCALE 4:1		SHEET 1 OF 1		REV AG2

METRIC