

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC

A1

DIST

—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	L2	OBSOLESCENCE OF P/N 1-826314-5	06SEP2013	SMT	RP

DIMENSIONS				PART NUMBER	
"B"	"D"	"C"	"F"	SEL. GOLD PLATED ^①	TIN PLATED ^②
6,7	1,5	3,2	4,4	825437	
6,7	4,0	5,7	4,4	825438	
6,7	6,6	8,3	4,4	825439 ^④	
4	4,0	6,7	4,0	826304 ^④	
5,8	1,5	3,2			826314

NOTES:

^① MATING SIDE AREA "F" 0.8µm GOLD OVER 1,27µm NICKEL
SOLDER SIDE AREA 2,5µm TIN OVER 1,27µm NICKEL

^② 2µm TIN OVER 1,27µm NICKEL

^③ TOLERANCE NOT CUMULATIVE

^④ OBSOLETE

^⑤ THE NO. OF POSITION PER ROW HAS TO BE ADDED TO BASE NO. AS A DASH NO.
EG. 2-825438-0 = 20 POSITIONS.

RECOMMENDED PCB LAYOUT

2.54±0,1

(L-2.54)±0,1

Ø1,0±0,05

②

CONTACT PIN

Cu Sn

^①

^②

COLOR: GREEN

①

PINHOUSING

PBT GF

FINISH

ITEM NO.

DESCRIPTION

MATERIAL

FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± 1°

TOLERANCES UNLESS OTHERWISE SPECIFIED:
±0.2 mm

^③

SEE TABLE

MATERIAL

SEE TABLE

DWN
MOHAMMED THAJUDEEN
06SEP2013

CHK
PRASHANTH S
06SEP2013

APVD
RAJENDRA PAI
06SEP2013

PRODUCT SPEC
108-18012

APPLICATION SPEC
—

WEIGHT
—

STE

TE Connectivity

NAME

AMPMODU II PINHEADER 90DEG, SINGLE ROW
AMPMODU II STIFTLEISTE 90DEG, EINREIHIG

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-825438

—

CUSTOMER DRAWING

SCALE
1:1

SHEET
1 OF 1

REV
L2

POS.x2.54=L ±0,3

(L-2.54)±0,1

2.54 ±0.1

2.8

"B"

"L"

0,63

2.5-0.1

3.7-0.2

0.3

RO.5

"D"

"C"

1470-19 (3/11)