


## P.C. MOUNTING

|           |           |
|-----------|-----------|
| O.P. (MM) | P.T. (MM) |
| 9.1 ±0.8  | 3.6 MAX   |




O.P. = OPERATING POINT  
P.T. = PER-TRAVEL




CIRCUIT: SPDT

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE:  $X.X \pm 0.4$   
 $X.XX \pm 0.25$
3. RATING: 5A @125/250VAC UL, CUL, VDE APPROVED
- ▲ 4. OPERATING FORCE:  $25 \pm 12$  GRAMS
5. OPERATING TEMP: -25°C TO 85°C
6. ELECTRICAL LIFE: 50,000 CYCLES MIN.
7. MECHANICAL LIFE: 1,000,000 CYCLES TYP.
8. INSULATION RESISTANCE: 100 MEGA-OHMS
9. DIELECTRIC STRENGTH: 1000VAC 1 MINUTE (INITAL VALUE)
10. CONTACT RESISTANCE: 100 mΩ MAX.
11. ▲ DENOTES CRITICAL PARAMETER.
12. 2002/95/EC (ROHS) COMPLIANT



## ISOMETRIC



|     |        |                              |         |    |
|-----|--------|------------------------------|---------|----|
| D   | 15658  | CHANGES NOTED                | 1/4/06  | PH |
| C   | 15283  | EDIT PC MOUNT, ROHS NOTE     | 9/15/05 | PH |
| B   | 15090  | CORRECTED NOTE AND DIMENSION | 7/12/05 | JB |
| A   | 15042  | RELEASED FOR PRODUCTION      | 6/30/05 | JB |
| REV | PCR NO | DESCRIPTION                  | DATE    | BY |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE MS0850501F025V1A

SCALE 2:1

|      |           |
|------|-----------|
| DATE | 6/30/2005 |
|------|-----------|

|    |  |
|----|--|
| DR |  |
| JB |  |

DWG Q970017

REV  
D