

SCR/SCR and SCR/Diode (MAGN-A-PAK Power Modules), 170 A, 250 A



MAGN-A-PAK

FEATURES

- High voltage
- Electrically isolated base plate
- 3500 V_{RMS} isolating voltage
- Industrial standard package
- Simplified mechanical designs, rapid assembly
- High surge capability
- Large creepage distances
- UL approved file E78996 
- Designed and qualified for industrial level
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

PRIMARY CHARACTERISTICS

$I_{T(AV)}$	170 A, 250 A
Type	Modules - thyristor, standard
Package	MAGN-A-PAK

DESCRIPTION

This VSK series of MAGN-A-PAK modules uses high voltage power thyristor/thyristor and thyristor/diode in seven basic configurations. The semiconductors are electrically isolated from the metal base, allowing common heatsinks and compact assemblies to be built. They can be interconnected to form single phase or three phase bridges or as AC-switches when modules are connected in anti-parallel mode. These modules are intended for general purpose applications such as battery chargers, welders, motor drives, UPS, etc.

MAJOR RATINGS AND CHARACTERISTICS

SYMBOL	CHARACTERISTICS	VSK.170..	VSK.250..	UNITS
$I_{T(AV)}$	85 °C	170	250	A
$I_{T(RMS)}$		377	555	
I_{TSM}	50 Hz	5100	8500	
	60 Hz	5350	8900	
I^2t	50 Hz	131	361	kA ² s
	60 Hz	119	330	
$I^2\sqrt{t}$		1310	3610	kA ² √s
V_{DRM}/V_{RRM}		400 to 1600	400 to 2000	V
T_J	Range	-40 to +130		°C



ELECTRICAL SPECIFICATIONS

VOLTAGE RATINGS				
TYPE NUMBER	VOLTAGE CODE	V_{RRM}/V_{DRM} , MAXIMUM REPETITIVE PEAK REVERSE AND OFF-STATE BLOCKING VOLTAGE V	V_{RSM} , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V	I_{RRM}/I_{DRM} AT 130 °C MAXIMUM mA
VS-VSK.170-	04	400	500	50
	08	800	900	
	10	1000	1100	
	12	1200	1300	
	14	1400	1500	
	16	1600	1700	
VS-VSK.250-	04	400	500	50
	08	800	900	
	10	1000	1100	
	12	1200	1300	
	14	1400	1500	
	16	1600	1700	
	18	1800	1900	60
	20	2000	2100	

ON-STATE CONDUCTION								
PARAMETER	SYMBOL	TEST CONDITIONS			VSK.170	VSK.250	UNITS	
Maximum average on-state current at case temperature	I _{T(AV)}	180° conduction, half sine wave			170	250	A	
					85	85	°C	
Maximum RMS on-state current	I _{T(RMS)}	As AC switch			377	555	A	
Maximum peak, one-cycle on-state non-repetitive, surge current	I _{TSM}	t = 10 ms	No voltage reapplied	Sinusoidal half wave, initial T _J = T _J maximum	5100	8500		
		t = 8.3 ms			5350	8900		
		t = 10 ms	100 % V _{RRM} reapplied		4300	7150		
		t = 8.3 ms			4500	7500		
Maximum I ² t for fusing	I ² t	t = 10 ms	No voltage reapplied		131	361	kA ² s	
		t = 8.3 ms			119	330		
		t = 10 ms	100 % V _{RRM} reapplied		92.5	255		
		t = 8.3 ms			84.4	233		
Maximum I ² √t for fusing	I ² √t	t = 0.1 ms to 10 ms, no voltage reapplied			1310	3610	kA ² √s	
Low level value or threshold voltage	V _{T(TO)1}	(16.7 % × π × I _{T(AV)} < I < π × I _{T(AV)}), T _J = T _J maximum			0.89	0.97	V	
High level value of threshold voltage	V _{T(TO)2}	(I > π × I _{T(AV)}), T _J = T _J maximum			1.12	1.00		
Low level value on-state slope resistance	r _{t1}	(16.7 % × π × I _{T(AV)} < I < π × I _{T(AV)}), T _J = T _J maximum			1.34	0.60	mΩ	
High level value on-state slope resistance	r _{t2}	(I > π × I _{T(AV)}), T _J = T _J maximum			0.96	0.57		
Maximum on-state voltage drop	V _{TM}	I _{TM} = π × I _{T(AV)} , T _J = T _J maximum, 180° conduction, average power = V _{T(TO)} × I _{T(AV)} + r _f × (I _{T(RMS)}) ²			1.60	1.44	V	
Maximum holding current	I _H	Anode supply = 12 V, initial I _T = 30 A, T _J = 25 °C			500	500	mA	
Maximum latching current	I _L	Anode supply = 12 V, resistive load = 1 Ω, gate pulse: 10 V, 100 μs, T _J = 25 °C			1000	1000		



SWITCHING					
PARAMETER	SYMBOL	TEST CONDITIONS	VSK.170	VSK.250	UNITS
Typical delay time	t _d	T _J = 25 °C, gate current = 1 A dI _g /dt = 1 A/μs V _d = 0.67 % V _{DRM}	1.0		μs
Typical rise time	t _r		2.0		
Typical turn-off time	t _q	I _{TM} = 300 A; dI/dt = 15 A/μs; T _J = T _J maximum; V _R = 50 V; dV/dt = 20 V/μs; gate 0 V, 100 Ω	50 to 150		

BLOCKING					
PARAMETER	SYMBOL	TEST CONDITIONS	VSK.170	VSK.250	UNITS
Maximum peak reverse and off-state leakage current	I_{RRM} , I_{DRM}	$T_J = T_J$ maximum	50	60	mA
RMS insulation voltage	V_{INS}	50 Hz, circuit to base, all terminals shorted, 25 $^\circ\text{C}$, 1 s	3000		V
Critical rate of rise of off-state voltage	dV/dt	$T_J = T_J$ maximum, exponential to 67 % rated V_{DRM}	1000		V/ μs

TRIGGERING					
PARAMETER	SYMBOL	TEST CONDITIONS	VSK.170	VSK.250	UNITS
Maximum peak gate power	P_{GM}	$t_p \leq 5\text{ ms}$, $T_J = T_J$ maximum	10.0		W
Maximum average gate power	$P_{G(AV)}$	$f = 50\text{ Hz}$, $T_J = T_J$ maximum	2.0		
Maximum peak gate current	+ I_{GM}	$t_p \leq 5\text{ ms}$, $T_J = T_J$ maximum	3.0		A
Maximum peak negative gate voltage	- V_{GT}	$t_p \leq 5\text{ ms}$, $T_J = T_J$ maximum	5.0		V
Maximum required DC gate voltage to trigger	V_{GT}	$T_J = -40\text{ }^\circ\text{C}$	4.0		
		$T_J = 25\text{ }^\circ\text{C}$	3.0		
		$T_J = T_J$ maximum	2.0		
Maximum required DC gate current to trigger	I_{GT}	$T_J = -40\text{ }^\circ\text{C}$	350		mA
		$T_J = 25\text{ }^\circ\text{C}$	200		
		$T_J = T_J$ maximum	100		
Maximum gate voltage that will not trigger	V_{GD}	$T_J = T_J$ maximum, rated V_{DRM} applied	0.25		V
Maximum gate current that will not trigger	I_{GD}	$T_J = T_J$ maximum, rated V_{DRM} applied	10.0		mA
Maximum rate of rise of turned-on current	dI/dt	$T_J = T_J$ maximum, $I_{TM} = 400\text{ A}$, rated V_{DRM} applied	500		A/ μs

THERMAL AND MECHANICAL SPECIFICATIONS					
PARAMETER	SYMBOL	TEST CONDITIONS	VSK.170	VSK.250	UNITS
Junction operating and storage temperature range	T_J , T_{Stg}		-40 to +130		$^\circ\text{C}$
Maximum thermal resistance, junction to case per junction	R_{thJC}	DC operation	0.17	0.125	K/W
Typical thermal resistance, case to heatsink per module	R_{thCS}	Mounting surface flat, smooth and greased	0.02	0.02	
Mounting torque $\pm 10\%$	MAGN-A-PAK to heatsink busbar to MAGN-A-PAK	A mounting compound is recommended and the torque should be rechecked after a period of about 3 hours to allow for the spread of the compound.	4 to 6		Nm
Approximate weight					
			500		g
			17.8		oz.
Case style			MAGN-A-PAK		


ΔR CONDUCTION PER JUNCTION

DEVICES	SINUSOIDAL CONDUCTION AT T _J MAXIMUM					RECTANGULAR CONDUCTION AT T _J MAXIMUM					UNITS
	180°	120°	90°	60°	30°	180°	120°	90°	60°	30°	
VSK.170-	0.009	0.010	0.010	0.020	0.032	0.007	0.011	0.015	0.020	0.033	K/W
VSK.250-	0.009	0.010	0.014	0.020	0.032	0.007	0.011	0.015	0.020	0.033	

Note

- Table shows the increment of thermal resistance R_{thJC} when devices operate at different conduction angles than DC




Fig. 1 - Current Ratings Characteristics




Fig. 3 - On-State Power Loss Characteristics




Fig. 2 - Current Ratings Characteristics




Fig. 4 - On-State Power Loss Characteristics




Fig. 5 - Maximum Non-Repetitive Surge Current




Fig. 6 - Maximum Non-Repetitive Surge Current




Fig. 7 - On-State Power Loss Characteristics




Fig. 8 - On-State Power Loss Characteristics




Fig. 9 - On-State Power Loss Characteristics




Fig. 10 - Current Ratings Characteristics




Fig. 12 - On-State Power Loss Characteristics




Fig. 11 - Current Ratings Characteristics




Fig. 13 - On-State Power Loss Characteristics




Fig. 14 - Maximum Non-Repetitive Surge Current




Fig. 15 - Maximum Non-Repetitive Surge Current




Fig. 16 - On-State Power Loss Characteristics




Fig. 17 - On-State Power Loss Characteristics




Fig. 18 - On-State Power Loss Characteristics




Fig. 19 - On-State Voltage Drop Characteristics




Fig. 21 - Reverse Recovery Charge Characteristics




Fig. 20 - On-State Voltage Drop Characteristics




Fig. 22 - Reverse Recovery Charge Characteristics





Fig. 23 - Gate Characteristics


Fig. 24 - Thermal Impedance Z_{thJC} Characteristics

ORDERING INFORMATION TABLE

Device code	VS-VS	KT	250	-	20	PbF
-------------	-------	----	-----	---	----	-----

(1)

(2)

(3)





(4)

(5)

- 1** - Vishay Semiconductors product
- 2** - Circuit configuration (see dimensions - link at the end of datasheet)
- 3** - Current rating
- 4** - Voltage code x 100 = V_{RRM} (see Voltage Ratings table)
- 5** -
 - None = standard production
 - PbF = lead (Pb)-free

Note


- To order the optional hardware go to www.vishay.com/doc?95172

CIRCUIT CONFIGURATION		
CIRCUIT DESCRIPTION	CIRCUIT CONFIGURATION CODE	CIRCUIT DRAWING
Two SCRs doubler circuit	KT	 Available up to 2000 V, contact factory for different requirement
SCR/diode doubler circuit, positive control	KH	 Available up to 2000 V, contact factory for different requirement
SCR/diode doubler circuit, negative control	KL	 Available up to 2000 V, contact factory for different requirement
Two SCRs common cathodes	KU	 Available up to 1200 V, contact factory for different requirement

LINKS TO RELATED DOCUMENTS	
Dimensions	www.vishay.com/doc?95086

MAGN-A-PAK

DIMENSIONS in millimeters (inches)



Notes

- Dimensions are nominal
- Full engineering drawings are available on request
- UL identification number for gate and cathode wire: UL 1385
- UL identification number for package: UL 94 V-0



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[VSKH170-16](#) [VSKH170-04](#) [VSKL170-16](#) [VSKL170-16D25](#) [VSKH170-12](#) [VSKL170-14D20](#) [VSKT250-12PBF](#)
[VSKT170-14](#) [VSKT170-08](#) [VSKH170-16D25](#) [VSKT170-16](#) [VSKV250-04](#) [VSKT170-12](#) [VSKV250-08](#) [VSKV250-12](#)
[VSKT170-04](#) [VSKH170-14D20](#) [VS-VSKH250-04PBF](#) [VS-VSKH170-16PBF](#) [VS-VSKH250-08PBF](#) [VS-VSKH250-14PBF](#) [VS-VSKV250-08PBF](#) [VS-VSKV250-12PBF](#) [VS-VSKH250-16PBF](#) [VS-VSKL250-12PBF](#) [VSKH170-12PBF](#)
[VSKL250-12PBF](#) [VSKL250-16PBF](#) [VSKT170-12PBF](#) [VSKT170-14PBF](#) [VSKT170-16PBF](#) [VSKT250-04PBF](#)
[VSKT250-08PBF](#) [VSKT250-14PBF](#) [VSKT250-16PBF](#) [VSKU250-12](#) [VSKU250-12PBF](#) [VSKV250-12PBF](#) [VS-](#)
[VSKL250-08PBF](#) [VS-VSKT250-04PBF](#) [VS-VSKT170-04PBF](#) [VS-VSKT250-12PBF](#) [VS-VSKT250-08PBF](#) [VS-](#)
[VSKT250-16PBF](#) [VS-VSKL250-16PBF](#) [VS-VSKT170-16PBF](#) [VS-VSKL250-14PBF](#) [VS-VSKT250-14PBF](#) [VS-](#)
[VSKV250-04PBF](#) [VS-VSKT170-14PBF](#) [VS-VSKL170-16PBF](#) [VS-VSKT170-12PBF](#) [VS-VSKH250-12PBF](#) [VS-](#)
[VSKT170-08PBF](#) [VS-VSKU250-12PBF](#) [VS-VSKH170-12PBF](#) [VS-VSKT250-18PBF](#) [VS-VSKL250-18PBF](#) [VS-](#)
[VSKL250-20PBF](#) [VS-VSKH250-20PBF](#) [VS-VSKT250-20PBF](#) [VS-VSKH250-18PBF](#)