








MATERIALS AND FINISHES

BODY, COUPLING NUT, FERRULE BRASS
PLATED NICKEL

CENTER CONTACT BRASS
PLATED GOLD

INSULATOR TEFLON



CABLE STRIP DIMENSIONS

73276-1340	73258-5059, ONE PER BAG
73258-5059	BULKPACK
PART NO.	PACKAGING

CHG: DELETE
AS-73597-0020
DELETE
ES-73599-0000
DELETE ELECTRICAL
SPECIFICATIONS

EC NO: URF2011-0247
2010/10/25
DRWN: JWIENER
CHKD: SSS
2010/10/25
APPR: JWIENER
2010/10/27

QUALITY
SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± .005	± .0005
3 PLACES	± .005	± .0005
2 PLACES	± .005	± .0005
1 PLACE	± .005	± .0005

ANGULAR ± 2 °

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN

DRAWN BY	DATE
FIELDS	1993/05/03
CHECKED BY	DATE
APPROVED BY	DATE
JWIENER	2010/10/27

MATERIAL NO.

SEE TABLE

SIZE
C

SCALE
METRIC

DESIGN UNITS
METRIC

THIRD ANGLE
PROJECTION

TITLE
N PLUG, STRAIGHT 50 OHM
RG142 CABLE, CRIMP/CRIMP
50 OHMS, N-PC

MOLEX INCORPORATED

DOCUMENT NO.
SD-73258-5059

SHEET NO.
1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION