


General Purpose Transistor



Pin Configuration:

1. Emitter
2. Base
3. Collector

Features:

- NPN silicon planar epitaxial transistors
- General purpose transistors, best suited for use in driver stages of audio amplifiers, of tape recorders. Low noise input stages, Hi-Fi amplifiers, signal processing circuits of television receivers

Absolute Maximum Ratings

Parameters	Symbol	Value	Unit
Collector Emitter Voltage	V_{CEO}	30	V
Collector Base Voltage	V_{CBO}		
Emitter Base Voltage	V_{EBO}		
Collector Current Continuous	I_C	100	mA
Power Dissipation at $T_a = 25^\circ\text{C}$ Derate above 25°C	P_D	625 5	mW mW/ $^\circ\text{C}$
Power Dissipation at $T_C = 25^\circ\text{C}$ Derate above 25°C		1.5 12	W mW/ $^\circ\text{C}$
Operating and Storage Junction Temperature Range	T_j, T_{stg}	-55 to +150	$^\circ\text{C}$

Thermal Resistance

Junction to Ambient	$R_{th(j-a)}$	200	$^\circ\text{C/W}$
Junction to Case	$R_{th(j-c)}$	83.3	

General Purpose Transistor

Electrical Characteristics ($T_a = 25^\circ\text{C}$ unless otherwise specified)

Parameters	Symbol	Test Condition	Min.	Typ.	Max.	Units
Collector Emitter Voltage	V_{CEO}	$I_C = 1\text{mA}, I_B = 0$	30	-	-	V
Collector Base Voltage	V_{CBO}	$I_C = 10\mu\text{A}, I_E = 0$		-	-	
Emitter Base Voltage	V_{EBO}	$I_E = 10\mu\text{A}, I_C = 0$	5	-	-	
Collector Cut off Current	I_{CBO}	$V_{CB} = 30\text{V}, I_E = 0$ $V_{CB} = 30\text{V}, I_E = 0,$ $T_a = +125^\circ\text{C}$	-	-	15 5	nA μA
Emitter Cut off Current	I_{EBO}	$V_{EB} = 4\text{V}, I_C = 0$	-	-	15	nA
DC Current Gain	h_{FE}	$V_{CE} = 5\text{V}, I_C = 10\mu\text{A}$ $V_{CE} = 5\text{V}, I_C = 2\text{mA}$	100 420	270 500	- 800	-
Collector Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C = 10\text{mA}, I_B = 0.5\text{mA}$ $I_C = 10\text{mA}, I_B = \text{see note 1}$ $I_C = 100\text{mA}, I_B = 5\text{mA}^*$	-	0.075 0.3 0.25	0.25 0.6 0.6	V
Base Emitter Saturation Voltage	$V_{BE(sat)}$	$I_C = 10\text{mA}, I_B = 5\text{mA}^*$	-	1.1	-	
Base Emitter on Voltage	$V_{BE(on)}$	$I_C = 10\mu\text{A}, V_{CE} = 5\text{V}$ $I_C = 100\mu\text{A}, V_{CE} = 5\text{V}$ $I_C = 2\text{mA}, V_{CE} = 5\text{V}$	0.55	0.52 0.55 0.62	0.7	


Dynamic Characteristics

Transition Frequency	f_T	$I_C = 10\text{mA}, V_{CE} = 5\text{V},$ $f = 100\text{MHz}$	-	250	-	MHz
Collector Output Capacitance	C_{cbo}	$I_E = 0, V_{CE} = 10\text{V}$ $f = 1\text{MHz}$	-	2.5	-	pF
Noise Figure	NF_1^* NF_2	$V_{CE} = 5\text{V}, I_C = 200\mu\text{A}$ $R_S = 2\text{K}\Omega,$ $f = 30\text{Hz} - 15\text{kHz}$ $V_{CE} = 5\text{V}, I_C = 200\mu\text{A}$ $R_S = 100\text{K}\Omega, f = 1\text{kHz}$	-	0.6	2.5 10	dB
Small Signal Current Gain	h_{fe}	$V_{CE} = 5\text{V}, I_C = 2\text{mA}$ $f = 1\text{kHz}$	450	600	900	-

Note 1: I_B is value for which $I_C = 11\text{mA}$ at $V_{CE} = 1\text{V}$

*Pulse Condition: = Pulse Width $\leq 300\mu\text{s}$, Duty Cycle $\leq 2\%$.

General Purpose Transistor



Dimensions	Min.	Max.
A	4.32	5.33
B	4.45	5.2
C	3.18	4.19
D	0.41	0.55
E	0.35	0.5
F	5°	
G	1.14	1.4
H		1.53
K	12.7	-
L	1.982	2.082

Dimensions : Millimetres

Pin Configuration:

1. Emitter
2. Base
3. Collector

Part Number Table

Description	Part Number
Transistor, NPN, TO-92	BC549C

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.