





STANDARD CRIMP




Standardcrimp



1-967591-1	B		> 10 - 16	7.1 - 7.7	CuNiSi	PRE TIN PLATED vorverzinkt 1 - 3 µm	H = 8.5 J = 13.5 K = 17.0 M = 42.5	A = 8.7 B = 9.1 D _{90°} = 5.1	C = 14.4 E = 13.2 D _{180°} = 10.5 L = 2.7	SINGLE WIRE SEAL Einzeldichtung
1-967590-2	B		6 - 10	4.6 - 6.4	CuNiSi	SILVER PLATED versilbert 3-5 µm (only contact area)	H = 6.5 J = 12.0 K = 16.0 M = 41.7	A = 7.1 B = 7.6 D _{90°} = 3.8	C = 12.8 E = 12.8 D _{180°} = 9.5 L = 2.5	
1-967590-1	B					PRE TIN PLATED vorverzinkt 1 - 3 µm	H = 9.5 J = 12.5 K = 16.0 M = 41.7	A = 9.1 B = 9.5 D _{90°} = 5.3	C = 12.1 E = 11.7 D _{180°} = 7.6 L = 0.9	
1-2177217-1	A		> 10 - 16	7.1 - 7.7	CuNiSi	PRE TIN PLATED vorverzinkt 1 - 3 µm	H = 9.5 J = 12.5 K = 16.0 M = 41.7	A = 9.1 B = 9.5 D _{90°} = 5.3	C = 12.1 E = 11.7 D _{180°} = 7.6 L = 0.9	STANDARD CRIMP Standardcrimp
1-967589-2	B					SILVER PLATED versilbert 3-5 µm (only contact area)	H = 9.5 J = 12.5 K = 16.0 M = 41.7	A = 8.7 B = 9.1 D _{90°} = 5.1	C = 11.6 E = 11.9 D _{180°} = 7.1 L = 1.0	
1-967589-1	B					PRE TIN PLATED vorverzinkt 1 - 3 µm	H = 9.5 J = 12.5 K = 16.0 M = 41.7	A = 8.7 B = 9.1 D _{90°} = 5.1	C = 11.6 E = 11.9 D _{180°} = 7.1 L = 1.0	
1-967588-2	B		6 - 10	4.6 - 6.4	CuNiSi	SILVER PLATED versilbert 3-5 µm (only contact area)	H = 6.5 J = 9.5 K = 12.5 M = 38.2	A = 7.1 B = 7.6 D _{90°} = 3.8	C = 9.3 E = 9.9 D _{180°} = 5.9 L = 0.9	
1-967588-1	B					PRE TIN PLATED vorverzinkt 1 - 3 µm	H = 6.5 J = 9.5 K = 12.5 M = 38.2	A = 7.1 B = 7.6 D _{90°} = 3.8	C = 9.3 E = 9.9 D _{180°} = 5.9 L = 0.9	
1-1241930-1	A					PRE TIN PLATED vorverzinkt 1 - 3 µm	H = 6.5 J = 9.5 K = 12.5 M = 38.2	A = 7.1 B = 7.6 D _{90°} = 3.8	C = 9.3 E = 9.9 D _{180°} = 5.9 L = 0.9	
1-1719386-1	B		3 - 6	4.0 - 5.1	CuNiSi	PRE TIN PLATED vorverzinkt 1 - 3 µm	H = 5.5 J = 7.8 K = 10.1 M = 38.2	A = 5.8 B = 6.1 D _{90°} = 2.9	C = 7.8 E = 8.0 D _{180°} = 4.6 L = 0.6	VERSION Ausführung
ORDER NO. Bestell-Nr.	REV.	TO BE USED ON TAB THICKNESS	WIRE SIZE RANGE	INSULATION DIA	MATERIAL	SURFACE	LENGTH Laenge	WIRE CRIMP Drahtcrimp	INSUL. CRIMP Isol.-Crimp	
Strip Bandware		Geeignet fuer Flachsteckerdicke	Leiterquerschnitt (mm²)	IsolationsØ (mm)	Werkstoff	Oberflaeche	CRIMP DIMENSIONS Crimpabmessungen (mm)			

SINGLE WIRE SEAL

Einzeldichtungssystem



SINGLE WIRE SEAL Einzeldichtung		
1355437-3	16	CLARET RED Weinrot
1355437-2	10	SKY BLUE Himmelblau
1355437-1	6	CLARET VIOLET Bordeauxviolett
ORDER NO. Bestell-Nr.	WIRE SIZE RANGE Drahtgroessenbereich (mm²)	COLOUR Farbe

- MATING PART SEE TE INTERFACE DRAWING: 114-18317
Gegenstecker nach TE Spezifikation: 114-18317
- TO BE USED ON TAB THICKNESS 0.8±0.05
Geeignet fuer Flachsteckerdicke 0.8±0.05
- TO BE USED ON TAB THICKNESS 1.2±0.05
Geeignet fuer Flachsteckerdicke 1.2±0.05
- BRANDNAME AND REVISION STATUS
Herstellerlogo und Revisionsstand
- IDENTIFICATION FOR 0.8mm VERSION
Kennzeichnung fuer 0.8mm Version

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN H.Keil	02OCT2000	TE Connectivity	
DIMENSIONS: mm		CHK G.v.d.Burgel	02OCT2000		
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN EN ISO 8015		APVD J.Woller	02OCT2000	NAME	
D. PLC 1. PLC 2. PLC 3. PLC 4. PLC ANGLES FINISH		PRODUCT SPEC 108-18630	APPLICATION SPEC 114-18269	PRODUCT GROUP DRAWING FOR AMP MCP 9.5 Tabellenzeichnung fuer AMP MCP 9.5	
MATERIAL -		WEIGHT -	SCALE Customer Drawing	SIZE A 1	
CAGE CODE 00779		DRAWING NO. C=1355037	RESTRICTED TO -	SHEET 1 OF 1	
REV B8		REV B8		REV B8	