


- Sensitive Gate Triacs
- 4 A RMS
- Glass Passivated Wafer
- 400 V to 700 V Off-State Voltage
- Max  $I_{GT}$  of 5 mA (Quadrants 1 - 3)



Pin 2 is in electrical contact with the mounting base.

MDC2ACA

### absolute maximum ratings over operating case temperature (unless otherwise noted)

RATING	SYMBOL	VALUE	UNIT
Repetitive peak off-state voltage (see Note 1)	$V_{DRM}$	400	
TIC206D		600	V
TIC206M		700	
TIC206S			
Full-cycle RMS on-state current at (or below) 85°C case temperature (see Note 2)	$I_{T(RMS)}$	4	A
Peak on-state surge current full-sine-wave at (or below) 25°C case temperature (see Note 3)	$I_{TSM}$	25	A
Peak gate current	$I_{GM}$	$\pm 0.2$	A
Peak gate power dissipation at (or below) 85°C case temperature (pulse width $\leq 200 \mu s$ )	$P_{GM}$	1.3	W
Average gate power dissipation at (or below) 85°C case temperature (see Note 4)	$P_{G(AV)}$	0.3	W
Operating case temperature range	$T_C$	-40 to +110	°C
Storage temperature range	$T_{stg}$	-40 to +125	°C
Lead temperature 1.6 mm from case for 10 seconds	$T_L$	230	°C

NOTES: 1. These values apply bidirectionally for any value of resistance between the gate and Main Terminal 1.  
 2. This value applies for 50-Hz full-sine-wave operation with resistive load. Above 85°C derate linearly to 110°C case temperature at the rate of 160 mA/°C.  
 3. This value applies for one 50-Hz full-sine-wave when the device is operating at (or below) the rated value of on-state current. Surge may be repeated after the device has returned to original thermal equilibrium. During the surge, gate control may be lost.  
 4. This value applies for a maximum averaging time of 20 ms.

### electrical characteristics at 25°C case temperature (unless otherwise noted )

PARAMETER	TEST CONDITIONS			MIN	TYP	MAX	UNIT
$I_{DRM}$ Repetitive peak off-state current	$V_D$ = rated $V_{DRM}$	$I_G$ = 0	$T_C$ = 110°C			$\pm 1$	mA
$I_{GT}$ Gate trigger current	$V_{supply} = +12 V \dagger$	$R_L = 10 \Omega$	$t_{p(g)} > 20 \mu s$		0.9	5	
	$V_{supply} = +12 V \dagger$	$R_L = 10 \Omega$	$t_{p(g)} > 20 \mu s$		-2.2	-5	
	$V_{supply} = -12 V \dagger$	$R_L = 10 \Omega$	$t_{p(g)} > 20 \mu s$		-1.8	-5	
	$V_{supply} = -12 V \dagger$	$R_L = 10 \Omega$	$t_{p(g)} > 20 \mu s$		2.4	10	mA

† All voltages are with respect to Main Terminal 1.

### PRODUCT INFORMATION

**electrical characteristics at 25°C case temperature (unless otherwise noted) (continued)**

PARAMETER		TEST CONDITIONS			MIN	TYP	MAX	UNIT
$V_{GT}$	Gate trigger voltage	$V_{supply} = +12 V$ †	$R_L = 10 \Omega$	$t_{p(g)} > 20 \mu s$		0.7	2	V
		$V_{supply} = +12 V$ †	$R_L = 10 \Omega$	$t_{p(g)} > 20 \mu s$		-0.7	-2	
		$V_{supply} = -12 V$ †	$R_L = 10 \Omega$	$t_{p(g)} > 20 \mu s$		-0.7	-2	
		$V_{supply} = -12 V$ †	$R_L = 10 \Omega$	$t_{p(g)} > 20 \mu s$		0.7	2	
$V_T$	On-state voltage	$I_T = \pm 4.2 A$	$I_G = 50 mA$	(see Note 5)		$\pm 1.4$	$\pm 2.2$	V
$I_H$	Holding current	$V_{supply} = +12 V$ †	$I_G = 0$	$Init' I_{TM} = 100 mA$		1.5	15	mA
		$V_{supply} = -12 V$ †	$I_G = 0$	$Init' I_{TM} = -100 mA$		-1.3	-15	
$I_L$	Latching current	$V_{supply} = +12 V$ †	(see Note 6)				30	mA
$dv/dt$	Critical rate of rise of off-state voltage	$V_{DRM} = \text{Rated } V_{DRM}$	$I_G = 0$	$T_C = 110^\circ C$		$\pm 20$		
$dv/dt_{(c)}$	Critical rise of commutation voltage	$V_{DRM} = \text{Rated } V_{DRM}$	$I_{TRM} = \pm 4.2 A$	$T_C = 85^\circ C$	$\pm 1$	$\pm 3$		V/ $\mu s$

† All voltages are with respect to Main Terminal 1.

NOTES: 5. This parameter must be measured using pulse techniques,  $t_p = \leq 1 ms$ , duty cycle  $\leq 2\%$ . Voltage-sensing contacts separate from the current carrying contacts are located within 3.2 mm from the device body.

6. The triacs are triggered by a 15-V (open circuit amplitude) pulse supplied by a generator with the following characteristics:

$R_G = 100 \Omega$ ,  $t_{p(g)} = 20 \mu s$ ,  $t_r = \leq 15 ns$ ,  $f = 1 kHz$ .

**thermal characteristics**

PARAMETER		MIN	TYP	MAX	UNIT
$R_{\theta JC}$	Junction to case thermal resistance			7.8	°C/W
$R_{\theta JA}$	Junction to free air thermal resistance			62.5	°C/W

**PRODUCT INFORMATION**

DECEMBER 1971 - REVISED SEPTEMBER 2002  
Specifications are subject to change without notice.

TYPICAL CHARACTERISTICS

GATE TRIGGER CURRENT  
VS  
TEMPERATURE




Figure 1.

GATE TRIGGER VOLTAGE  
VS  
TEMPERATURE




Figure 2.

HOLDING CURRENT  
VS  
CASE TEMPERATURE




Figure 3.

LATCHING CURRENT  
VS  
CASE TEMPERATURE




Figure 4.

PRODUCT INFORMATION

DECEMBER 1971 - REVISED SEPTEMBER 2002  
Specifications are subject to change without notice.