

INSULATOR (YELLOW)
[絶縁チューブ (黄色)]

MARKING (GREEN) MEANS
"CR" BATTERY
[緑色 (CR電池)]

12.6±0.2

4.0±0.1
(4.5)

(1.95)

13.5±1.0

2.65±0.4

7.7±0.8

TIN PLATING
[Snメッキ]

3.5±0.5

TIN PLATING
[Snメッキ]

3.5±0.5

0.75±0.1

0.2±0.05

5.05±0.8

0.2±0.05

0.75±0.1


10.0±1.0





(4.5)

4.0±0.1

* NOTE [注記]

- TAB PULLING STRENGTH OVER 19.6N
[端子溶接強度: 19.6N以上]
- TAB MATERIAL: STAINLESS STEEL WITH
TIN PLATING 
[端子材料: 基材 ステンレス/表面 部分Snメッキ 
- (): REFERENCE DIMENSION AND ANGLE
[() 寸法、角度は参考値]


PRODUCT NO.	CR-1220/HFN	SCALE	
		4:1	
DRAWING NO.	JEHA1Z	REV.	 UNIT: mm
		0	



* NOTE [注記]

- TAB PULLING STRENGTH OVER 14.7N [端子溶接強度: 14.7N以上]
- TAB MATERIAL: STAINLESS STEEL WITH TIN PLATING [端子材料: 基材 ステンレス/表面 部分Snメッキ]
- (): REFERENCE DIMENSION AND ANGLE [() 寸法、角度は参考値]





PRODUCT NO.	CR-1616/F2N	SCALE
DRAWING NO.	MDF A6U	4:1
	REV. 0	UNIT: mm



* NOTE [注記]

1. TAB PULLING STRENGTH OVER 9.8 N [端子溶接強度: 9.8 N以上]
2. TAB MATERIAL: STAINLESS STEEL WITH TIN PLATING [端子材料: 基材 ステンレス/表面 部分Snメッキ]
3. (): REFERENCE DIMENSION AND ANGLE [() 寸法、角度は参考値]




PRODUCT NO.	CR-2016/F2N	SCALE	
		4:1	
DRAWING NO.	PDF A6Z	REV.	
		0	



* NOTE [注記]

1. TAB PULLING STRENGTH OVER 14.7N [端子溶接強度: 14.7N以上]
2. TAB MATERIAL: STAINLESS STEEL WITH TIN PLATING [端子材料: 基材 ステンレス/表面 部分Snメッキ]
3. (): REFERENCE DIMENSION AND ANGLE [() 寸法、角度は参考値]


PRODUCT NO.	CR-2032/F4N	SCALE	
		4 : 1	
DRAWING NO.	PMFB6Z	REV.	
		0	



* NOTE [注記]

1. TAB PULLING STRENGTH OVER 19.6N [端子溶接強度: 19.6N以上]
2. TAB MATERIAL: STAINLESS STEEL WITH TIN PLATING [端子材料: 基材 ステンレス/表面 部分Snメッキ]
3. (): REFERENCE DIMENSION AND ANGLE [() 寸法、角度は参考値]




PRODUCT NO.	CR-2330/VCN	SCALE	
		4:1	
DRAWING NO.	QKVA1Z	REV.	
		0	



※ NOTE [注記]

1. TAB PULLING STRENGTH OVER 19.6N [端子溶接強度: 19.6N以上]
2. TAB MATERIAL: STAINLESS STEEL WITH TIN PLATING [端子材料: 基材 ステンレス/表面 部分Snメッキ]
3. (): REFERENCE DIMENSION AND ANGLE [() 寸法、角度は参考値]


PRODUCT NO.	CR-2354/GUN	SCALE	
		4:1	
DRAWING NO.	QVGB1N	REV.	
		0	



* NOTE [注記]

1. TAB PULLING STRENGTH OVER 19.6N [端子溶接強度: 19.6N以上]
2. TAB MATERIAL: STAINLESS STEEL WITH TIN PLATING [端子材料: 基材 ステンレス/表面 部分Snメッキ]
3. (): REFERENCE DIMENSION AND ANGLE [() 寸法、角度は参考値]




PRODUCT NO.	CR-2354/VCN	SCALE	
		4 : 1	
DRAWING NO.	QVVA1Z	REV.	
		0	
			UNIT: mm



* NOTE [注記]

1. TAB PULLING STRENGTH OVER 19.6N [端子溶接強度: 19.6N以上]
2. TAB MATERIAL: STAINLESS STEEL WITH TIN PLATING [端子材料: 基材 ステンレス/表面 部分Snメッキ]
3. (): REFERENCE DIMENSION AND ANGLE [() 寸法、角度は参考値]

PRODUCT NO.	CR-2477/HFN	SCALE	
		4:1	
DRAWING NO.	RXHA1Z	REV.	 UNIT:mm
		0	



* NOTE [注記]

1. TAB PULLING STRENGTH OVER 19.6N [端子溶接強度: 19.6N以上]
2. TAB MATERIAL: STAINLESS STEEL WITH TIN PLATING [端子材料: 基材 ステンレス/表面 部分Snメッキ]
3. (): REFERENCE DIMENSION AND ANGLE [() 寸法、角度は参考値]

PRODUCT NO.	CR-2477/VCN	SCALE	
		4:1	
DRAWING NO.	RXVA1Z	REV.	
		0	