

Improved Quad CMOS Analog Switches

DESCRIPTION

The DG201B, DG202B analog switches are highly improved versions of the industry-standard DG201A, DG202. These devices are fabricated in Vishay Siliconix' proprietary silicon gate CMOS process, resulting in lower on-resistance, lower leakage, higher speed, and lower power consumption.

These quad single-pole single-throw switches are designed for a wide variety of applications in telecommunications, instrumentation, process control, computer peripherals, etc. An improved charge injection compensation design minimizes switching transients. The DG201B and DG202B can handle up to ± 22 V input signals, and have an improved continuous current rating of 30 mA. An epitaxial layer prevents latchup.

All devices feature true bi-directional performance in the on condition, and will block signals to the supply voltages in the off condition.

The DG201B is a normally closed switch and the DG202B is a normally open switch. (see Truth Table.)

FEATURES

- ± 22 V supply voltage rating
- TTL and CMOS compatible logic
- Low on-resistance - $R_{DS(on)}$: 45 Ω
- Low leakage - $I_{D(on)}$: 20 pA
- Single supply operation possible
- Extended temperature range
- Fast switching - t_{ON} : 120 ns
- Low glitching - Q: 1 pC



BENEFITS

- Wide analog signal range
- Simple logic interface
- Higher accuracy
- Minimum transients
- Reduced power consumption
- Superior to DG201A, DG202

APPLICATIONS

- Industrial instrumentation
- Test equipment
- Communications systems
- Disk drives
- Computer peripherals
- Portable instruments
- Sample-and-hold circuits
- Hi-Rel systems

FUNCTIONAL BLOCK DIAGRAM AND PIN CONFIGURATION



TRUTH TABLE		
Logic	DG201B	DG202B
0	On	Off
1	Off	On

Notes

- Logic "0" ≤ 0.8 V
- Logic "1" ≥ 2.4 V



ORDERING INFORMATION (Hi-Rel)						
PART	CONFIGURATION	TEMP. RANGE	PACKAGE	ORDERING PART	GENERIC	DSCC NUMBER
DG201B	SPST x 4, NC	- 55 °C to 125 °C	16-pin CerDIP	DG201BAK	DG201BAK	-
				DG201BAK-E3	DG201BAK-E3	-
				DG201BAK/883	DG201BAK/883	5962-8671604MEA (Vishay qualified, DSCC approval in progress)
			LCC-20	DG201BAZ/883	DG201BAZ/883	5962-8671604M2A (Vishay qualified, DSCC approval in progress)
DG202B	SPST x 4, NO	- 55 °C to 125 °C	16-pin CerDIP	DG202BAK	DG202BAK	-
				DG202BAK-E3	DG202BAK-E3	-
				DG202BAK/883	DG202BAK/883	5962-8671605MEA (Vishay qualified, DSCC approval in progress)
			LCC-20	DG202BAZ/883	DG202BAZ/883	5962-8671605M2A (Vishay qualified, DSCC approval in progress)

ABSOLUTE MAXIMUM RATINGS			
PARAMETER		LIMIT	UNIT
Voltages Referenced to V-		44	V
GND		25	
Digital Inputs ^a , V _S , V _D		(V-) - 2 to (V+) + 2 or 30 mA, whichever occurs first	
Current (any terminal)		30	mA
Peak Current, S or D (pulsed at 1 ms, 10 % duty cycle max.)		100	
Storage Temperature		(A suffix)	°C
Power Dissipation (Package) ^b	16-pin CerDIP ^c	900	mW
	LCC-20 ^d	750	

Notes

- a. Signals on S_X, D_X or IN_X exceeding V+ or V- will be clamped by internal diodes. Limit forward diode current to maximum current ratings.
b. All leads soldered or welded to PC board.
c. Derate 12 mW/°C above 75 °C.
d. Derate 10 mW/°C above 75 °C.


SCHEMATIC DIAGRAM (typical channel)

Fig. 1

**SPECIFICATIONS^a**

PARAMETER	SYMBOL	TEST CONDITIONS UNLESS OTHERWISE SPECIFIED	TEMP. ^b	TYP. ^c	A SUFFIX - 55 °C to 125 °C		UNIT
		V+ = 15 V, V- = - 15 V			MIN. ^d	MAX. ^d	
		V _{IN} = 2.4 V, 0.8 V ^f					
Analog Switch							
Analog Signal Range ^e	V _{ANALOG}		Full	-	- 15	15	V
Drain-Source On-Resistance	R _{DS(on)}	V _D = ± 10 V, I _S = 1 mA	Room	45	-	85	Ω
R _{DS(on)} Match	ΔR _{DS(on)}		Full	-	-	100	
Source Off Leakage Current	I _{S(off)}	V _S = ± 14 V, V _D = ± 14 V	Room	± 0.01	- 0.5	0.5	nA
			Full	-	- 20	20	
Drain Off Leakage Current	I _{D(off)}	V _S = ± 14 V, V _D = ± 14 V	Room	± 0.01	- 0.5	0.5	
			Full	-	- 20	20	
Drain On Leakage Current	I _{D(on)}	V _S = ± 14 V, V _D = ± 14 V	Room	± 0.02	- 0.5	0.5	
			Full	-	- 40	40	
Digital Control							
High Input Voltage	V _{INH}		Full	-	2.4	-	V
Low Input Voltage	V _{INL}		Full	-	-	0.8	
Input Current	I _{INH} or I _{INL}	V _{INH} or V _{INL}	Full	-	- 1	1	μA
Input Capacitance	C _{in}		Room	5	-	-	pF
Dynamic Characteristics							
Turn-On Time	t _{ON}	V _S = 2 V see switching time test circuit	Room	120	-	300	ns
			Full	-	-	-	
Turn-Off Time	t _{Off}		Room	65	-	200	
			Full	-	-	-	
Charge Injection	Q	C _L = 1000 pF, V _g = 0 V, R _g = 0 Ω	Room	1	-	-	pC
Source Off Capacitance	C _{S(off)}	V _S = 0 V, f = 1 MHz	Room	5	-	-	pF
Drain Off Capacitance	C _{D(off)}		Room	5	-	-	
Channel On Capacitance	C _{D(on)}	V _D = V _S = 0 V, f = 1 MHz	Room	16	-	-	
Off Isolation	OIRR	C _L = 15 pF, R _L = 50 Ω, V _S = 1 V _{RMS} , f = 100 kHz	Room	90	-	-	dB
Channel-to-Channel Crosstalk	X _{TALK}		Room	95	-	-	
Power Supply							
Positive Supply Current	I+	V _{IN} = 0 V or 5 V	Room	-	-	50	μA
			Full	-	-	100	
Negative Supply Current	I-		Room	-	- 1	-	
			Full	-	- 5	-	
Power Supply Range for Continuous Operation	V _{OP}		Full	-	± 4.5	± 22	V



SPECIFICATIONS ^a (Single Supply)							
PARAMETER	SYMBOL	TEST CONDITIONS UNLESS OTHERWISE SPECIFIED	TEMP. ^b	TYP. ^c	A SUFFIX - 55 °C to 125 °C		UNIT
		V ₊ = 12 V, V ₋ = 0 V			MIN. ^d	MAX. ^d	
		V _{IN} = 2.4 V, 0.8 V ^f					
Analog Switch							
Analog Signal Range ^e	V _{ANALOG}		Full	-	0	12	V
Drain-Source On-Resistance	R _{DS(on)}	V _D = 3 V, 8 V, I _S = 1 mA	Room	90	-	160	Ω
			Full	-	-	200	
Dynamic Characteristics							
Turn-On Time	t _{ON}	V _S = 8 V	Room	120	-	300	ns
Turn-Off Time	t _{OFF}	see switching time test circuit	Room	60	-	200	
Charge Injection	Q	C _L = 1 nF, V _{gen} = 6 V, R _{gen} = 0 Ω	Room	4	-	-	pC
Power Supply							
Positive Supply Current	I ₊	V _{IN} = 0 V or 5 V	Room	-	-	50	μA
			Full	-	-	100	
Negative Supply Current	I ₋		Room	-	- 1	-	
			Full	-	- 5	-	
Power Supply Range for Continuous Operation	V _{OP}		Full	-	4.5	25	V


Notes

- a. Refer to PROCESS OPTION FLOWCHART.
- b. Room = 25 °C, full = as determined by the operating temperature suffix.
- c. Typical values are for DESIGN AID ONLY, not guaranteed nor subject to production testing.
- d. The algebraic convention whereby the most negative value is a minimum and the most positive a maximum, is used in this datasheet.
- e. Guaranteed by design, not subject to production test.
- f. V_{IN} = input voltage to perform proper function.


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.




TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




$R_{DS(on)}$ vs. V_D and Power Supply Voltages




$R_{DS(on)}$ vs. V_D and Temperature




$R_{DS(on)}$ vs. V_D and Single Power Supply Voltages



Input Switching Threshold vs. Supply Voltage




Leakage Currents vs. Analog Voltage




Leakage Currents vs. Temperature




TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Switching Time vs. Single Supply Voltage




Switching Time vs. Power Supply Voltage









Q_S, Q_D - Charge Injection vs. Analog Voltage



Off Isolation vs. Frequency



Supply Current vs. Switching Frequency

TEST CIRCUITS

Fig. 2 - Switching Time

Fig. 3 - Off Isolation

Fig. 4 - Channel-to-Channel Crosstalk

Fig. 5 - Charge Injection


V_O = measured voltage error due to charge injection
The charge injection in coulombs is $Q = C_L \times V_O$

APPLICATIONS




Fig. 6 - Sample-and-Hold





Fig. 7 - Active Low Pass Filter with Digitally Selected Break Frequency



$$A_L \text{ (Voltage Gain Below Break Frequency)} = \frac{R_3}{R_1} = 100 \text{ (40 dB)}$$

$$f_C \text{ (Break Frequency)} = \frac{1}{2 R_3 C_X}$$

$$f_L \text{ (Unity Gain Frequency)} = \frac{1}{2 R_1 C_X}$$

$$\text{Max. Attenuation} = \frac{R_{DS(on)}}{10 \text{ k}} \approx -47 \text{ dB}$$





Fig. 8 -A Precision Amplifier with Digitally Programmable Input and Gains

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see www.vishay.com/ppg?63374.




CERDIP: 16-LEAD



Dim	MILLIMETERS		INCHES	
	Min	Max	Min	Max
A	4.06	5.08	0.160	0.200
A ₁	0.51	1.14	0.020	0.045
B	0.38	0.51	0.015	0.020
B ₁	1.14	1.65	0.045	0.065
C	0.20	0.30	0.008	0.012
D	19.05	19.56	0.750	0.770
E	7.62	8.26	0.300	0.325
E ₁	6.60	7.62	0.260	0.300
e ₁	2.54 BSC		0.100 BSC	
e _A	7.62 BSC		0.300 BSC	
L	3.18	3.81	0.125	0.150
L ₁	3.81	5.08	0.150	0.200
Q ₁	1.27	2.16	0.050	0.085
S	0.38	1.14	0.015	0.045
∞	0°	15°	0°	15°
ECN: S-03946—Rev. G, 09-Jul-01 DWG: 5403				



20-LEAD LCC



Dim	MILLIMETERS		INCHES	
	Min	Max	Min	Max
A	1.37	2.24	0.054	0.088
A₁	1.63	2.54	0.064	0.100
B	0.56	0.71	0.022	0.028
D	8.69	9.09	0.342	0.358
E	8.69	9.09	0.442	0.358
e	1.27 BSC		0.050 BSC	
L	1.14	1.40	0.045	0.055
L₁	1.96	2.36	0.077	0.093
ECN: S-03946—Rev. B, 09-Jul-01 DWG: 5321				



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.