

F


E

D

C


B

A



POL	MATERIAL NUMBER	ENGINEERING NUMBER	FINISHED LENGTH
12	1200940124	K02101P80M050	16.40' +6.50" -0 [5.0M +165.1 -0]
12	1200940125	K02101P80M100	32.81' +12.50" -0 [10.0M +317.5 -0]

POL	MATERIAL NUMBER	ENGINEERING NUMBER	FINISHED LENGTH
19	1200945027	K03001P80M050	16.40' +6.50" -0 [5.0M +165.1 -0]
19	1200940044	K03001P80M100	32.81' +12.50" -0 [10.0M +317.5 -0]



CONNECTOR SPECIFICATION:

VOLTAGE RATING	63V AC/DC
AMPERAGE RATING	6 AMPS
PROTECTION CLASS	IP67
OPERATING TEMPERATURE	-25°C TO 90°C
UL CERTIFICATIONS	NOT APPLICABLE
CSA CERTIFICATIONS	NOT APPLICABLE

ITEM	COMPONENT	MATERIAL	FINISH
1	INSERT	POLYURETHANE (PUR)	BLACK
2	CONTACT MATERIAL	COPPER ALLOY	GOLD OVER NICKEL
3	COUPLING NUT	BRASS	NICKEL PLATED
4	OVERMOLD	TPU	BLACK
12 POLE 5 19 POLE	CABLE 3x0.75 ² /18 AWG CABLE 8x0.34 ² /22 AWG CABLE 3x0.75 ² /18 AWG CABLE 16x0.34 ² /22 AWG	JACKET: PUR	JACKET: BLACK

DESCRIPTION EC NO: WEU2010-0281 DRWN: BBRAUCH 2010/001/19 CHKD: RE APPR: NSTAUDIG 2010/001/25	QUALITY SYMBOLS ▽ = 0 ▽C = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
1	REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. SEE TABLE		DOCUMENT NO. SD-120094-002		SHEET NO. 1 OF 1	
				SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			