


B-CD-503-02

- STUD SIZES: (1,005)

WIRE SIZE: 16-14 AWG
1.0-2.5 MM²

ALL DIMENSIONS= $\frac{\text{INCHES}}{\text{MM}}$

(MWID)=DENOTES MAXIMUM WIRE INSULATION DIAMETER



PART NUMBER	"W" ±.010	"C" MIN.	"L" MAX.	AVAILABLE STUD SIZES
B - 507 -	$\frac{.245}{6.22}$	$\frac{.209}{5.31}$	$\frac{.930}{23.62}$	04, 06
B - 524 -	$\frac{.295}{7.49}$	$\frac{.211}{5.36}$	$\frac{.927}{23.55}$	04, 06, 08
B - 527 -	$\frac{.362}{9.19}$	$\frac{.269}{6.83}$	$\frac{1.062}{26.97}$	06, 08, 10

DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED				REFERENCE	SCALE:	NTS	DATE	TITLE:
FRAC.	DEC.	ANG.		REV A 02A/1030 Rev 1/6/98			11-12-84	SPADE TONGUE TERMINAL AVIKRIMP 500-SERIES
±	±	±					12-4-84	

DWG. NO.	A	CUSTOMER DWG
-------------	---	-----------------



ETCmolex
INCORPORATED

ETC
INCORPORATED
molex

DWG. NO.	A	CUSTOMER DWG
-------------	----------	-----------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[19196-0037](#) [19196-0039](#)