

Three Phase Bridge (Power Modules), 60/70 A



MTK

FEATURES

- Package fully compatible with the industry standard INT-A-PAK power modules series
- High thermal conductivity package, electrically insulated case
- Excellent power volume ratio, outline for easy connections to power transistor and IGBT modules
- 4000 V_{RMS} isolating voltage
- UL E78996 approved 
- Totally lead (Pb)-free
- Designed and qualified for industrial level



RoHS
COMPLIANT

PRODUCT SUMMARY

I_o	60/70 A
-------	---------

DESCRIPTION

A range of extremely compact, encapsulated three phase bridge rectifiers offering efficient and reliable operation. They are intended for use in general purpose and heavy duty applications.

MAJOR RATINGS AND CHARACTERISTICS

SYMBOL	CHARACTERISTICS	60MT.K	70MT.K	UNITS
I_o		60 (75)	70 (90)	A
	T_c	85 (61)	85 (57)	°C
I_{FSM}	50 Hz	420	480	A
	60 Hz	440	500	
I^2t	50 Hz	870	1150	kA ² s
	60 Hz	790	1050	
$I^2\sqrt{t}$		8700	11 500	kA ² √s
V_{RRM}	Range	800 to 1600		V
T_{Stg}	Range	- 40 to 150		°C
T_J				

ELECTRICAL SPECIFICATIONS

VOLTAGE RATINGS

TYPE NUMBER	VOLTAGE CODE	V_{RRM} , MAXIMUM REPETITIVE PEAK REVERSE VOLTAGE V	V_{RSM} , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V	I_{RRM} MAXIMUM AT T_J MAXIMUM mA
60-70MT..K	80	800	900	10
	100	1000	1100	
	120	1200	1300	
	140	1400	1500	
	160	1600	1700	

FORWARD CONDUCTION								
PARAMETER	SYMBOL	TEST CONDITIONS			60MT.K	70MT.K	UNITS	
Maximum DC output current at case temperature	I _O	120° rect. conduction angle			60 (75)	70 (90)	A	
					85 (61)	85 (57)	°C	
Maximum peak, one-cycle forward, non-repetitive surge current	I _{FSM}	t = 10 ms	No voltage reapplied	Initial T _J = T _J maximum	420	480	A	
		t = 8.3 ms			440	500		
		t = 10 ms	100 % V _{RRM} reapplied		350	400		
		t = 8.3 ms			370	420		
Maximum I ² t for fusing	I ² t	t = 10 ms	No voltage reapplied		870	1150	kA ² s	
		t = 8.3 ms			790	1050		
		t = 10 ms	100 % V _{RRM} reapplied		610	800		
		t = 8.3 ms			560	730		
Maximum I ² √t for fusing	I ² √t	t = 0.1 to 10 ms, no voltage reapplied			8700	11 300	A ² √s	
Low level value of threshold voltage	V _{F(TO)1}	(16.7 % x π x I _{F(AV)}) < I < π x I _{F(AV)} , T _J maximum			0.85	0.86	V	
High level value of threshold voltage	V _{F(TO)2}	(I > π x I _{F(AV)}), T _J maximum			1.07	1.08		
Low level value of forward slope resistance	r _{f1}	(16.7 % x π x I _{F(AV)}) < I < π x I _{F(AV)} , T _J maximum			8.04	7.35	mΩ	
High level value of forward slope resistance	r _{f2}	(I > π x I _{F(AV)}), T _J maximum			7.08	6.53		
Maximum forward voltage drop	V _{FM}	I _{pk} = 100 A, T _J = 25 °C, t _p = 400 μs single junction			1.75	1.55	V	
RMS isolation voltage	V _{ISOL}	T _J = 25 °C, all terminal shorted f = 50 Hz, t = 1 s			4000			

THERMAL AND MECHANICAL SPECIFICATIONS						
PARAMETER	SYMBOL	TEST CONDITIONS	60MT.K	70MT.K	UNITS	
Maximum junction operating and storage temperature range	T _J , T _{Stg}		- 40 to 150		°C	
Maximum thermal resistance, junction to case	R _{thJC}	DC operation per module	0.37	0.29	K/W	
		DC operation per junction	2.22	1.75		
		120° rect. conduction angle per module	0.40	0.34		
		120° rect. conduction angle per junction	2.42	2.01		
Maximum thermal resistance, case to heatsink per module	R _{thCS}	Mounting surface smooth, flat and greased	0.03			
Mounting torque ± 10 %	to heatsink	A mounting compound is recommended and the torque should be rechecked after a period of 3 hours to allow for the spread of the compound. Lubricated threads.	4 to 6		Nm	
	to terminal		3 to 4			
Approximate weight				176		g




Fig. 1 - Current Ratings Characteristics




Fig. 2 - Forward Voltage Drop Characteristics





Fig. 3 - Total Power Loss Characteristics




Fig. 4 - Maximum Non-Repetitive Surge Current




Fig. 5 - Maximum Non-Repetitive Surge Current

60-70MT..KPbF Series

Vishay High Power Products Three Phase Bridge
(Power Modules), 60/70 A




Fig. 6 - Current Ratings Characteristics




Fig. 7 - Forward Voltage Drop Characteristics





Fig. 8 - Total Power Loss Characteristics




Fig. 9 - Maximum Non-Repetitive Surge Current




Fig. 10 - Maximum Non-Repetitive Surge Current




Fig. 11 - Thermal Impedance Z_{thJC} Characteristics


ORDERING INFORMATION TABLE

Device code	7	0	MT	160	K	PbF
	①	②	③	④	⑤	⑥
1	- Current rating code: 6 = 60 A (average) 7 = 70 A (average)					
2	- Three phase diodes bridge					
3	- Essential part number					
4	- Voltage code x 10 = V_{RRM} (see Voltage Ratings table)					
5	- PbF = Lead (Pb)-free					

Note

- To order the optional hardware go to www.vishay.com/doc?95172

CIRCUIT CONFIGURATION



LINKS TO RELATED DOCUMENTS	
Dimensions	http://www.vishay.com/doc?95004



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.