

MICRO SWITCH
a Honeywell Division

FED.MFG.CODE 91929

ASSEMBLY— PUSHBUTTON SWITCH

CATALOG LISTING

701PB542

CATALOG LISTING
701PB542
PAGE 1 OF 1

ISSUE
7

REPLACES

RELEASE NO. PR-22201

CHECK

CHECK

REVISIONS

A	PR-22201	JJA	30 MAY 96
B	C083238	DLT	2 OCT 96
C	201261	CSL	7 SEP 00
D	201411	CSL	2 OCT 00

CHECK

CHECK

CHECK

CHECK


CHECK

CHECK

CHECK

CHECK

CHECK




NOTES

- 1 - UNIT INCLUDES "19HM1" BASIC SWITCHES
- 2 - TERMINALS ARE TINNED FOR SOLDERING
- 3 - RECOMMENDED FOR MANUAL OPERATION ONLY
- 4 - FOR USE IN TEMPERATURE RANGE -65°F TO +500°F

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL	DO NOT SCALE PRINT
OPERATING FORCE — — — 2 LBS MAX	CONTACT ARRANGEMENT 2X S P D T 28 VOLTS DC RATING INDUCTIVE---SEA LEVEL---1/4 AMP 70,000 FT---1/4 AMP RESISTIVE---SEA LEVEL---1/2 AMP 70,000 FT---1/2 AMP	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
OVERTRAVEL FORCE — — — 2.5 LBS MAX		ONE PLACE (.0)	± .030
RELEASE FORCE — — — 2 OZ MIN		TWO PLACE (.00)	± .015
OVERTRAVEL — — — .030 MIN		THREE PLACE (.000)	± .005
DIFFERENTIAL TRAVEL---.031 MAX		ANGLES	±
		WEIGHT	

RASTER

DRAWN

CHECK

CHECK

CHECK