

## Comparator with 1.25% Reference and Adjustable Hysteresis

#### **Features**

- · 1.5V to 5.5V Operating Range
- 1.5 µA Typical Supply Current
- ±1.25% Voltage Threshold Accuracy
- 10 nA Maximum Input Leakage Current Over Temperature
- 10 μs Propagation Delay
- Externally Adjustable Hysteresis (MIC841)
- Internal 20 mV Hysteresis (MIC842)
- · Output Options:
  - Push-Pull, Active-High
  - Push-Pull. Active-Low
  - Open-Drain, Active-Low
- Open-Drain Output can be Pulled to 6V Regardless of V<sub>DD</sub>
- · Immune to Brief Input Transients
- Teeny 5-Pin SC-70 Package
- 6-Pin 1.6 mm x 1.6 mm TDFN (MIC841)
- 4-Pin 1.2 mm x 1.6 mm TDFN (MIC842)

#### **Applications**

- Smartphones
- PDAs
- · Precision Battery Monitoring
- · Battery Chargers

#### **General Description**

The MIC841 and MIC842 are micro-power, precision-voltage comparators with an on-chip voltage reference.

Both devices are intended for voltage monitoring applications. External resistors are used to set the voltage monitor threshold. When the threshold is crossed, the outputs switch polarity.


The MIC842 incorporates a voltage reference and comparator with fixed internal hysteresis; two external resistors are used to set the switching threshold voltage. The MIC841 provides a similar function with user adjustable hysteresis; this part requires three external resistors to set the upper and lower thresholds (the difference between the threshold voltages being the hysteresis voltage).

Both the MIC841 and MIC842 are available with push-pull or open-drain output stage. The push-pull output stage is configured either active-high or active-low; the open-drain output stage is only configured active-low.


Supply current is extremely low (1.5  $\mu$ A, typical), making it ideal for portable applications.


The MIC841/2 is supplied in the Teeny 5-pin SC-70, 6-pin 1.6 mm × 1.6 mm Thin DFN (MIC841), and 4-pin 1.2 mm × 1.6 mm Thin DFN (MIC842) packages.

## Package Types



## **Typical Application Circuits**





#### 1.0 FUNCTIONAL BLOCK DIAGRAMS

Note: Block diagrams show SC-70 package pin numbers.




FIGURE 1-1: MIC841H Block Diagram




FIGURE 1-2: MIC841L Block Diagram




FIGURE 1-3: MIC841N Block Diagram




FIGURE 1-4: MIC842H Block Diagram




FIGURE 1-5: MIC842L Block Diagram




FIGURE 1-6: MIC842N Block Diagram

#### 2.0 ELECTRICAL CHARACTERISTICS

#### **Absolute Maximum Ratings †**

Supply Voltage ( $V_{DD}$ )	+7V ±20 mA
Operating Ratings ‡	
Supply Voltage (V <sub>DD</sub> )	+1.5V to +5.5V
Input Voltage (V <sub>INP</sub> , V <sub>ITH</sub> , V <sub>HTH</sub> )	0V to +6V
V <sub>OUT</sub> ('H' and 'L' versions)	V <sub>DD</sub>
V <sub>OUT</sub> ('N' version)	

**† Notice:** Stresses above those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operational sections of this specification is not intended. Exposure to maximum rating conditions for extended periods may affect device reliability.

**‡ Notice:** The device is not guaranteed to function outside its operating ratings.

**Note 1:** Devices are ESD sensitive. Handling precautions are recommended. Human body model, 1.5 k $\Omega$  in series with 100 pF.

TABLE 2-1: ELECTRICAL CHARACTERISTICS

Electrical Characteristics: $1.5\text{V} \le \text{V}_{DD} \le 5.5\text{V}$ ; $\text{T}_{A} = 25^{\circ}\text{C}$ . $-40^{\circ}\text{C} \le \text{T}_{A} \le +85^{\circ}\text{C}$ , unless noted. (Note 1).							
Parameters	Min. Typ. Max.		Units	Conditions			
Supply Current (I <sub>DD</sub> )	_	1.5	3	μΑ	Output not asserted		
Input Leakage Current (I <sub>INP</sub> )	_	0.005	10	nA	_		
Reference Voltage (V <sub>REF</sub> )	1.225	1.240	1.256	V	0°C ≤ T <sub>A</sub> ≤ 85°C		
	1.219	1.240	1.261	V	–40°C ≤ T <sub>A</sub> ≤ 85°C		
Hysteresis Voltage (V <sub>HYST</sub> ) (Note 2)	8	20	35	mV	MIC842 only		
Propagation Delay (t <sub>D</sub> )	_	12	50		V <sub>INP</sub> = 1.352V to 1.128V		
	_	8	50	μs	V <sub>INP</sub> = 1.143V to 1.367V		
Output Voltage-Low (V <sub>OUT</sub> )	_	0.05	0.3		$I_{SINK}$ = 1.6 mA, $V_{DD} \ge 1.6V$		
(Note 3)	_	0.005	0.4		I <sub>SINK</sub> = 100 μA, V <sub>DD</sub> ≥ 1.2V		
Output Voltage-High (V <sub>OUT</sub> )		0.99V <sub>DD</sub>	_	V	I <sub>SOURCE</sub> = 500 μA, V <sub>DD</sub> ≥ 1.6V		
(Note 3)	_	0.99V <sub>DD</sub>			I <sub>SOURCE</sub> = 50 μA, V <sub>DD</sub> ≥ 1.2V		

Note 1: Specification for packaged product only.

2:  $V_{HTH} = V_{REF} + V_{HYST}$ .

3:  $V_{DD}$  operating range is 1.5V to 5.5V. Output is guaranteed to be de-asserted down to  $V_{DD}$  = 1.2V.

## **TEMPERATURE SPECIFICATIONS**

Parameters	Sym.	Min.	Тур.	Max.	Units	Conditions	
Temperature Ranges							
Maximum Junction Temperature	T <sub>J</sub>	_	_	+150	°C	Note 1	
Storage Temperature Range	T <sub>S</sub>	-65	_	+150	°C	_	
Ambient Temperature Range	T <sub>A</sub>	-40	_	+85	°C	_	
Lead Temperature	_	_	_	+260	°C	Soldering, 10s	
Package Thermal Resistances							
SC-70-5	$\theta_{JA}$	_	256.5	_	°C/W	_	
6-Pin 1.6 mm x 1.6 mm TDFN	$\theta_{JA}$	_	92	_	°C/W	_	
4-Pin 1.2 mm x 1.6 mm TDFN	$\theta_{JA}$	_	173	_	°C/W	_	

Note 1: The maximum allowable power dissipation is a function of ambient temperature, the maximum allowable junction temperature and the thermal resistance from junction to air (i.e., T<sub>A</sub>, T<sub>J</sub>, θ<sub>JA</sub>). Exceeding the maximum allowable power dissipation will cause the device operating junction temperature to exceed the maximum +150°C rating. Sustained junction temperatures above +150°C can impact the device reliability.

#### 3.0 PIN DESCRIPTIONS

The descriptions of the pins are listed in Table 3-1 and Table 3-2.

TABLE 3-1: MIC841 PIN FUNCTION TABLE

Pin Number SC-70	Pin Number TDFN	Symbol	Description	
1	3	HTH	High Threshold Input. HTH and LTH monitor external voltages.	
2	2	GND	Ground.	
3	1	LTH	Low Threshold Input. LTH and HTH monitor external voltages.	
		OUT	("H" Version) Active-Low Push-Pull Output. OUT asserts low when $V_{\rm LTH}$ < $V_{\rm REF}$ . OUT remains low until $V_{\rm HTH}$ > $V_{\rm REF}$ .	
4	6	OUT	("L" Version) Active-High Push-Pull Output. OUT asserts high when $V_{\rm LTH}$ < $V_{\rm REF}$ . OUT remains high until $V_{\rm HTH}$ > $V_{\rm REF}$ .	
		OUT	("N" Version) Active-Low, Open-Drain Output. OUT asserts low when V <sub>LTH</sub> < V <sub>REF</sub> . OUT remains low until V <sub>HTH</sub> > V <sub>REF</sub> .	
5	4	VDD	Power Supply Input.	
_	5	NC	No Connect. Not internally connected.	
_	EP	ePAD	Heatsink Pad. Connect to GND for best thermal performance.	

TABLE 3-2: MIC842 PIN FUNCTION TABLE

Pin Number SC-70	Pin Number TDFN	Symbol	Description	
1	3	INP	Threshold Input. INP monitors an external voltage.	
2	2	GND	Ground.	
3	_	NC	No Connect. Not internally connected.	
		OUT	("H" Version) Active-Low, Push-Pull Output. OUT asserts low when $V_{INP}$ < $V_{REF}$ . OUT remains low until $V_{INP}$ > ( $V_{REF}$ + $V_{HYST}$ ).	
4	1	OUT	("L" Version) Active-High, Push-Pull Output. OUT asserts high when $V_{INP}$ < $V_{REF}$ . OUT remains high until $V_{INP}$ > ( $V_{REF}$ + $V_{HYST}$ ).	
		OUT	("N" Version) Active-Low, Open-Drain Output. OUT asserts low when $V_{INP}$ < $V_{REF}$ . OUT remains low until $V_{INP}$ > ( $V_{REF}$ + $V_{HYST}$ ).	
5	4	VDD	Power Supply Input.	
_	EP	ePAD	Heatsink Pad. Connect to GND for best thermal performance.	

#### 4.0 APPLICATION INFORMATION

#### 4.1 Output

The MIC841N and MIC842N outputs are an open-drain MOSFET, so most applications will require a pull-up resistor. The value of the resistor should not be too large or leakage effects may dominate. 470 k $\Omega$  is the maximum recommended value. Note that the output of the "N" version may be pulled up as high as 6V regardless of the IC's supply voltage. The "H" and "L" versions of the MIC841 and MIC842 have a push-pull output stage with a diode clamped to  $V_{DD}$ . Thus, the maximum output voltage of the "H" and "L" versions is  $V_{DD}$  (see Table 2-1).

When working with large resistors on the input to the devices, a small amount of leakage current can cause voltage offsets that degrade system accuracy. The maximum recommended total resistance from  $V_{\text{IN}}$  to ground is 3  $\mathrm{M}\Omega.$  The accuracy of the resistors can be chosen based upon the accuracy required by the system. The inputs may be subjected to voltages as high as 6V steady-state without adverse effects of any kind regardless of the IC's supply voltage. This applies even if the supply voltage is zero. This permits the situation in which the IC's supply is turned off, but voltage is still present on the inputs (see Table 2-1).

# 4.2 Programming the MIC841 Thresholds

The low-voltage threshold is calculated using Equation 4-1.

#### **EQUATION 4-1:**

$$V_{IN(LO)} = V_{REF} \times \left(\frac{R1+R2+R3}{R2+R3}\right)$$
 Where: 
$$V_{REF} = 1.240 V$$

The high-voltage threshold is calculated using Equation 4-2.

#### **EQUATION 4-2:**

$$V_{IN(HI)} = V_{REF} \times \left(\frac{R1+R2+R3}{R3}\right)$$
 Where: 
$$V_{REF} = 1.240 V$$

In order to provide the additional criteria needed to solve for the resistor values, the resistors can be selected such that they have a given total value, that is, R1 + R2 + R3 =  $R_{TOTAL}$ . A value such as 1  $M\Omega$  for  $R_{TOTAL}$  is a reasonable value because it draws minimum current but has no significant effect on accuracy.




FIGURE 4-1:

MIC841 Example Circuit

Once the desired trip points are determined, set the  $V_{\text{IN(HI)}}$  threshold first.

For example, use a total of 1 M $\Omega$  = R1 + R2 + R3. For a typical single-cell lithium ion battery, 3.6V is a good "high threshold" because at 3.6V the battery is moderately charged. Solving for R3:

#### **EQUATION 4-3:**

$$V_{IN(HI)} = 3.6V = 1.24V \bigg(\frac{1M\Omega}{R3}\bigg)$$
 Solve: R3 344 k $\Omega$ 

Once R3 is determined, the equation for  $V_{IN(LO)}$  can be used to determine R2. A single lithium-ion cell, for example, should not be discharged below 2.5V. Many applications limit the drain to 3.1V.

Using 3.1V for the  $V_{\text{IN(LO)}}$  threshold allows the calculation of the two remaining resistor values.

#### **EQUATION 4-4:**

$$V_{IN(LO)} = 3.1V = 1.24V \bigg(\frac{1M\Omega}{R2+344k\Omega}\bigg)$$
 Solve: 
$$R2 \qquad 56 \text{ k}\Omega$$
 
$$R1 \qquad 1 \text{ M}\Omega - R2 - R3$$
 
$$R1 \qquad 600 \text{ k}\Omega$$

The accuracy of the resistors can be chosen based upon the accuracy required by the system.




FIGURE 4-2: Hysteresis

Output Response and

#### nysieresis

# 4.3 Programming the MIC842 Thresholds

The voltage threshold is calculated using Equation 4-5.

#### **EQUATION 4-5:**

$$V_{IN(LO)} = V_{REF} \! \left( \! rac{R1+R2}{R2} \! 
ight)$$
 Where:  $V_{\rm REF} = 1.240 {
m V}$ 




FIGURE 4-3: MIC842 Example Circuit

In order to provide the additional criteria needed to solve for the resistor values, the resistors can be selected such that they have a given total value, that is, R1 + R2 =  $R_{TOTAL}.$  A value such as 1  $M\Omega$  for  $R_{TOTAL}$  is a reasonable value because it draws minimum current, but has no significant effect on accuracy.

#### 4.4 Input Transients

The MIC841/2 is inherently immune to very short negative-going "glitches." Very brief transients may exceed the  $V_{\text{IN(LO)}}$  threshold without tripping the output.

As shown in Figure 4-4, the narrower the transient, the deeper the threshold overdrive that will be ignored by the MIC841/2. The graph represents the typical allowable transient duration for a given amount of threshold overdrive that will not generate an output.




FIGURE 4-4: Input Transient Response

#### 5.0 PACKAGING INFORMATION

#### 5.1 Package Marking Information

5-Pin SC-70\*

Example



Device	Marking
MIC841H	<u>B1</u> 3
MIC841L	<u>B1</u> 4
MIC841N	<u>B1</u> 5
MIC842H	<u>B1</u> 6
MIC842L	<u>B</u> 17
MIC842N	<u>B1</u> 8

<u>B1</u>4 408

4-Pin TDFN\* 6-Pin TDFN\*

Example



Device	Marking
MIC841H	ВН
MIC841L	BL
MIC841N	BN
MIC842H	НВ
MIC842L	HL
MIC842N	HN

**▲** BL

**Legend:** XX...X Product code or customer-specific information

Y Year code (last digit of calendar year)
YY Year code (last 2 digits of calendar year)
WW Week code (week of January 1 is week '01')

NNN Alphanumeric traceability code

(e3) Pb-free JEDEC® designator for Matte Tin (Sn)


This package is Pb-free. The Pb-free JEDEC designator (e3) can be found on the outer packaging for this package.

•, ▲, ▼ Pin one index is identified by a dot, delta up, or delta down (triangle mark).


**Note**: In the event the full Microchip part number cannot be marked on one line, it will be carried over to the next line, thus limiting the number of available characters for customer-specific information. Package may or may not include the corporate logo.

Underbar (\_) and/or Overbar (¯) symbol may not be to scale.


#### 5 Lead SC70 Package Outline and Recommended Land Pattern



#### 6-Lead 1.6 mm x 1.6 mm Package Outline and Recommended Land Pattern



#### 4-Lead 1.2 mm x 1.6 mm Package Outline and Recommended Land Pattern



**NOTES:** 

## **APPENDIX A: REVISION HISTORY**

## **Revision A (April 2017)**

- Converted Micrel data sheet MIC841/2 to Microchip data sheet DS20005758A.
- Minor grammatical corrections throughout.

NOTES:

## PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, contact your local Microchip representative or sales office.

DARTA	10 V	V VV VV	Examples:			
PART N Device	T	X XX -XX       ut Temp. Package Media e Type	a)	MIC841HYC5-T5:	Comparator with 1.25% Reference and Adjustable Hysteresis, Push-Pull, Active-Low, –40°C to	
Device:	MIC841: MIC842:	Adjustable Hysteresis	b)	MIC841LYMT-TR:	+85°C Temperature Range, SC-70-5 Pack- age, 500/Reel Comparator with 1.25%	
Output Stage:	H = L = N =	Push-Pull, Active-Low Push-Pull, Active-High Open-Drain, Active-Low			Reference and Adjustable Hysteresis, Push-Pull, Active-High, –40°C to +85°C Temperature Range, 1.6 mm x 1.6 mm TDFN Package, 5,000/	
Temperature:	Y =	-40°C to +85°C	c)	MIC841NYC5-T5:	Reel Comparator with 1.25% Reference and Adjustable	
Package:	C5 = MT = MT =	SC-70-5 1.6 mm x 1.6 mm TDFN (MIC841 Only) 1.2 mm x 1.6 mm TDFN (MIC842 Only)			Hysteresis, Open-Drain, Active-Low, –40°C to +85°C Temperature Range, SC-70-5 Pack- age, 500/Reel	
Media Type	T5 = TR =	500/Reel 5,000/Reel	d)	MIC842HYMT-T5:	Comparator with 1.25% Reference and Internal Fixed Hysteresis, Push- Pull, Active-Low, –40°C to +85°C Temperature Range, 1.2 mm x 1.6 mm	
			e)	MIC842LYC5-TR:	TDFN Package, 500/Reel Comparator with 1.25% Reference and Internal Fixed Hysteresis, Push- Pull, Active-High, –40°C to +85°C Temperature Range, SC-70-5 Pack- age, 5,000/Reel	
			f)	MIC842NYMT-TR:	Comparator with 1.25% Reference and Internal Fixed Hysteresis, Open- Drain, Active-Low, -40°C to +85°C Temperature Range, 1.2 mm x 1.6 mm TDFN Package, 5,000/ Reel	

NOTES:

#### Note the following details of the code protection feature on Microchip devices:

- · Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these methods, to our knowledge, require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Most likely, the person doing so is engaged in theft of intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not mean that we are guaranteeing the product as "unbreakable."

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Microchip received ISO/TS-16949:2009 certification for its worldwide headquarters, design and wafer fabrication facilities in Chandler and Tempe, Arizona; Gresham, Oregon and design centers in California and India. The Company's quality system processes and procedures are for its PIC® MCUs and dsPIC® DSCs, KEELOQ® code hopping devices, Serial EEPROMs, microperipherals, nonvolatile memory and analog products. In addition, Microchip's quality system for the design and manufacture of development systems is ISO 9001:2000 certified.

# QUALITY MANAGEMENT SYSTEM CERTIFIED BY DNV = ISO/TS 16949=

#### **Trademarks**

The Microchip name and logo, the Microchip logo, AnyRate, dsPIC, FlashFlex, flexPWR, Heldo, JukeBlox, KeeLoq, KeeLoq logo, Kleer, LANCheck, LINK MD, MediaLB, MOST, MOST logo, MPLAB, OptoLyzer, PIC, PICSTART, PIC32 logo, RightTouch, SpyNIC, SST, SST Logo, SuperFlash and UNI/O are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

ClockWorks, The Embedded Control Solutions Company, ETHERSYNCH, Hyper Speed Control, HyperLight Load, IntelliMOS, mTouch, Precision Edge, and QUIET-WIRE are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, BodyCom, chipKIT, chipKIT logo, CodeGuard, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, EtherGREEN, In-Circuit Serial Programming, ICSP, Inter-Chip Connectivity, JitterBlocker, KleerNet, KleerNet logo, MiWi, motorBench, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PureSilicon, RightTouch logo, REAL ICE, Ripple Blocker, Serial Quad I/O, SQI, SuperSwitcher, SuperSwitcher II, Total Endurance, TSHARC, USBCheck, VariSense, ViewSpan, WiperLock, Wireless DNA, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

 $\ensuremath{\mathsf{SQTP}}$  is a service mark of Microchip Technology Incorporated in the U.S.A.

Silicon Storage Technology is a registered trademark of Microchip Technology Inc. in other countries.

GestIC is a registered trademarks of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2017, Microchip Technology Incorporated, Printed in the U.S.A., All Rights Reserved.

ISBN: 978-1-5224-1663-0



## Worldwide Sales and Service

#### **AMERICAS**

**Corporate Office** 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200

Fax: 480-792-7277 **Technical Support:** 

http://www.microchip.com/ support

Web Address:

www.microchip.com Atlanta

Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

Austin, TX Tel: 512-257-3370

**Boston** 

Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL

Tel: 630-285-0071 Fax: 630-285-0075

**Dallas** 

Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

Detroit Novi, MI

Tel: 248-848-4000

Houston, TX Tel: 281-894-5983

Indianapolis

Noblesville, IN Tel: 317-773-8323 Fax: 317-773-5453 Tel: 317-536-2380

Los Angeles Mission Viejo, CA

Tel: 949-462-9523 Fax: 949-462-9608 Tel: 951-273-7800

Raleigh, NC Tel: 919-844-7510

New York, NY

Tel: 631-435-6000

San Jose, CA Tel: 408-735-9110 Tel: 408-436-4270

Canada - Toronto Tel: 905-695-1980 Fax: 905-695-2078

#### ASIA/PACIFIC

**Asia Pacific Office** Suites 3707-14, 37th Floor Tower 6, The Gateway

Harbour City, Kowloon

Hong Kong Tel: 852-2943-5100 Fax: 852-2401-3431

Australia - Sydney Tel: 61-2-9868-6733 Fax: 61-2-9868-6755

China - Beijing Tel: 86-10-8569-7000 Fax: 86-10-8528-2104

China - Chengdu Tel: 86-28-8665-5511 Fax: 86-28-8665-7889

China - Chongqing Tel: 86-23-8980-9588 Fax: 86-23-8980-9500

China - Dongguan Tel: 86-769-8702-9880

China - Guangzhou Tel: 86-20-8755-8029

China - Hangzhou Tel: 86-571-8792-8115 Fax: 86-571-8792-8116

China - Hong Kong SAR Tel: 852-2943-5100 Fax: 852-2401-3431

China - Nanjing Tel: 86-25-8473-2460 Fax: 86-25-8473-2470

China - Qingdao Tel: 86-532-8502-7355 Fax: 86-532-8502-7205

China - Shanghai Tel: 86-21-3326-8000

Fax: 86-21-3326-8021

China - Shenyang Tel: 86-24-2334-2829 Fax: 86-24-2334-2393

China - Shenzhen Tel: 86-755-8864-2200 Fax: 86-755-8203-1760

China - Wuhan Tel: 86-27-5980-5300 Fax: 86-27-5980-5118

China - Xian Tel: 86-29-8833-7252 Fax: 86-29-8833-7256

#### ASIA/PACIFIC

China - Xiamen Tel: 86-592-2388138 Fax: 86-592-2388130

China - Zhuhai Tel: 86-756-3210040 Fax: 86-756-3210049

India - Bangalore Tel: 91-80-3090-4444 Fax: 91-80-3090-4123

India - New Delhi Tel: 91-11-4160-8631 Fax: 91-11-4160-8632

India - Pune Tel: 91-20-3019-1500

Japan - Osaka Tel: 81-6-6152-7160 Fax: 81-6-6152-9310

Japan - Tokyo Tel: 81-3-6880- 3770 Fax: 81-3-6880-3771

Korea - Daegu Tel: 82-53-744-4301 Fax: 82-53-744-4302

Korea - Seoul Tel: 82-2-554-7200 Fax: 82-2-558-5932 or 82-2-558-5934

Malaysia - Kuala Lumpur Tel: 60-3-6201-9857 Fax: 60-3-6201-9859

Malaysia - Penang Tel: 60-4-227-8870 Fax: 60-4-227-4068

Philippines - Manila Tel: 63-2-634-9065 Fax: 63-2-634-9069

Singapore

Tel: 65-6334-8870 Fax: 65-6334-8850

Taiwan - Hsin Chu Tel: 886-3-5778-366 Fax: 886-3-5770-955

Taiwan - Kaohsiung Tel: 886-7-213-7830

Taiwan - Taipei Tel: 886-2-2508-8600 Fax: 886-2-2508-0102

Thailand - Bangkok Tel: 66-2-694-1351 Fax: 66-2-694-1350

#### **EUROPE**

Austria - Wels Tel: 43-7242-2244-39 Fax: 43-7242-2244-393

Denmark - Copenhagen Tel: 45-4450-2828 Fax: 45-4485-2829

Finland - Espoo Tel: 358-9-4520-820

France - Paris Tel: 33-1-69-53-63-20 Fax: 33-1-69-30-90-79

France - Saint Cloud Tel: 33-1-30-60-70-00

Germany - Garching Tel: 49-8931-9700 Germany - Haan Tel: 49-2129-3766400

Germany - Heilbronn Tel: 49-7131-67-3636

Germany - Karlsruhe Tel: 49-721-625370

Germany - Munich Tel: 49-89-627-144-0 Fax: 49-89-627-144-44

Germany - Rosenheim Tel: 49-8031-354-560

Israel - Ra'anana Tel: 972-9-744-7705

Italy - Milan Tel: 39-0331-742611 Fax: 39-0331-466781

Italy - Padova Tel: 39-049-7625286

Netherlands - Drunen Tel: 31-416-690399 Fax: 31-416-690340

Norway - Trondheim Tel: 47-7289-7561

Poland - Warsaw Tel: 48-22-3325737

Romania - Bucharest Tel: 40-21-407-87-50

Spain - Madrid Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

Sweden - Gothenberg Tel: 46-31-704-60-40

Sweden - Stockholm Tel: 46-8-5090-4654

**UK - Wokingham** Tel: 44-118-921-5800 Fax: 44-118-921-5820