

P/N: L-53SGD-12V

SUPER BRIGHT GREEN


Features

- LOW POWER CONSUMPTION.
- POPULAR T-1 3/4 DIAMETER PACKAGE.
- GENERAL PURPOSE LEADS.
- RELIABLE AND RUGGED.
- LONG LIFE - SOLID STATE RELIABILITY.
- AVAILABLE ON TAPE AND REEL.
- 12V INTERNAL RESISTOR.
- RoHS COMPLIANT.

Description

The Super Bright Green source color devices are made with Gallium Phosphide Green Light Emitting Diode.

Package Dimensions



Notes:

1. All dimensions are in millimeters (inches).
2. Tolerance is $\pm 0.25(0.01)$ unless otherwise noted.
3. Lead spacing is measured where the leads emerge from the package.
4. Specifications are subject to change without notice.

Selection Guide

Part No.	Dice	Lens Type	Iv (mcd) [2] V=12V		Viewing Angle [1]
			Min.	Typ.	2 θ 1/2
L-53SGD-12V	SUPER BRIGHT GREEN (GaP)	GREEN DIFFUSED	8	20	60°

Notes:

1. θ 1/2 is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.
2. Luminous Intensity / Luminous Flux: +/-15%.

Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Typ.	Max.	Units	Test Conditions
λ_{peak}	Peak Wavelength	Super Bright Green	565		nm	VF=12V
λ_D [1]	Dominant Wavelength	Super Bright Green	568		nm	VF=12V
$\Delta\lambda_{1/2}$	Spectral Line Half-width	Super Bright Green	30		nm	VF=12V
IF	Forward Current	Super Bright Green	8.5	11.5	mA	VF=12V
IR	Reverse Current	Super Bright Green		10	uA	VR= 5V

Note:


1. Wavelength: +/-1nm.

Absolute Maximum Ratings at TA=25°C

Parameter	Super Bright Green	Units
Power dissipation	120	mW
Forward Voltage	14	V
Reverse Voltage	5	V
Operating Temperature	-40°C To +70°C	
Storage Temperature	-40°C To +85°C	
Lead Solder Temperature[1]	260°C For 3 Seconds	
Lead Solder Temperature[2]	260°C For 5 Seconds	

Notes:

- 1.2mm below package base.
- 2.5mm below package base.



Super Bright Green

L-53SGD-12V

