







LOC		DIST		REVISIONS					
CM	00	P	LTR	DESCRIPTION			DATE	DWN	APVD
			AN2	REVISED PER ECO-11-004587			11MAR11	RK	HMR
			AN3	REVISED PER ECR-14-002588			06MAR14	AV	KD


1. MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK PLUG.
2. RECOMMENDED PANEL THICKNESS 0.76 - 2.29.
3. PANEL MUST BE PUNCHED SO THAT THE HOUSING ENTERS THE PANEL IN THE SAME DIRECTION AS THE PUNCH.
4. OPTIONAL FOR KEYING HOUSING IN PANEL.
5. CIRCUIT NUMBER 1 LOCATION.
6. DIMENSION INDICATED IS AS MOLDED. ADDITIONAL GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR.
7. FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION. NO RIBS OR SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, OPTIONAL.
8. UNDERWRITERS RECOGNIZED COMPONENT LOGO AND CSA CERTIFICATION LOGO TO BE LOCATED ONCE EACH ON SIDE OF HOUSING.
9. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



DETAIL A
OPTIONAL CONSTRUCTIONS



RECOMMENDED PANEL CUT OUT



3-DIMENSIONAL MODEL
NTS

4.45	.175	27.43	1.080
2.79	.110	20.70	.815
2.54	.100	20.32	.800
2.41	.095	13.46	.530
2.29	.090	13.21	.520
0.76	.030	8.64	.340
0.38	.015	8.13	.320
0.25	.010	7.62	.300
0.13	.005	6.35	.250
MM	IN	MM	IN

CONVERSION TABLE


BLACK	1-480701-9
GRAY	1-480701-8
BLUE	1-480701-6
GREEN	1-480701-5
YELLOW	1-480701-4
ORANGE	1-480701-3
RED	1-480701-2
BROWN	1-480701-1
NATURAL	1-480701-0
COLOR	PART NO.

9. OBSOLETE





THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 28JUL2004	 TE Connectivity					
DIMENSIONS: mm		CHK S. RIDGILL 28JUL2004						
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CAP, 3 CIRCUIT, UNIVERSAL MATE-N-LOK(TM)	RESTRICTED TO				
	0.13	±			APVD S. RIDGILL 28JUL2004			
	0.13	±			PRODUCT SPEC			
	0.13	±			APPLICATION SPEC			
	0.13	±			—			
MATERIAL NYLON, UL94V-2		FINISH —	SIZE A1	CAGE CODE 00779	DRAWING NO C480701	SCALE 4:1	SHEET 1 OF 2	REV AN3

METRIC

LOC	DIST	REVISIONS				
CM	00	P	LTR	DESCRIPTION	DATE	APVD
		-	-	SEE SHEET 1	-	-




- 1 . STAMP NUMBERS 3.18 HIGH AT WIRE END OF HOUSING (12 POINT DAVID TYPE).
- 2 . CHARACTERS TO BE STAMPED ON HOUSING IN A MANNER AS TO BE READ FROM WIRE END ONLY.
- 3 . VIOLET, BLACK, BROWN AND BLUE COLORED BLOCKS TO BE STAMPED WITH WHITE CHARACTERS. ALL OTHER COLORED BLOCKS TO BE STAMPED WITH BLACK CHARACTERS.



5.59	.220	-	-
4.70	.185	27.43	1.080
3.18	.125	20.32	.800
0.38	.015	13.21	.520
0.25	.010	8.13	.320
0.13	.005	7.62	.300
MM	IN	MM	IN

CONVERSION TABLE



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES
FINISH

± -
± -
± 0.13
± -
± -
± 0°30'

-

DWN
K. WHITAKER
28JUL2004

CHK
S. RIDGILL
28JUL2004

APVD
S. RIDGILL
28JUL2004

TE Connectivity

CAP,
3 CIRCUIT,
UNIVERSAL MATE-N-LOK(TM)

SIZE
A1

CAGE CODE
00779

DRAWING NO
480701

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
4:1

SHEET
2

OF
2

REV
AN2