

Features

Unregulated Converters

- UL/CSA and EN Safety certified
- EN-60601 for Medical Applications
- Isolation 6.4kVDC
- Optional Continuous Short Circuit Protected
- /X2 Option for >9mm Input/Output Clearance
- Suitable for IGBT Applications

Selection Guide

Part Number SIP 7	Input Voltage (VDC)	Output Voltage (VDC)	Output Current (mA)	Efficiency Std (%)	Max Capacitive Load ⁽¹⁾
RxxP3.3S	5, 9, 12, 15, 24	3.3	303	70	2200µF
RxxP05S	5, 9, 12, 15, 24	5	200	70-75	1000µF
RxxP09S	5, 9, 12, 15, 24	9	111	70-75	1000µF
RxxP12S	5, 9, 12, 15, 24	12	84	70-75	470µF
RxxP15S	5, 9, 12, 15, 24	15	66	75-80	470µF
RxxP3.3D	5, 9, 12, 15, 24	±3.3	±151	70	±1000µF
RxxP05D	5, 9, 12, 15, 24	±5	±100	70-75	±470µF
RxxP09D	5, 9, 12, 15, 24	±9	±55	70-75	±470µF
RxxP12D	5, 9, 12, 15, 24	±12	±41	70-75	±220µF
RxxP15D	5, 9, 12, 15, 24	±15	±33	75-80	±220µF

xx = Input Voltage. Other input and output voltage combinations available on request.

No suffix is functional isolation e.g. R05P05S

* add Suffix "P" for Continuous Short Circuit Protection, e.g. R05P05S/P, R05P05D/P

* add Suffix "/X2" for single output with alternative pinout, e.g. R05P05S/X2, R05P05S/P/X2

Specifications (measured at $T_A = 25^\circ\text{C}$, nominal input voltage, full load and after warm-up)

Input Voltage Range	±10%
Output Voltage Accuracy	±5%
Line Voltage Regulation	1.2%/1% of V_{in} typ.
Load Voltage Regulation (10% to 100% full load)	3.3, 5V output types 15% max. other output types 10% max.
Output Ripple and Noise (20MHz BW)	200mVp-p max.
Operating Frequency	20kHz min. / 50kHz typ. / 85kHz max.
Efficiency at Full Load	65% min. / 75% typ.
Minimum Load = 0%	Specifications valid for 10% minimum load only
Isolation Voltages	(tested for 1 second) 6400VDC (rated for 1 minute) 3200VAC / 60Hz
Isolation Capacitance	4pF min. / 10pF max.
Isolation Resistance	15 GΩ min.
Short Circuit Protection	1 Second
P-Suffix	Continuous
Operating Temperature Range (free air convection)	-40°C to +85°C (see Graph)
Storage Temperature Range	-55°C to +125°C
Relative Humidity	95% RH
Package Weight	4.3g
Packing Quantity	25 pcs per Tube cont.

ECONOLINE


DC/DC-Converter

with 3 year Warranty

RECOM

1 Watt

SIP 7 Single & Dual Output



EN-60950-1 Certified

EN-60601-1 Certified

UL/CSA 60950-1 Certified


IEC 60601-1 CB Report

RxxPxx

Description


The RxxPxxS_D Series of DC/DC Converters are certified to UL/CSA-60950. This makes them ideal for medical and safety applications where approved isolation is required.

Derating-Graph (Ambient Temperature)



Refer to Application Notes

Tolerance Envelope



Specifications (continued)



MTBF (+25°C)	Detailed Information see Application Notes chapter "MTBF"	using MIL-HDBK 217F	2974 x 10 ³ hours
(+85°C)		using MIL-HDBK 217F	728 x 10 ³ hours
Certifications	UL/cUL General Safety EN General Safety CB/EN Medical Safety	Report: E358085 Report: PS-R7219C1 Report: MDD1205098-4 + RM1205098-4 Medical Report + ISO14971 Risk Assessment	UL 60950-1 1st Ed. EN60950-1:2001 + A11: 2004 IEC/EN 60601-1 3rd Edition

Notes



Note 1 Maximum capacitive load is defined as the capacitive load that will allow start up in under 1 second without damage to the converter.

Typical Characteristics



RxxP05/09S





RxxP05/09D



RxxP12/15S







RxxP12/15D




Package Style and Pinning (mm)

7 PIN SIP Package


3rd angle projection






Dual Output



Single Output



Recommended Footprint Details



Pin Connections

Pin #	Single	Dual	/X2
1	+Vin	+Vin	+Vin
2	-Vin	-Vin	-Vin
5	-Vout	-Vout	No Pin
6	No Pin	Com	-Vout
7	+Vout	+Vout	+Vout

XX.X $\pm$ 0.5 mm

XX.XX $\pm$ 0.25 mm