




N-Channel 30-V (D-S) MOSFET with Schottky Diode


MOSFET PRODUCT SUMMARY		
V_{DS} (V)	$r_{DS(on)}$ (Ω)	I_D (A)
30	0.018 @ $V_{GS} = 10$ V	9
	0.028 @ $V_{GS} = 4.5$ V	7.3

SCHOTTKY PRODUCT SUMMARY		
V_{DS} (V)	V_{SD} (V) Diode Forward Voltage	I_F (A)
30	0.50 V @ 1.0 A	1.4



Ordering Information:

Si4812DY
Si4812DY-T1 (with Tape and Reel)
Si4812DY—E3 (Lead (Pb)-Free)
Si4812DY-T1—E3 (Lead (Pb)-Free with Tape and Reel)



ABSOLUTE MAXIMUM RATINGS (T _A = 25°C UNLESS OTHERWISE NOTED)					
Parameter		Symbol	Limit		Unit
			10 sec	Steady State	
Drain-Source Voltage (MOSFET)		V _{DS}	30		V
Reverse Voltage (Schottky)			30		
Gate-Source Voltage (MOSFET)		V _{GS}	± 20		
Continuous Drain Current (T _J = 150°C) (MOSFET) ^{a, b}	T _A = 25°C	I _D	9	6.9	A
	T _A = 70°C		7.5	5.6	
Pulsed Drain Current (MOSFET)		I _{DM}	50		
Continuous Source Current (MOSFET Diode Conduction) ^{a, b}		I _S	2.1	1.2	
Average Foward Current (Schottky)		I _F	1.4	0.8	
Pulsed Foward Current (Schottky)		I _{FM}	30		
Maximum Power Dissipation (MOSFET) ^{a, b}	T _A = 25°C	P _D	2.5	1.4	W
	T _A = 70°C		1.6	0.9	
Maximum Power Dissipation (Schottky) ^{a, b}	T _A = 25°C		2.0	1.2	
	T _A = 70°C		1.3	0.8	
Operating Junction and Storage Temperature Range		T _J , T _{stg}	–55 to 150		°C

THERMAL RESISTANCE RATINGS					
Parameter	Device	Symbol	Typical	Maximum	Unit
Maximum Junction-to-Ambient ($t \leq 10$ sec) ^a	MOSFET	R_{thJA}	40	50	$^\circ\text{C/W}$
	Schottky		50	60	
Maximum Junction-to-Ambient ($t = \text{steady state}$) ^a	MOSFET		72	90	
	Schottky		85	100	

Notes

a. Surface Mounted on FR4 Board.

b. $t \leq 10$ sec.

For SPICE model information via the Worldwide Web: <http://www.vishay.com/www/product/spice.htm>







MOSFET + SCHOTTKY SPECIFICATIONS (T _J = 25 °C UNLESS OTHERWISE NOTED)						
Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Static						
Gate Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = 250 μA	1		3	V
Gate-Body Leakage	I _{GSS}	V _{DS} = 0 V, V _{GS} = ± 20 V			± 100	nA
Zero Gate Voltage Drain Current (MOSFET + Schottky)	I _{DSS}	V _{DS} = 30 V, V _{GS} = 0 V		0.004	0.100	mA
		V _{DS} = 30 V, V _{GS} = 0 V, T _J = 100°C		0.7	10	
		V _{DS} = 30 V, V _{GS} = 0 V, T _J = 125°C		3.0	20	
On-State Drain Current ^a	I _{D(on)}	V _{DS} ≥ 5 V, V _{GS} = 10 V	20			A
Drain-Source On-State Resistance ^a	r _{DS(on)}	V _{GS} = 10 V, I _D = 9 A		0.012	0.018	Ω
		V _{GS} = 4.5 V, I _D = 7.3 A		0.019	0.028	
Forward Transconductance ^a	g _{fs}	V _{DS} = 15 V, I _D = 9 A		23		S
Schottky Diode Forward Voltage ^a	V _{SD}	I _S = 1.0 A, V _{GS} = 0 V		0.45	0.50	V
		I _S = 1.0 A, V _{GS} = 0 V, T _J = 125°C		0.33	0.42	
Dynamic ^b						
Total Gate Charge	Q _g	V _{DS} = 15 V, V _{GS} = 5 V, I _D = 9 A		13	24	nC
Gate-Source Charge	Q _{gs}			4		
Gate-Drain Charge	Q _{gd}			5.7		
Gate Resistance	R _g		0.2		2.4	Ω
Turn-On Delay Time	t _{d(on)}	V _{DD} = 15 V, R _L = 15 Ω I _D ≅ 1 A, V _{GEN} = 10 V, R _g = 6 Ω		16	25	ns
Rise Time	t _r			10	20	
Turn-Off Delay Time	t _{d(off)}			35	50	
Fall Time	t _f			13	20	
Source-Drain Reverse Recovery Time	t _{rr}	I _F = 1.0 A, di/dt = 100 A/μs		35	70	

Notes






- a. Pulse test; pulse width $\leq 300\ \mu\text{s}$, duty cycle $\leq 2\%$.
b. Guaranteed by design, not subject to production testing.



TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)




TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)





TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)





Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[SI4812DY-T1](#) [SI4812DY-T1-E3](#) [SI4812DY-E3](#) [SI4812DY](#)