



RECOMMENDED PANEL LAYOUT



NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NO'S FOR REFERENCE ONLY
4. RATING: 3A@ 125VAC; 1.5A @250VAC
5. CONTACT RESISTANCE:
50mILLI-OHMS max.
6. INSULATION RESISTANCE:
500V 100Mega-OHMS min.
7. DIELECTRIC STENGTH:
1000V 1minute



C	14259	CORRECT CIRCUIT DIAGRAM	8/24/04	AR	 PS 1024A (w/no cap)				
B	12574	ADD COMPONENT	11/18/02	CJB					
A	12105	RELEASED FOR PRODUCTION	5/1/02	CJB					
REV.	ECN No.	DESCRIPTION	DATE	CHKD					
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED									
					SCALE	DATE	DR	DWG	REV
					1.5:1	5/1/02	CJB	F010244	C