





MARKETING SALES DRAWING
 DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
 DIMENSIONS IN METRIC []

This drawing is the property of Tusonix, Inc., and may not be used, reproduced, published or disclosed to others without expressed authorization by Tusonix Inc.

Electrical Testing
 per Tusonix standard
 test plans and Mil-Std-202
 Test Methods.



NOTES:

1. INDUCTANCE TO BE 0.1 μ H MINIMUM.
2. PACKAGE: BULK OR BLISTER TAPE TO IEC-60286-3 TYPE II AND EIA-481-A.
3. TUSONIX STANDARD PART NUMBER: 4700-056.
 TUSONIX RoHS COMPLIANT PART NUMBER: 4700-056 LF.
 CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
4. PART MARKING - STANDARD PART: NO MARKING.
 RoHS PART: LABELED ON PACKAGING ONLY.
5. TERMINATION: STANDARD PART: SOLDER
 RoHS COMPLIANT PART: MATTE TIN.

CAP.		TOLERANCE	WVDC +125°C	TEST VOLTAGE	I.R.MIN. @ 100 (VDC.)	IDC	TYPICAL NO LOAD INSERTION LOSS dB AT 25°C PER MIL-STD-220		
5000 pF		-20% / +80%	100 @+85°C	300 VDC	10 G Ω	10 A	10 MHZ	100 MHZ	1 GHZ
							15	55	70
REVISION RECORD	Original Release C.O.	0		--TOLERANCES-- Unless Otherwise Specified			Title SURFACE MOUNT ROUND STYLE PI FILTER		
	ADDED NOTES 3,4 & 5. S.M. 06-09-05	14		DECIMAL ± .005 [0.12]			Drawn FG 9-9-94		
	ADDED PROPERTY NOTE. REVISED NOTES 2. S.M. 03-09-07	15		ANGLES ± 			Scale 10 X		
	20050607-6-02			TUSONIX TUCSON, ARIZONA			Approved NV 9-9-94		
	20070301-1-19						A 4700-056		