

Solenoids

Series 41 Small, powerful, high force/stroke ratio solenoid



GENERAL DESCRIPTION

AC & DC types



Pull & thrust versions

Shading ring for quiet AC operation

PERFORMANCE

ELECTRICAL	Item	Specification
	Maximum Ontime	See table below
	Closed power (continuous rating)	AC: 10.5VA DC: 6.5W
	Maximum permissible voltage	240V
MECHANICAL	Insulation	All coils tested to frame at 1500V RMS 50Hz
	Weight	142g Plunger: 35g
	Ambient temperature	The information given on this page is based on room temperature of 20 C allowing for a nominal 75 C temperature rise in coil.
	Force/Stroke curve	These force curves show average performance only. In addition to normal manufacturing tolerances, deviations can be expected at some voltages due to the coil winding tolerances.
	Approvals	Solenoids which are approved to the Canadian Standards Association requirements can be supplied if specified

FORCE/STROKE CURVES & ON TIME




MAXIMUM ON TIME


	10%		25%		50%	
	1 cycle	Cont. cycle	1 cycle	Cont cycling	1 cycle	Cont. cycling
AC	50 sec	30 sec	2.75 min	1.7 min	8 min	6.25 min
DC	35 sec	20 sec	1.75 min	1 min	4.5 min	3.75 min

DIMENSIONS (mm)

PULL TYPE - SHOWN ENERGISED



PUSH TYPE - SHOWN ENERGISED



CODING

4	1	1	2	0	X	X	X	X	X	X
---	---	---	---	---	---	---	---	---	---	---

AC	1
DC	6
Pull	1
Push	2
STANDARD	0
With Push Off Spring	1

		Cont.	50%	25%	10%
COIL	24V AC 50 Hz	01	02	03	04
	50V AC 50Hz	08	09	10	11
	115V AC 50Hz	15	16	17	18
	220V AC 50Hz	23	24	25	26
	230V AC 50Hz	39	40	41	42
	115V AC 60Hz	19	20	21	22
	220V AC 60Hz	27	28	29	30
	230V AC 60Hz	43	44	45	46
	6V DC	54	55	56	57
	9V DC	58	59	60	61
	12V DC	62	63	64	65
	24V DC	72	73	74	75
	28V DC	76	77	78	79
	36V DC	80	81	82	83
	50V DC	84	85	86	87
	115V DC	88	89	90	91
	220V DC	92	93	94	95
	240V DC	96	97	98	99
Standard Leads					0
Faston Tags "250" Type					3



BLP products are designed, manufactured and tested to ISO 9001 quality standards.
BLP Reserve the right to change without prior notice the information contained in this leaflet.

BLP Components Ltd., Exning Rd, Newmarket, Suffolk CB8 0AX, England

Tel: +44 (0)1638 665161 Fax: +44 (0)1638 660718 Email: sales@blpcomp.com Website: <http://www.blpcomp.com>