

**EC2SMB-20-9.8304M** **ITEM DESCRIPTION**

Quartz Crystal Resonator HC49/UP 2 Pad Surface Mount (SMD) 4.5mm Height Metal Resistance Weld Seal 9.8304MHz  $\pm 50$ ppm at 25°C,  $\pm 100$ ppm over -40°C to +85°C 20pF Parallel Resonant

**ELECTRICAL SPECIFICATIONS**


|                               |                                                         |
|-------------------------------|---------------------------------------------------------|
| Nominal Frequency             | 9.8304MHz                                               |
| Frequency Tolerance/Stability | $\pm 50$ ppm at 25°C, $\pm 100$ ppm over -40°C to +85°C |
| Aging at 25°C                 | $\pm 5$ ppm/year Maximum                                |
| Load Capacitance              | 20pF Parallel Resonant                                  |
| Shunt Capacitance (C0)        | 7pF Maximum                                             |
| Equivalent Series Resistance  | 80 Ohms Maximum                                         |
| Mode of Operation             | AT-Cut Fundamental                                      |
| Drive Level                   | 1mWatt Maximum                                          |
| Storage Temperature Range     | -40°C to +85°C                                          |
| Insulation Resistance         | 500 Megaohms Minimum at 100Vdc                          |

**ENVIRONMENTAL & MECHANICAL SPECIFICATIONS**

|                              |                                      |
|------------------------------|--------------------------------------|
| Fine Leak Test               | MIL-STD-883, Method 1014 Condition A |
| Gross Leak Test              | MIL-STD-883, Method 1014 Condition C |
| Mechanical Shock             | MIL-STD-202, Method 213 Condition C  |
| Resistance to Soldering Heat | MIL-STD-202, Method 210              |
| Resistance to Solvents       | MIL-STD-202, Method 215              |
| Solderability                | MIL-STD-883, Method 2003             |
| Temperature Cycling          | MIL-STD-883, Method 1010             |
| Vibration                    | MIL-STD-883, Method 2007 Condition A |

# EC2SMB-20-9.8304M


## MECHANICAL DIMENSIONS (all dimensions in millimeters)



| LINE | MARKING                                                                 |
|------|-------------------------------------------------------------------------|
| 1    | <b>E9.8304M</b><br>E=Ecliptek Designator<br>M=Frequency Unit of Measure |


## Suggested Solder Pad Layout

All Dimensions in Millimeters



All Tolerances are ±0.1

## Recommended Solder Reflow Methods




### High Temperature Infrared/Convection

|                                            |                                      |
|--------------------------------------------|--------------------------------------|
| <b>Ts MAX to Tl (Ramp-up Rate)</b>         | 3°C/Second Maximum                   |
| <b>Preheat</b>                             |                                      |
| - Temperature Minimum (Ts MIN)             | 150°C                                |
| - Temperature Typical (Ts TYP)             | 175°C                                |
| - Temperature Maximum (Ts MAX)             | 200°C                                |
| - Time (ts MIN)                            | 60 - 180 Seconds                     |
| <b>Ramp-up Rate (Tl to Tp)</b>             | 3°C/Second Maximum                   |
| <b>Time Maintained Above:</b>              |                                      |
| - Temperature (Tl)                         | 217°C                                |
| - Time (tL)                                | 60 - 150 Seconds                     |
| <b>Peak Temperature (Tp)</b>               | 260°C Maximum for 10 Seconds Maximum |
| <b>Target Peak Temperature (Tp Target)</b> | 250°C +0/-5°C                        |
| <b>Time within 5°C of actual peak (tp)</b> | 20 - 40 Seconds                      |
| <b>Ramp-down Rate</b>                      | 6°C/Second Maximum                   |
| <b>Time 25°C to Peak Temperature (t)</b>   | 8 Minutes Maximum                    |
| <b>Moisture Sensitivity Level</b>          | Level 1                              |

# EC2SMB-20-9.8304M

## Recommended Solder Reflow Methods



### Low Temperature Infrared/Convection 245°C Time (t)

**Ts MAX to Tl (Ramp-up Rate)** 5°C/Second Maximum

#### Preheat

- Temperature Minimum (Ts MIN) N/A
- Temperature Typical (Ts TYP) 150°C
- Temperature Maximum (Ts MAX) N/A
- Time (ts MIN) 30 - 60 Seconds

**Ramp-up Rate (Tl to Tp)** 5°C/Second Maximum

#### Time Maintained Above:

- Temperature (Tl) 150°C
- Time (tL) 200 Seconds Maximum

**Peak Temperature (Tp)** 245°C Maximum

**Target Peak Temperature (Tp Target)** 245°C Maximum 2 Times / 230°C Maximum 1 Time

**Time within 5°C of actual peak (tp)** 10 Seconds Maximum 2 Times / 80 Seconds Maximum 1 Time

**Ramp-down Rate** 5°C/Second Maximum

**Time 25°C to Peak Temperature (t)** N/A

**Moisture Sensitivity Level** Level 1

### Low Temperature Manual Soldering

185°C Maximum for 10 Seconds Maximum, 2 times Maximum.

### High Temperature Manual Soldering

260°C Maximum for 5 Seconds Maximum, 2 times Maximum.