

BULK CABLE TIE ORDERING INFORMATION

Our Cable Tie Part Numbers are easy to understand. This chart breaks down the Cable Tie Part Numbers.

CT **18** **-** **4** **NAT** **-** **C** **-** **WR**
Family **Tensile Strength** **-** **Length** **Color** **-** **Pack Size** **-** **Options**

Family	Tensile Strength	-	Length	Color	-	Pack Size	-	Options
CT	18 lbs./80 Newtons	-	3 = 3 Inches	NAT = Natural	-	Q = 25 pieces	-	WR = Weather Resistant Black
			4 = 4 Inches	BLK = Black		L = 50 pieces		HS = Heat Stabilizer
			5 = 5 1/2 Inches	RED = Red		C = 100 pieces		FR = Fire Retardant
			8 = 8 Inches	WHT = White		M = 1000 pieces		N12 = Nylon 12
	40 lbs./178 Newtons	-	4 = 4 3/4 Inches	BLU = Blue	-		-	
			6 = 6 Inches	YEL = Yellow				
			8 = 8 Inches	GRN = Green				
			11 = 11 Inches	ORG = Orange				
	50 lbs./222 Newtons	-	14 = 14 1/2 Inches	PUR = Purple	-		-	
			4 = 4 3/4 Inches	GRY = Gray				
			6 = 6 1/4 Inches	GRN/NEON = Neon Green				
			8 = 8 Inches	PNK/NEON = Neon Pink				
	120 lbs./534 Newtons	-	11 = 11 Inches	YEL/NEON = Neon Yellow	-		-	
			14 = 14 1/2 Inches	ORG/NEON = Neon Orange				
			17 = 17 Inches	(Custom colors also available.)				
			8 = 8 Inches					
	175 lbs./778 Newtons	-	11 = 11 Inches		-		-	
			15 = 15 Inches					
			17 = 17 3/4 Inches					
			24 = 24 Inches					
		-	30 = 30 Inches		-		-	
			37 = 37 Inches					
			48 = 48 Inches					

NOTE: 18 lb tensile strength is 0.097" (2.46 mm) in width.
40 lb tensile strength is 0.135" (3.43 mm) in width.
50 lb tensile strength is 0.174" (4.42 mm) in width.
120 lb tensile strength is special order only.
175 lb tensile strength is special order only.

**Always
in Stock!**

MOST POPULAR BULK CABLE TIES



Natural

Black

Most Popular Bulk Cable Ties

Stock Bulk Cable Ties Come in Polybags in Quantities of 25, 50, 100 or 1,000 Pieces.

Retail Part No.	Strength Classification	Max. Bundle Diameter
CT18-4NAT-C	Miniature	.625 in./15.875 mm
CT18-4NAT-M	Miniature	.625 in./15.875 mm
CT18-4BLK-C	Miniature	.625 in./15.875 mm
CT18-4BLK-M	Miniature	.625 in./15.875 mm
CT18-5NAT-C	Miniature	1.25 in./31.75 mm
CT18-5NAT-M	Miniature	1.25 in./31.75 mm
CT18-5BLK-C	Miniature	1.25 in./31.75 mm
CT18-5BLK-M	Miniature	1.25 in./31.75 mm
CT18-8NAT-C	Miniature	1.875 in./47.625 mm
CT18-8NAT-M	Miniature	1.875 in./47.625 mm
CT18-8BLK-C	Miniature	1.875 in./47.625 mm
CT18-8BLK-M	Miniature	1.875 in./47.625 mm
CT40-6NAT-C	Intermediate	1.00 in./25.4 mm
CT40-6NAT-M	Intermediate	1.00 in./25.4 mm
CT40-6BLK-C	Intermediate	1.00 in./25.4 mm
CT40-6BLK-M	Intermediate	1.00 in./25.4 mm
CT40-8NAT-C	Intermediate	1.875 in./47.625 mm
CT40-8NAT-M	Intermediate	1.875 in./47.625 mm
CT40-8BLK-C	Intermediate	1.875 in./47.625 mm
CT40-8BLK-M	Intermediate	1.875 in./47.625 mm

Retail Part No.	Strength Classification	Max. Bundle Diameter
CT40-11NAT-C	Intermediate	3.00 in./76.2 mm
CT40-11NAT-M	Intermediate	3.00 in./76.2 mm
CT40-11BLK-C	Intermediate	3.00 in./76.2 mm
CT40-11BLK-M	Intermediate	3.00 in./76.2 mm
CT40-14NAT-C	Intermediate	4.00 in./101.6 mm
CT40-14NAT-M	Intermediate	4.00 in./101.6 mm
CT40-14BLK-C	Intermediate	4.00 in./101.6 mm
CT40-14BLK-M	Intermediate	4.00 in./101.6 mm
CT50-8NAT-C	Standard	1.875 in./47.625 mm
CT50-8NAT-M	Standard	1.875 in./47.625 mm
CT50-8BLK-C	Standard	1.875 in./47.625 mm
CT50-8BLK-M	Standard	1.875 in./47.625 mm
CT50-11NAT-C	Standard	3.00 in./76.2 mm
CT50-11NAT-M	Standard	3.00 in./76.2 mm
CT50-11BLK-C	Standard	3.00 in./76.2 mm
CT50-11BLK-M	Standard	3.00 in./76.2 mm
CT50-14NAT-C	Standard	4.00 in./101.6 mm
CT50-14NAT-M	Standard	4.00 in./101.6 mm
CT50-14BLK-C	Standard	4.00 in./101.6 mm
CT50-14BLK-M	Standard	4.00 in./101.6 mm

Strength Classification Uses

Miniature - Audio/Video and other small wire bundling
Intermediate - Medium Strength for Indoor/Enclosed Applications
Standard - Standard Duty for Indoor/Enclosed Applications, and Identification Purposes
Heavy Duty - Heavy Duty Bundling for Outdoor Applications

NOTE: 18 lb tensile strength is 0.097" (2.46 mm) in width.
40 lb tensile strength is 0.135" (3.43 mm) in width.
50 lb tensile strength is 0.174" (4.42 mm) in width.