



PRODUCT NUMBER

20020621-XXXXXXLF

20020621-□□□□A0□LF

PITCH

M : 7.62 mm

POLES

02: 2 POLES  
03: 3 POLES  
04: 4 POLES  
.

16: 16 POLES


LF : DENOTED ROHS COMPATIBLE

1 : STANDARD PRODUCT  
W/ BOX PACKING

HOUSING CODE

CODE	COLOR	AVAILABILITY
1	GREEN(RAL 6018/T)	STANDARD
2	BLACK	ON REQUEST ONLY
3	GREY(RAL 7004/P)	ON REQUEST ONLY
4	BLUE(RAL 5015/A)	ON REQUEST ONLY

## PROPERTY TABLE

FCI SERIES NAME	07-762
PITCH (mm)	7.62
VOLTAGE RATING (VAC)	300
CURRENT RATING (A)	32
WITHSTANDING VOLTAGE (kV)	1.6
OPERATING TEMP. (°C)	-40~+115
SOLDERING TEMP. (°C)	250±10 (5 sec.)
POLES AVAILABLE	02~16
SAFETY CERTIFICATE	

## NOTES:

## 1. MATERIALS

1-1 HOUSING: THERMALPLASTIC RESIN, UL 94V-0 RATED.

1-2 TERMINAL: COPPER ALLOY, TIN PLATED.

## 2. PRODUCTION SPECIFICATION REFER TO FCI GS-12-625.


## 3. BOXED PACKAGING.

DETAILED PRODUCT PACKING SPECIFICATION REFER TO FCI GS-14-1394.

## 4. FCI, SAFETY CERTIFICATE LOGO AND SERIES NAME TO BE SHOWN ON PRODUCT SURFACE.

## 5. THE PRODUCTS WHERE THE PART NUMBER END IN "LF" MEET THE EUROPEAN UNION DIRECTIVE AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

## 6. RECOMENDED SOLDERING PROCESS BY WAVE SOLDER.

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection 	product family TERMINAL BLOCK			
ltr	ecn no	dr	date	tolerances unless otherwise specified			title TERMINAL BLOCK PLUGGABLE SOCKET, POWER, STRAIGHT W/FLANGE			
A	T10-0062	WL	050710	angles	X.±0.5	MM				
B	T10-0155	WL	093010	tolerances	X.X±0.3	INCH	dwg no 20020621			
C	T10-0187	WL	121410	X'±1"	X.XX±0.1	scale				
D	T-004860	WL	080411	dr	WENDY CHEN	042610	sheet 1 of 2			
				engr	JASON HSU	042610				
				chr	GARY HSIEH	042610	A4			
				appd	JOSEPH HSIA	042610				
sheet index	revision sheet	D	D				type			
		1	2				CUSTOMER Drawing			

