






LOC	DIST	REVISIONS						
FX	00	P	LTR	DESCRIPTION	DATE	DWN	APVD	
		H		REVISED PER EC 0K80-0002-03	15JAN2003	AH	WB	
		J		REVISED PER EC 0K80-0093-03	24APR2003	AH	MS	
		JI		REVISED PER EC 0K80-0147-03	03JUN2003	DA	TS	
		K		REV PER 0K80-0340-03	18NOV2003	AG	MS	



- 1 PLATED WITH 0.00076 MIN THICK GOLD IN MATING AREA, 0.0038 MIN THICK TIN ON SOLDER TAIL, ALL OVER 0.0020 MIN THICK NICKEL
- 2 RECOMMENDED DIMENSION. CUSTOMER TO DETERMINE ACTUAL LENGTH.
- 3 MEASURE AT **-CC-**.
- 4 PART MEET SOLDERABILITY REQUIREMENT PER EIA-364-52.
- 5 SEE TERMINAL LOCATION TABLE ON SHEET TWO.



SUGGESTED P.C. BOARD LAYOUT (HEADER SIDE OF BOARD) SCALE 2:1

42	GREY	9.00	6.00	6.00	9.00	A	B	1326017-9
20	GREY	9.00	6.00	7.50	7.50	AI	B	1326017-7
28	BLACK	9.00	6.00	6.00	9.00	A	B	1326017-6
64	TAN	3.00	6.00	6.00	9.00	A	BI	1326017-5
OBSOLETE								1326017-4
OBSOLETE								1326017-3
64	GREY	9.00	6.00	7.50	7.50	AI	B	1326017-2
64	BLACK	9.00	6.00	6.00	9.00	A	B	1326017-1
TERMINALS PER ASSY		5	CC	BB	AA	LEFT POCKET	RIGHT POCKET	PART NUMBER
COLOR		DIMENSION						KEYING

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN		30NOV99		Tyco Electronics	
mm		9 PLC ±		F. KINSEY		08DEC99		Tyco Electronics	
9 PLC ±		2 PLC ±0.20		LT LE		08DEC99		Harrisburg, PA 17105-3608	
3 PLC ±		4 PLC ±		LT LE		08DEC99		NAME	
4 PLC ±		ANGLES ±°		PRODUCT SPEC		SAE J558-2 8/97		HEADER ASSEMBLY, 64 WAY AIR BAG	
MATERIAL		FINISH		APPLICATION SPEC		-		SIZE	
SEE CALLOUT		SEE CALLOUT		WEIGHT		-		CAGE CODE	
CUSTOMER DRAWING		SCALE		2:1		SHEET		OF 2	
								REV	
								K	



LEGEND

T - TERMINAL

- - NO TERMINAL

AMP 4805 REV 31MAR2000