








PC LAYOUT



CIRCUIT LAYOUT


NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: $X.X \pm 0.4$
 $X.XX \pm 0.25$
3. TERMINAL NUMBERS FOR REF. ONLY.
- ▲ 4. OPERATING FORCE: 500 ± 100 gf
5. TRAVEL: 0.6 ± 0.25 mm
6. CONTACT RATING: 25mA, 24VDC
7. CONTACT RESISTANCE: $100m\Omega$ MAX.
8. INSULATION RESISTANCE: $100M\Omega$ MIN @ 500VDC
9. DIELECTRIC STRENGTH: 300VAC 1 MIN.
10. LIFE: 1,000 CYCLES.
11. OPERATING TEMPERATURE: -40°C TO 85°C
- ▲ 12. PACKAGING: 4,000 PCS PER REEL
13. ▲ DENOTES CRITICAL PARAMETER.
14. 2002/95/EC (ROHS) COMPLIANT
15. SWITCHES TO BE SHIPPED WITH THE ACTUATORS IN THE 'ON' POSITION



ISOMETRIC

.05
[.002 in]
REMOVABLE
POLYIMIDE TAPE SEAL
FOR SOLDER FLUX



TITLE KAN1102 RR

B	17519	ADD NOTE 15, REDRAW	7/31/07	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE 10:1

DATE 7/31/2007

DR BLR

DWG N111250

REV B